#### Metal Switch Short Stroke



MCS 19 painted green



MCS 19 actuator painted red



MCS 19 stainless steel



#### Description

- Momentary action switch available in version Standard, with Point Illumination, Lettering, varnished in different colours

#### - Assembly by mounting with nut

- Pin connections, Pins with Soldering Aid or Clip for Pins

#### Approvals

- EMC: EMC directive 2004/108/EWG

#### **Characteristics**

- Housing and actuator material types: zinc die-cast with nickel plating or stainless steel
- Wide range of materials, colours, lettering, colours of illumination
- Switching voltage 48 VDC, switching current 125 mA
- Zinc die-cast for housing and actuator
- For indoor use, no illumination, no lettering
- Stainless Steel for actuator Optional point illumination and laser lettering with standard or customer-specific symbols
- Stainless Steel for housing and actuator
- for use in harsh environments outdoors
- Varnished Version

Colour adjustments to customer housings possible, as standard: Signal colors red, green and yellow, optional: housing or actuator varnishing according to provided color specifications the varnished actuators are sealed by transparent lacqueur after the laser lettering

#### Weblinks

html-datasheet, General Product Information, CE declaration of conformity, RoHS, CHINA-RoHS, e-Shop, CAD-Drawings, Product News, Detailed request for product

## **MCS 19**


#### **Technical Data**

LED operating data are listed in sepa-			
rate table			
min. 4 VDC , max. 48 VDC			
max. 125 mA			
1.2 W			
1 million actuations at Rated Switching Capacity			
$< 50 \mathrm{m}\Omega, < 150 \mathrm{m}\Omega$ after lifetime			
> 100 MΩ			
< 5 ms			
min. 50 mVDC, max. 24 VDC			
max. 80 mA			
0.36 W			
1 million actuations at Rated Switching			
Capacity			
< 50 m $\Omega$ , < 150 m $\Omega$ after lifetime			
> 100 MΩ			
< 5 ms			


Mechanical Data	
Actuating Force	3.7 N
Actuating Travel	0.4 mm,
Lifetime	1 million actuations
Shock Protection	IK 05 ,
Tightening Torque	0.4 Nm with Sealing Ring, 1.5 Nm wit- hout Sealing Ring
Climatical Data	
Operating Temperature	-20 to +60 °C
Storage Temperature	-20 to +60 °C
IP-Protection	IP 65 Front Side Contact Area, IP 40 Front Side mechanical,
Salt Spray Test (acc. to DIN 50021-SS)	24 h / 48 h / 96 h Residence Time
Other Data	
Contact Material	Ag / Au
Soldering Data	
Tinning	260 °C / 2 sec according to DIN IEC 60068-2-20
Solderability	260 °C / 2 sec (IEC 68-2-20 Test Ta Method 1)
Resistance to Soldering Heat	260 °C / 5 sec (IEC 68-2-20 Test Tb Method 1A)
Material	
Housing	Stainless Steel 1.4305 / Zinc Die Ca- sting Nickel Plated
Actuator unlettered	Zinc Die Casting Nickel Plated
Actuator lettered	Stainless Steel
Contact	CuZn37 2,5 µm Ag
Snap Dome	X 12 CrNi 177 gold plated
Socket	PA

### Dimension

MCS 19




#### MCS 19 Connection Versions




Drawing 1: Pins Drawing 2: Pins with Soldering Aid Drawing 3: Clip for Pins

#### MCS 19 PI




Legend: Zinc Die Casting Version: x = 1 mm without sealing ring x = 2 mm with sealing ring Stainless Steel Version: x = 1 mm without sealing ring x = 1,7 mm with sealing ring


#### Dimension




### Drilling diagram

#### Diagrams







#### **Point Illumination**

Operating Data	Forward Current max.	Forward Voltage at 10 mA	Forward Voltage max.		
LED red	30 mA	1.9 VDC	3.0 VDC		
LED green	30 mA	2.1 VDC	3.0 VDC		
LED yellow	30 mA	2.1 VDC	3.0 VDC		
LED blue	20 mA	3.8 VDC	4.5 VDC		
LED red/green	25 mA	2.0 VDC	2.5 VDC		
Attention: Switches are delivered without series resistor.					

## **MCS 19**

[nicht konfiguriert]: element\_name:Beschriftung\_MCS\_19\_ ES: id:170327

### Lettering

0		
Die letzten drei		
000	keine Beschriftung	
001-074	Standardbeschrif-	
101-	kundenspezifische	

Bestellbeispiel

#### Lettering Colour of Laser Lettering

Material	Lettering Colou	r			
Stainless Steel	black	Filled letters			
For further Lettering details see also weblink:					
General Product Information					

#### **Order Index Lettering**

Laser Marking			
001 = <b>A</b>	021 = <b>U</b>	041 = ÷	061 = <b>EIN</b>
002 = <b>B</b>	022 = <b>V</b>	042 = *	062 = <b>AUS</b>
003 = <b>C</b>	023 = <b>W</b>	043 = <b>=</b>	063 = <b>AUF</b>
004 = <b>D</b>	024 = <b>X</b>	044 = #	064 = <b>AB</b>
005 = <b>E</b>	025 = <b>Y</b>	045 = ↔	065 = <b>ON</b>
006 = <b>F</b>	026 = <b>Z</b>	046 = ≎	066 = <b>OFF</b>
007 = <b>G</b>	027 = <b>0</b>	047 = →	067 = <b>UP</b>
008 = <b>H</b>	028 = <b>1</b>	048 = ←	068 = <b>DOWN</b>
009 = <b>I</b>	029 = <b>2</b>	049 = ↓	069 = <b>HIGH</b>
010 = <b>J</b>	030 = <b>3</b>	050 = ↑	070 = <b>LOW</b>
011 = <b>K</b>	031 = <b>4</b>	051 = %	071 = <b>ON/OFF</b>
012 = <b>L</b>	032 = <b>5</b>	052 =	072 = <b>START</b>
013 = <b>M</b>	033 = <b>6</b>	053 = <b>CTRL</b>	073 = <b>RESET</b>
014 = <b>N</b>	034 = <b>7</b>	054 = <b>RETURN</b>	074 = 🕛
015 = <b>O</b>	035 = <b>8</b>	055 = <b>SHIFT</b>	075 = 🔆
016 = <b>P</b>	036 = <b>9</b>	056 = <b>LOCK</b>	076 = 🗘
017 = <b>Q</b>	037 = <b>+</b>	057 = <b>STOP</b>	
018 = <b>R</b>	038 = <b>-</b>	058 = <b>ENTER</b>	
019 = <b>S</b>	039 = .	059 = <b>BACK</b>	
020 = <b>T</b>	040 = x	060 = <b>LINE</b>	

#### All Variants

Terminal	Kontakte	Housing Material	Actuator Material	Lettering	Illumination	Color LED	Config. Code	Bestellnummer	_
Pins	Ag	Zinc Diecasting	Zinc Diecasting	without Lettering	non-illuminated	-	MCS 19 Zinc	1241.2800	
Pins with Solde- ring Aid	Ag	Zinc Diecasting	Zinc Diecasting	without Lettering	non-illuminated	-	MCS 19 Zinc	1241.2801	
Clip for Pins	Ag	Zinc Diecasting	Zinc Diecasting	without Lettering	non-illuminated	-	MCS 19 Zinc	1241.2802	
Pins	Ag	Zinc Diecasting	Stainless Steel	without Lettering	non-illuminated	-	MCS 19 Zinc/Stainless Steel	1241.2805	
Pins	Ag	Zinc Diecasting	Stainless Steel	with Lettering	non-illuminated	-	MCS 19 Zinc/Stainless Steel	1241.2805.057	
Pins with Solde- ring Aid	Ag	Zinc Diecasting	Stainless Steel	without Lettering	non-illuminated	-	MCS 19 Zinc/Stainless Steel	1241.2806	
Clip for Pins	Ag	Zinc Diecasting	Stainless Steel	without Lettering	non-illuminated	-	MCS 19 Zinc/Stainless Steel	1241.2807	
Pins	Au	Zinc Diecasting	Zinc Diecasting	without Lettering	non-illuminated	-	MCS 19 Zinc	1241.2810	

Switches

#### **Metal Line Switches** www.schurter.com/PG70

### **MCS 19**

Clip for Pins	Au	Zinc Diecasting	Zinc Diecasting	without Lettering	non-illuminated	-	MCS 19 Zinc	1241.2812	
Pins	Au	Zinc Diecasting	Stainless Steel	without Lettering	non-illuminated	-	MCS 19 Zinc/Stainless Steel	1241.2815	
Clip for Pins	Au	Zinc Diecasting	Stainless Steel	without Lettering	non-illuminated	-	MCS 19 Zinc/Stainless Steel	1241.2817	
Pins	Ag	Stainless Steel	Stainless Steel	without Lettering	non-illuminated	-	MCS 19 Stainless Steel	1241.2820	
Pins with Solde- ring Aid	Ag	Stainless Steel	Stainless Steel	without Lettering	non-illuminated	-	MCS 19 Stainless Steel	1241.2821	
Clip for Pins	Ag	Stainless Steel	Stainless Steel	without Lettering	non-illuminated	-	MCS 19 Stainless Steel	1241.2822	
Clip for Pins	Au	Stainless Steel	Stainless Steel	without Lettering	non-illuminated	-	MCS 19 Stainless Steel	1241.2827	
Pins with Solde- ring Aid	Ag	Stainless Steel	Stainless Steel	without Lettering	Point Illumination	red	MCS 19 PI	1241.2830	
Pins with Solde- ring Aid	Ag	Stainless Steel	Stainless Steel	without Lettering	Point Illumination	green	MCS 19 PI	1241.2831	
Pins with Solde- ring Aid	Ag	Stainless Steel	Stainless Steel	without Lettering	Point Illumination	red / green	MCS 19 PI	1241.2833	
Pins with Solde- ring Aid	Ag	Zinc Diecasting	Stainless Steel	without Lettering	Point Illumination	red	MCS 19 PI	1241.2855	
Pins with Solde- ring Aid	Ag	Zinc Diecasting	Stainless Steel	without Lettering	Point Illumination	green	MCS 19 PI	1241.2856	P
Pins with Solde- ring Aid	Ag	Zinc Diecasting	Stainless Steel	without Lettering	Point Illumination	yellow	MCS 19 PI	1241.2857	
Pins with Solde- ring Aid	Ag	Zinc Diecasting	Stainless Steel	without Lettering	Point Illumination	red / green	MCS 19 PI	1241.2858	ŀ
Pins with Solde- ring Aid	Ag	Zinc Diecasting	Stainless Steel	without Lettering	Point Illumination	blue	MCS 19 PIPI	1241.2859	

Order numbers MCS 19, varnished versions (Colour of the switch housing or the actuator): 1241.28xxA => A = 1 (yellow) / 3 (red) / 5 (green) xx = 70 standard pins, 71 Soldering aid, 72 Screw connection with varnished housing die cast / actuator die cast

x = 73 standard pins, 74 soldering aid, 75 screw connection with varnished housing die cast / actuator stainless steel xx = 77 standard pins, 78 soldering aid, 79 screw connection with varnished actuator stainless steel / housing die cast Order numbers MCS 19, illuminated versions (Point Illumination): 1241.2876.A.XXX.B and respectively 1241.2880.A.XXX.B => B = 1 (red) / 2 (green) / 3 (yellow) / 4 (blue) / 5 (red-green)

For Lettering versions see tables "Lettering" and "Order Index Lettering" to determine the symbol

Plastic nut with gasket are enclosed in the box.

#### Most Popular.

Availability for all products can be searched real-time:http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

20 in box with insert (20 pcs, with connecting terminal 10 pcs.) Packaging unit



- Actuating elements in ESD safe packaging - Screw nuts and sealing rings in a bag (enclosd in the box)



- Actuating elements in ESD safe packaging

- Screw nuts and sealing rings in a bag (enclosed in the box)

# **MCS 19**

#### Accessories

Description



Connecting Terminal MCS 19 Connecting Terminal

The specifications, descriptions and illustrations indicated in this document are based on current information. All content is subject to modifications and amendments. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability and test each product selected for their own applications.