

# 17P/PC 470KA 6X19FL SPDT PP ✓ ACTIVE

Citec | Citec 17P

TE Part # 1624197-5

TE Internal #: 17PCSA474MC19P

[View on TE.com >](#)



Passive Components > Resistors > Variable Resistors > Potentiometers



Termination Type: **Printed Circuit Board**

Sealed: **No**

Tolerance: **20%**

Resistance: **470K  $\Omega$**

Power Rating: **.25 W**

## Features

### Product Type Features

Switch Type	Rotary Push Push SPDT
Product Type	Variable Resistor
Sealed	No

### Electrical Characteristics

Voltage Rating	350 V
Tolerance	20%
Resistance	470K $\Omega$
Power Rating	.25 W

### Termination Features

Termination Type	Printed Circuit Board
------------------	-----------------------

### Dimensions

Dimensions	19.2 x 17 mm
------------	--------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197)



Candidate List Declared Against: JAN 2019 (197)

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

### Compatible Parts



Potentiometers(12)

### Also in the Series | Citec 17P



Potentiometers(13)

### Customers Also Bought



## Documents

### Datasheets & Catalog Pages

[1309350\\_PASSIVE\\_COMPONENT](#)

English

[Spindle Operated Potentiometers - Type 17P series - Tyco Electronics Passives](#)

English