



















	CTS35UN			CTS50/70N			CTS50/70NA			CTS95U/120N			
													
Terminal Width	16 mm			20.5 mm			20.5 mm			25 mm			
Height x Length	58 x 50.5 mm			75.5 x 71 mm			75.5 x 71 mm			90 x 83 mm			
Stripping Length	15 mm			22 mm			24 mm			24 mm			
Insulation Material	Polyamide 6.6			Polyamide 6.6			Polyamide 6.6			Polyamide 6.6			
Type of Connection	2 screw clamps & 1 tapped hole for cross			2 screw clamp connections			2 screw clamp connections			2 screw clamp connections			
Approvals													
Wire Range	12-2 AWG	4-35 sq.mm	12-2 AWG	8-2/0 AWG	10-70 sq.mm	8-2/0 AWG	8-2/0 AWG	10-70 sq.mm	8-2/0 AWG	2-250 KCMIL	25-120 sq.mm	2-250 KCMIL	
Voltage Rating	600 V	1000 V	600 V	1000V	1000 V	1000 V	1000V	1000 V	1000 V	1000V	1000 V	1000 V	
Current Rating	130 A	125 A	130 A	175 A	192 A	175 A	175 A	192 A	175 A	240 A	269 A	240 A	
Torque	25 lb-in	2.5 Nm	25 lb-in	38 lb-in	3 Nm	38 lb-in	38 lb-in	3 Nm	38 lb-in	90 lb-in	6 Nm	90 lb-in	
Other Approvals													
<b>Terminal Block</b>	<b>Cat. No.</b>	<b>Std. Pk.</b>	<b>Cat. No.</b>	<b>Std. Pk.</b>	<b>Cat. No.</b>	<b>Std. Pk.</b>	<b>Cat. No.</b>	<b>Std. Pk.</b>	<b>Cat. No.</b>	<b>Std. Pk.</b>	<b>Cat. No.</b>	<b>Std. Pk.</b>	
	<b>CTS35UN</b>	50	<b>CTS50/70N</b>	20	<b>CTS50/70NA</b>	20	<b>CTS95U/120N</b>	10					
<b>Isolation Partition</b>	<b>PP35UN</b>	50											
<b>DIN Rail</b> for ordering information refer to pages 90-91													
<b>End Stop</b> for ordering info. refer to page 92	<b>CA702</b>	50	<b>CA202</b>	50	<b>CA202</b>	50	<b>CA202</b>	50	<b>CA202</b>	50	<b>CA202</b>	50	
	<b>CA802</b>	50	<b>CA102</b>	50	<b>CA102</b>	50	<b>CA102</b>	50	<b>CA102</b>	50	<b>CA102</b>	50	
<b>Internal Jumper</b>	2 pole	CA771/2	50	<b>AUX6</b> <b>Auxiliary Terminal Block</b> Used for: CTS50/70N CTS50/70NA CTS95/120N  Wire Range 22-8 AWG  In certain power circuits, there is a need to take an extra connection for an Auxiliary circuit like an indicating light or contactor. The AUX6 terminal easily plugs into the terminal and provides this extra connection point.							<b>Ratings As Per</b> IEC60947-7-1 Voltage/Current: 1000 V / 41 A Torque: 0.8 Nm <b>IEC 60079-7</b> Voltage/Current: 630 V / 36 A Torque: 0.8 Nm <b>UL-1059</b> Voltage/Current: 600 V / 50 A Torque: 14 lb-in <b>CSA22.2-158</b> Voltage/Current: 600 V / 50 A Torque: 14 lb-in <b>Width x Length x Height</b> 8 x 53.6 x 29.4 mm <b>Std. Pk.: 10</b> <b>Marking Tag: MT8</b>		
	3 pole	CA771/3	25										
	4 pole	CA771/4	25										
	10 pole	CA771/10	10										
<b>Insulated Internal Jumper</b>	2 pole	CA781/2	50										
	3 pole	CA781/3	25										
	4 pole	CA781/4	25										
	10 pole	CA781/10	10										
<b>Current Bars</b>	2 pole	CA703/10	100										
	3 pole	CA704/10	100										
	4 pole	CA705/10	100										
	10 pole	CA770/10	100										
	10 pole (breakable)	CA770/10	100										
	100 pole												
<b>Shorting Link System</b>				<b>CA628/2</b>	10	<b>CA628/2</b>	10	<b>CA628/2</b>	10	<b>CA629/2</b>	10	<b>CA629/2</b>	10
				<b>CA628/3</b>	10	<b>CA628/3</b>	10	<b>CA628/3</b>	10	<b>CA629/3</b>	10	<b>CA629/3</b>	10
<b>Shorting Sleeve &amp; Screw</b>		<b>CA707/S/Q/2</b>	100										
<b>Marking Tags</b>	<b>MT16</b>	100	<b>MT16</b>	100	<b>MT16</b>	100	<b>MT16</b>	100	<b>MT16</b>	100	<b>MT16</b>	100	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[CTS35UN](#) [CTS50/70N](#) [CTS50/70NA](#) [CTS95/120N](#)