SECTION A-A Top View of Assembly End View of Assembly 70.99 [2.80] В В (Inner Box Width) 57.35 304.44 [2.26] [11.99] 75.84 [2.99] **SECTION B-B** Cover **Side View of Assembly** Ø4.76 [.19] 57.35 1.02 47.83 [2.26] [.04] [1.88] (Wall Thickness) 302.41 285.39 [11.91] [11.24] (Inner Box Length) 293.32 [11.55] 55.32 Enclosures can be Factory Modified (Milling, Drilling, Printing etc.) [2.18] Contact Factory mjm@hammondmfg.com for quotes Solid models of this enclosure available in STEP or IGES. (Inner Box Height) NOTE **Bottom** Ø2.69 Purchased assembly includes bottom, cover and 4 cover screws. [.11] Bottom and cover are made from 0.04" Aluminum Panels. PART NUMBERS 56.34 37.52 1411W Enclosure [2.22] [1.48] Natural Finish Enclosure 1411WU ASA 61 Grev Enclosure 1411W **ACCESSORIES** 293.32 Plated Cover Screws (Pkg 6) [11.55] 1421J6 73.03 [6-32 x 1/4" Self-Tapping Screws] [2.88] 301.63 [11.88] MANUFACTURING TO 1411W Dimensions: mm www.hammondmfg.com [inches]