


Chassis Mount Fuse Holder




Description

A chassis mount fuseholder suitable for fuses 32mm×6.25mm fuses up to a maximum current of 10A, 250V AC.

Specifications

Power Rating	: 10A 250V AC
Contact Resistance	: DC 500V 100MΩ Min.
Insulation Resistance	: AC 1500V 1 minute
Fuse Size	: Ø6.35mm×30mm
Material Frame	: Black, PBT
Terminal Material	: Nickel Plated Brass

Diagram



Part Number Table

Dimensions : Millimetres
Tolerances: ±0.3mm

Description	Part Number
Chassis Mount Fuse Holder for 10A, 32mm×6.35mm Fuses	PE01001

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.