

# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-4029** 



Release | Revision: B/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

#### Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

#### Page 2

**Reliability Tests** 

#### Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

#### Page 4

Frequency Response Curve

#### Page 5

Dimensions

#### Page 6

Packing

# **Dynamic Speaker Electroacoustic Characteristics**

#### **Sound Pressure Level**

85±3dB SPL @ 0.8, 1.0, 1.2 and 1.5KHz in (1.0W/0.5M) in average **Test Set Up:** Measuring conditions and procedures shown in Figure 1 & 2

#### **Frequency Response Curve**

As shown in Figure 3

#### **Frequency Range**

F0 Hz ~ 20 KHz

#### **Resonance Frequency**

 $450 \pm 20\%$ Hz

#### **Input Power (Nominal and Maximum)**

Rated Noise Power 2.0W

**Short Term Max Power: 3.0W** 

#### **Distortion**

Less than 7% @1KHz, 1.0W/0.5W

#### Buzz & Rattle, Etc.

Should not be audible at 5.65V sine Wave between F0 ~ 20KH

#### **Polarity**

Cone will move forward with positive dc current to "+" terminal

## **General Specifications**

#### **Temperature Range**

Operating Temperature -20°C~+60°C

Storage Temperature -25°C~+70°C

#### **Standard Test Conditions**

**Temperature** 17°C ~ 25°C

Relative Humidity 45% ~ 85% (RH)

#### **AC Impedance**

16±15%Ω

#### **Dimension**

40.2 x 28.5 x H11.5 mm Wire 40 mm UL1571 / AWG 28# Connector JST-SHR-02V-S-B

#### IP Level

No rating



# soberton inc.

# **SP DYNAMIC SPEAKER UNIT**

**Acoustic Product Specification** 

**Product Number: SP-4029** 



# Release | Revision: B/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

## Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

#### Page 2

**Reliability Tests** 

#### Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

#### Page 4

Frequency Response Curve

## Page 5

**Dimensions** 

#### Page 6

**Packing** 

### **Reliability Tests**

After any following test, parts should conform to original performance within ±3 dB tested with Rated Power, after 6 hours of recovery period.

#### **High Temperature Test**

High Temperature +70±3°C

**Duration** 96 hours

#### **Low Temperature Test**

Low Temperature -25±3°C

**Duration** 96 hours

#### **Humidity Test**

Temperature +30±3°C

**Relative Humidity** 90%~96%

**Duration** 96 hours

#### **Temperature Cycle Test**

Temperature -25°C +65°C

**Duration** 6 hours 6 hours

Temperature gradient ±3°C

Cycle 5

#### **Drop Test**

The speakers contained in normal box onto the board 40mm thick 10 times from the height of 75cm

#### **Vibration Test**

10Hz ~ 55Hz ~ 10Hz sine-wave sweep 15min. 5G(constant) X,Y, Z 3 direction. 2 hours each, total 6 hours.

#### **Load Test**

Rated Power Pink Noise is applied for 24 hours at room temperature

#### **Lead Wire Pull Strength Test**

The pull force shall be applied to double lead wire: Horizontal 3.0N(0.306kg) for 30 seconds. Vertical 2.0N(0.204kg) for 30 seconds.



# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-4029** 



# Release | Revision: B/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

#### Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

#### Page 2

**Reliability Tests** 

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

#### Page 4

Frequency Response Curve


# Page 5

Dimensions


#### Page 6

Packing

# Measuring Method (Fig. 1)



# **Standard Test Condition of Speaker (Fig. 2)**



Audio Analyzer JHDS Type 6160S



# **SP DYNAMIC SPEAKER UNIT**

**Acoustic Product Specification** 

**Product Number: SP-4029** 



Release | Revision: B/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

#### Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

## Page 2

**Reliability Tests** 

#### Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of

#### Page 4

Frequency Response Curve

#### Page 5

Dimensions


#### Page 6

**Packing** 

# Frequency Response Curve (Fig. 3)

The swept sine-wave frequency response of a loudspeaker should ideally not deviate more than indicate per Fig.3

#### XY Graph 3





# soberton inc.

# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-4029** 



Release | Revision: B/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

#### Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

### Page 2

**Reliability Tests** 

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

#### Page 4

Frequency Response Curve

#### Page 5


Dimensions


#### Page 6

Packing

### **Dimensions**

Tolerance: ±0.5 (unit: mm)





No.	Part Name	Material	Quantity
1	PCB Terminal	Paper + metal	1
2	Yoke	SPCC	1
3	Magnet	Nd Fe B	1
4	Plate	SPCC	1
5	Frame	ABS	1
6	Voice Coil	Paper + Cu	1
7	Diaphragm	Cloth-edge + paper	1
8	Сар	Paper	1
9	Wire (40mm)	UL1571 / AWG 28#	2
10	Connector	JST-SHR-02V-S-B	1





# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-4029** 



Release | Revision: B/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

#### Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

### Page 2

**Reliability Tests** 

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

#### Page 4


Frequency Response Curve

#### Page 5

Dimensions

#### Page 6

**Packing** 



6