

# PRODUCT DATASHEET LN COMP HO 1500 25 W 3000 K

LINEAR COMPACT HIGH OUTPUT | Compact single or light line luminaire with high luminous flux



#### **AREAS OF APPLICATION**

- Direct replacement for luminaires with fluorescent lamps
- Indoor applications
- Corridors, entrance areas, stairwells, living rooms, basements
- Accent lighting
- Public areas
- Cove lighting
- Shelves, furniture integration or under cabinet mounting
- Seamless linear lighting

#### **PRODUCT BENEFITS**

- Compact dimensions
- Little space required thanks to compact dimensions
- Seamless connection of up to 10 luminaires in a line
- High lumen output up to 2500 lm
- Seamless connection without visible cables when connected to Linear Compact Batten
- Low flicker light thanks to special electronic control gear
- Angled connection possible with included cable
- Flexible installation in 2 different angles with 2 different mounting options
- Flexible application due to a wide range of available lengths of 600 to 1500 mm
- 5 years quarantee

#### **PRODUCT FEATURES**

- Replacement for traditional T8 or T5 luminaires
- Up to 10 luminaires connectable



- Translucent end caps
- Linear Compact Batten connectable at the beginning of the row with wiring on back side
- Versions with luminous flux 1000...2500 lm available
- 4 different lengths available
- High luminous efficacy: up to 100 lm/W
- Glow Wire Test according to IEC 60695-2-12: 850 °C

### **TECHNICAL DATA**

#### Electrical data

Nominal wattage	25.00 W
Operating mode	Integrated LED driver
Nominal voltage	220240 V
Power factor λ	>0.90
Mains frequency	50/60 Hz
Inrush current	10.0 A
Total harmonic distortion	91 %
Inrush current time T <sub>h50</sub>	160 µs

#### Luminaire control gear data

Ouput current	270 mA
Max. no. of lum. on circuit break. B16 A	75
Max. no. of lum. on circuit break. C10 A	60
Max. no. of lum. on circuit break. C16 A	96

#### Photometrical data

Color temperature	3000 K
Luminous flux	2500 lm
Luminous efficacy	100 lm/W
Standard deviation of color matching	<5 sdcm
Light color (designation)	Warm White
Color rendering index Ra	>80

### Light technical data

Beam angle	140°
Seam angle	110

# Dimensions & weight



Length	1473 mm
Width	24.0 mm
Height	36.0 mm
Product weight	600.00 g

# Colors & materials

Body material	Polycarbonate (PC)
Housing color	White
Product color	White
Housing color	White
Cover material	Polycarbonate (PC)

# Temperatures & operating conditions

Ambient temperature range	-20+40 °C

# Lifespan

Number of switching cycles	100000
Lifespan L70/B50 at 25 °C	50000 h
Lifespan L80/B10 at 25 °C	40000 h
Lifespan L90/B10 at 25 °C	30000 h

# Additional product data

Mounting type	Surface
Mounting location	Ceiling / Wall


# Capabilities

Dimmable	No
Type of connection	Screw terminal, 2-Pole (L,N)
LED module replaceable	Not replaceable

Ball shot safe	No
Certificates & standards	
Protection class IK (shock resistance)	IK03

Protection class IK (shock resistance)	IK03
Glow Wire Test according to IEC 695-2-1	850 °C
Photobiological safety group EN62778	RG 0
Protection class	1
Type of protection	IP20
Standards	CE/CB/TÜV SÜD/EAC/RoHS

# Light Distribution



LDC typ polar

### **EQUIPMENT / ACCESSORIES**

- All required accessories included

## **LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075106352	Folding carton box 1	1680 mm x 40 mm x 30 mm	741.00 g	2.02 dm <sup>3</sup>
4058075106369	Shipping carton box 25	1718 mm x 233 mm x 180 mm	19491.00 g	72.05 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

# **REFERENCES / LINKS**

For Guarantee see

www.ledvance.com/guarantee

#### **DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.