
#### TPDVxx40



## 40 A high voltage Triacs

Datasheet - production data



#### **Features**

On-state current (I<sub>T(RMS)</sub>): 40 A

Max. blocking voltage (V<sub>DRM</sub>/V<sub>RRM</sub>): 1200 V

Gate current (I<sub>GT</sub>): 200 mA

Commutation at 10 V/µs: up to 142 A/ms

Noise immunity: 500 V/μs

Insulated package:

- 2,500 V rms (UL recognized: E81734)

#### **Description**

The TPDVxx40 series use a high performance alternistor technology. Featuring very high commutation levels and high surge current capability, this family is well adapted to power control on inductive load (motor, transformer...).

**Table 1. Device summary** 

Parameter	Blocking voltage V <sub>DRM</sub> /V <sub>RRM</sub>	On-state current I <sub>T(RMS)</sub>	Gate current I <sub>GT</sub>	
TPDV640RG	600 V			
TPDV840RG	800 V	V 40 A 200		
TPDV1240RG	1200 V			

Characteristics TPDVxx40

## 1 Characteristics

Table 2. Absolute ratings (limiting values)

Symbol	Parameter			Value	Unit
I <sub>T(RMS)</sub>	On-state rms current (180° conduction a	ngle)	T <sub>c</sub> = 75 °C	40	Α
		t <sub>p</sub> = 2.5 ms		590	А
I <sub>TSM</sub>	Non repetitive surge peak on-state current	$t_p = 8.3 \text{ ms}$	T <sub>j</sub> = 25 °C	370	
		t <sub>p</sub> = 10 ms		350	
I <sup>2</sup> t	I <sup>2</sup> t value for fusing	t <sub>p</sub> = 10 ms	T <sub>j</sub> = 25 °C	610	A <sup>2</sup> S
dI/dt	Critical rate of rise of on-state current $I_G = 500 \text{ mA}$ ; $dI_G/dt = 1 \text{ A/}\mu\text{s}$	Repetitive F =	Repetitive F = 50 Hz		A/µs
di/di		Non repetitive	Non repetitive		
	Repetitive peak off-state voltage	TPDV640	T <sub>j</sub> = 125 °C	600	V
V <sub>DRM</sub> V <sub>RRM</sub>		TPDV840		800	
RRIVI		TPDV1240		1200	
T <sub>stg</sub>	Storage junction temperature range			-40 to +150	°C
Tj	Operating junction temperature range	-40 to +125			
$T_L$	Maximum lead temperature for soldering during 10 s at 2 mm from case			260	°C
V <sub>INS(RMS)</sub> <sup>(1)</sup>	Insulation rms voltage			2500	V

<sup>1.</sup> A1, A2, gate terminals to case for 1 minute

Table 3. Electrical Characteristics ( $T_j = 25$  °C, unless otherwise specified)

Symbol	Test condition		Quadrant		Value	Unit
I <sub>GT</sub>	V 40 V DO D 00 0		1 11 111	Max.	200	mA
V <sub>GT</sub>	$V_D = 12 \text{ V DC}, R_L = 33 \Omega$		-    -	Max.	1.5	V
V <sub>GD</sub>	$V_D = V_{DRM} R_L = 3.3 \text{ k}\Omega$	T <sub>j</sub> = 125 °C	1 - 11 - 111	Min.	0.2	V
t <sub>gt</sub>	$V_D = V_{DRM} I_G = 500 \text{ mA dI}_G/\text{dt}$	= 3A/µs	1 - 11 - 111	Тур.	2.5	μs
I <sub>H</sub> <sup>(1)</sup>	I <sub>T</sub> = 500 mA Gate open		Тур.	50	mA	
IL	I <sub>G</sub> = 1.2 x I <sub>GT</sub>		1 - 111	T. 100	100	mA
"L	IG - 1.2 X IGT	1.2 X IGT		Тур.	200	
dV/dt	Linear slope up to : $V_D = 67\% V_{DRM}$ Gate open $T_j = 125 ^{\circ}\text{C}$			Min.	500	V/µs
V <sub>TM</sub> <sup>(1)</sup>	I <sub>TM</sub> = 56 A t <sub>p</sub> = 380 μs		Max.	1.8	V	
I <sub>DRM</sub>	I <sub>DRM</sub> V			Max.	20	μA
I <sub>RRM</sub>	$V_{DRM} = V_{RRM}$	T <sub>j</sub> = 125 °C		IVIAA.	8	mA
(dl/dt)c (1)	$(dV/dt)c = 200 V/\mu s$ $T_i = 125 °C$			Min.	35	A/ms
(dirat)C · ·	(dV/dt)c = 10 V/μs	1, - 123 0		iviill.	142	Ailla

<sup>1.</sup> For either polarity of electrode  ${\rm A_2}$  voltage with reference to electrode  ${\rm A_1}$ .



TPDVxx40 Characteristics

Table 4. Gate characteristics (maximum values)

Symbol	Parameter	Value	Unit	
P <sub>G(AV)</sub>	Average gate power dissipation	1	W	
P <sub>GM</sub>	Peak gate power dissipation $t_p = 20 \mu s$		40	W
I <sub>GM</sub>	Peak gate current $t_p = 20 \mu s$		8	А
V <sub>GM</sub>	Peak positive gate voltage $t_p = 20 \mu s$		16	V

Table 5. Thermal resistance

Symbol	Parameter	Value	Unit
R <sub>th(j-a)</sub>	Junction to ambient	50	°C/W
R <sub>th(j-c)</sub> DC	Junction to case for DC	1.2	°C/W
R <sub>th(j-c)</sub> AC	Junction to case for 360 °conduction angle (F = 50 Hz)	0.9	°C/W

Figure 1. Max. rms power dissipation versus on-state rms current (F = 50 Hz) (curves limited by (dl/dt)c)




Figure 2. Max. rms power dissipation and max. allowable temperatures ( $T_{amb}$  and  $T_{case}$ ) for various  $R_{th}$ 




Figure 3. On-state rms current versus case temperature








Figure 4. Relative variation of thermal impedance versus pulse duration



Characteristics TPDVxx40











Figure 9. Safe operating area below curve



TPDVxx40 Package information

## 2 Package information

- Epoxy meets UL94, V0
- Cooling method:C (by conduction)
- Recommended torque value:0.9 to 1.2 N·m

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: <a href="https://www.st.com">www.st.com</a>. ECOPACK® is an ST trademark.

#### 2.1 TOP3 insulated package information

Figure 10. TOP3 insulated package outline

Package information TPDVxx40

Table 6. TOP3 insulated package mechanical data

	Dimensions					
Ref.		Millimeters			Inches <sup>(1)</sup>	
	Тур.	Min.	Max.	Тур.	Min.	Max.
Α		4.4	4.6		0.173	0.181
В		1.45	1.55		0.057	0.061
С		14.35	15.60		0.565	0.614
D		0.5	0.7		0.020	0.028
Е		2.7	2.9		0.106	0.114
F		15.8	16.5		0.622	0.650
G		20.4	21.1		0.815	0.831
Н		15.1	15.5		0.594	0.610
J		5.4	5.65		0.213	0.222
K		3.4	3.65		0.134	0.144
ØL		4.08	4.17		0.161	0.164
Р		1.20	1.40		0.047	0.055
R	4.60			0.181		

<sup>1.</sup> Values in inches are converted from mm and rounded to 4 decimal digits.

# 3 Ordering information

**Table 7. Ordering information** 

Order code	Marking	Package	Weight	Base qty.	delivery mode
TPDV640RG	TPDV640				
TPDV840RG	TPDV840	TOP3 insulated	4.5 g	30	Tube
TPDV1240RG	TPDV1240				

## 4 Revision history

**Table 8. Document revision history** 

Date	Revision	Changes
30-Mar-2011	1	Initial release.
10-Jun-2015	2	Updated <i>Table 3</i> . Updated <i>Figure 9</i> . Format updated to current standard.

#### **IMPORTANT NOTICE - PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2015 STMicroelectronics - All rights reserved

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics:

TPDV1240RG TPDV640RG TPDV840RG