


A759, Polymer Aluminum, 150 uF, 20%, 35 VDC, -55/+125°C, Lead Spacing = 5mm



Dimensions	
D	10mm +/-0.5mm
L	12mm +/-1mm
S	5mm +/-0.5mm
H0	18.5mm +/-0.5mm
F	0.6mm +/-0.5mm

Packaging Specifications	
Packaging:	Ammo
Packaging Quantity:	500

General Information	
Supplier:	KEMET
Series:	A759
Dielectric:	Polymer Aluminum
Description:	Single Ended, Polymer Aluminum
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No

Specifications	
Capacitance:	150 uF
Capacitance Tolerance:	20%
Voltage DC:	35 VDC, 40.2 VDC (Surge)
Temperature Range:	-55/+125°C
Rated Temperature:	125°C
Life:	2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor:	12.00% 120Hz 20c
Resistance:	30 mOhms (100kHz 20C)
Ripple Current:	4630 mAmps (100kHz 105C), 2700 mAmps (100kHz 125C)
Leakage Current:	787.5 uA (2min 20°C)
Impedance Ratio at -25C:	1.25
Impedance Ratio at -55C:	1.25