

Is Now Part of



# **ON Semiconductor**®

# To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="https://www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to <a href="https://www.onsemi.com">Fairchild\_questions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese



#### April 2015


# MOC8021M, MOC8050M 6-Pin DIP Photodarlington Optocoupler (No Base Connection)

#### Features

- High BV<sub>CEO</sub>:
  - Minimum 50 V (MOC8021M)
  - Minimum 80 V (MOC8050M)
- High Current Transfer Ratio:
  - Minimum 1000% (MOC8021M)
  - Minimum 500% (MOC8050M)
- No Base Connection for Improved Noise Immunity
- Safety and Regulatory Approvals:
  - UL1577, 4,170 VAC<sub>RMS</sub> for 1 Minute
  - DIN-EN/IEC60747-5-5, 850 V Peak Working Insulation Voltage

### Applications

- Appliances, Measuring Instruments
- I/O Interface for Computers
- Programmable Controllers
- Portable Electronics
- Interfacing and Coupling Systems of Different Potentials and Impedance
- Solid State Relays



# Description

The MOC8021M and MOC8050M are photodarlingtontype optically coupled optocouplers. The devices have a gallium arsenide infrared emitting diode coupled with a silicon darlington phototransistor. MOC8021M, MOC8050M — 6-Pin DIP Photodarlington Optocoupler (No Base Connection)

## Safety and Insulation Ratings

As per DIN EN/IEC 60747-5-5, this optocoupler is suitable for "safe electrical insulation" only within the safety limit data. Compliance with the safety ratings shall be ensured by means of protective circuits.

| Parameter                                  |                        | Characteristics |
|--|------------------------|-----------------|
| Installation Classifications per DIN VDE   | < 150 V <sub>RMS</sub> | I–IV            |
| 0110/1.89 Table 1, For Rated Mains Voltage | < 300 V <sub>RMS</sub> | I–IV            |
| Climatic Classification                    |                        | 55/100/21       |
| Pollution Degree (DIN VDE 0110/1.89)       |                        | 2               |
| Comparative Tracking Index                 |                        | 175             |

| Symbol                | Parameter  | Value             | Unit              |
|-----------------------|--|-------------------|-------------------|
| V                     | Input-to-Output Test Voltage, Method A, $V_{IORM} \times 1.6 = V_{PR}$ ,<br>Type and Sample Test with $t_m = 10$ s, Partial Discharge < 5 pC           |                   | V <sub>peak</sub> |
| V <sub>PR</sub>       | Input-to-Output Test Voltage, Method B, $V_{IORM} \times 1.875 = V_{PR}$ ,<br>100% Production Test with $t_m = 1 \text{ s}$ , Partial Discharge < 5 pC | 1594              | V <sub>peak</sub> |
| V <sub>IORM</sub>     | Maximum Working Insulation Voltage   | 850               | V <sub>peak</sub> |
| V <sub>IOTM</sub>     | Highest Allowable Over-Voltage   | 6000              | V <sub>peak</sub> |
|                       | External Creepage  | ≥ 7               | mm                |
|                       | External Clearance   | ≥ 7               | mm                |
|                       | External Clearance (for Option TV, 0.4" Lead Spacing)  | ≥ 10              | mm                |
| DTI                   | Distance Through Insulation (Insulation Thickness)   | ≥ 0.5             | mm                |
| Τ <sub>S</sub>        | Case Temperature <sup>(1)</sup>  | 175               | °C                |
| I <sub>S,INPUT</sub>  | Input Current <sup>(1)</sup>   | 350               | mA                |
| P <sub>S,OUTPUT</sub> | Output Power <sup>(1)</sup>  | 800               | mW                |
| R <sub>IO</sub>       | Insulation Resistance at T <sub>S</sub> , $V_{IO}$ = 500 V <sup>(1)</sup>  | > 10 <sup>9</sup> | Ω                 |

Note:

1. Safety limit values - maximum values allowed in the event of a failure.

# **Absolute Maximum Ratings**

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

| Symbol           | Parameter  | Value              | Unit  |  |
|------------------|--|--------------------|-------|--|
| TOTAL DEVIC      | E  |                    |       |  |
| T <sub>STG</sub> | Storage Temperature -40 to +125                        |                    | °C    |  |
| T <sub>OPR</sub> | Operating Temperature                                  | -40 to +100        | °C    |  |
| TJ               | Junction Temperature                                   | -40 to +125        | °C    |  |
| T <sub>SOL</sub> | Lead Solder Temperature                                | 260 for 10 seconds | °C    |  |
|                  | Total Device Power Dissipation @ T <sub>A</sub> = 25°C | 270                | mW    |  |
| PD               | Derate Above 25°C                                      | 2.94               | mW/°C |  |
| EMITTER          |  |                    |       |  |
| I <sub>F</sub>   | DC/Average Forward Input Current 60                    |                    | mA    |  |
| V <sub>R</sub>   | Reverse Input Voltage                                  | 3                  | V     |  |
| Р                | LED Power Dissipation @ $T_A = 25^{\circ}C$            | 120                | mW    |  |
| PD               | Derate Above 25°C                                      | 1.41               | mW/°C |  |
| DETECTOR         |  |                    |       |  |
| ۱ <sub>C</sub>   | Continuous Collector Current                           | 150                | mA    |  |
| V <sub>CEO</sub> | Collector-Emitter Voltage<br>MOC8021M                  | 50                 | V     |  |
|                  | MOC8050M   | 80                 | V     |  |
| P <sub>D</sub>   | Detector Power Dissipation @ $T_A = 25^{\circ}C$       | 150                | mW    |  |
|                  | Derate Above 25°C                                      | 1.76               | mW/°C |  |

# **Electrical Characteristics**

 $T_A$  = 25°C Unless otherwise specified.

#### Individual Component Characteristics

| Symbol            | Parameter                           | Test Conditions                             | Min. | Тур.  | Max. | Unit |
|-------------------|-------------------------------------|---|------|-------|------|------|
| EMITTER           |                                     |   |      |       |      |      |
| V <sub>F</sub>    | Input Forward Voltage               | I <sub>F</sub> = 10 mA                      |      | 1.18  | 2.00 | V    |
| I <sub>R</sub>    | Reverse Leakage Current             | V <sub>R</sub> = 3.0 V                      |      | 0.001 | 10   | μA   |
| DETECTOR          |                                     |   |      |       |      |      |
|                   | Collector-Emitter Breakdown Voltage |   |      |       |      |      |
| BV <sub>CEO</sub> | MOC8021M                            | I <sub>C</sub> = 1.0 mA, I <sub>F</sub> = 0 | 50   | 100   |      | V    |
|                   | MOC8050M                            |   | 80   | 100   |      | V    |
| BV <sub>ECO</sub> | Emitter-Collector Breakdown Voltage | I <sub>E</sub> = 100 μA, I <sub>F</sub> = 0 | 5    | 10    |      | V    |
| I <sub>CEO</sub>  | Collector-Emitter Dark Current      | V <sub>CE</sub> = 60 V, I <sub>F</sub> = 0  |      |       | 1    | μA   |
| C <sub>CE</sub>   | Capacitance                         | V <sub>CE</sub> = 0 V, f = 1 MHz            |      | 8     |      | pF   |

#### **Transfer Characteristics**

| Symbol           | Parameter                                       | Test Conditions   | Min.  | Тур. | Max. | Unit |
|------------------|---|---|-------|------|------|------|
| DC CHARA         | CTERISTICS                                      |   |       |      |      |      |
|                  | Current Transfer Ratio,<br>Collector to Emitter |   |       |      |      |      |
| CTR              | MOC8021M  | $I_{\rm F} = 10 \text{ mA}, V_{\rm CE} = 5 \text{ V}$               | 1,000 |      |      | %    |
|                  | MOC8050M  | I <sub>F</sub> = 10 mA, V <sub>CE</sub> = 1.5 V                     | 500   |      |      | %    |
| AC CHARA         | CTERISTICS                                      |   |       |      | •    |      |
| t <sub>on</sub>  | Turn-on Time                                    | $I_{F} = 5 \text{ mA}, V_{CC} = 10 \text{ V},$ $R_{L} = 100 \Omega$ |       | 8.5  |      | μs   |
| t <sub>off</sub> | Turn-off Time                                   | $I_{F} = 5 \text{ mA}, V_{CC} = 10 \text{ V},$ $R_{L} = 100 \Omega$ |       | 95   |      | μs   |

#### **Isolation Characteristics**

| Symbol           | Characteristic                 | Test Conditions                                    | Min.             | Тур. | Max. | Unit               |
|------------------|--------------------------------|--|------------------|------|------|--------------------|
| V <sub>ISO</sub> | Input-Output Isolation Voltage | t = 1 Minute                                       | 4170             |      |      | VAC <sub>RMS</sub> |
| C <sub>ISO</sub> | Isolation Capacitance          | V <sub>I-O</sub> = 0 V, f = 1 MHz                  |                  | 0.2  |      | pF                 |
| R <sub>ISO</sub> | Isolation Resistance           | V <sub>I-O</sub> = ±500 VDC, T <sub>A</sub> = 25°C | 10 <sup>11</sup> |      |      | Ω                  |




Figure 3. LED Forward Voltage vs. Forward Current




Figure 4. Normalized CTR vs. Forward Current





Figure 5. Normalized CTR vs. Ambient Temperature









Figure 6. Turn-on Time vs. Forward Current



©2000 Fairchild Semiconductor Corporation MOC8021M, MOC8050M Rev. 3.2





## **Ordering Information**

| Part Number  | Package  | Packing Method             |
|--------------|--|----------------------------|
| MOC8021M     | DIP 6-Pin  | Tube (50 Units)            |
| MOC8021SM    | SMT 6-Pin (Lead Bend)                                    | Tube (50 Units)            |
| MOC8021SR2M  | SMT 6-Pin (Lead Bend)                                    | Tape and Reel (1000 Units) |
| MOC8021VM    | DIP 6-Pin, DIN EN/IEC60747-5-5 Option                    | Tube (50 Units)            |
| MOC8021SVM   | SMT 6-Pin (Lead Bend), DIN EN/IEC60747-5-5 Option        | Tube (50 Units)            |
| MOC8021SR2VM | SMT 6-Pin (Lead Bend), DIN EN/IEC60747-5-5 Option        | Tape and Reel (1000 Units) |
| MOC8021TVM   | DIP 6-Pin, 0.4" Lead Spacing, DIN EN/IEC60747-5-5 Option | Tube (50 Units)            |

#### Note:

2. The product orderable part number system listed in this table also applies to the MOC8050M device.

## **Marking Information**




Figure 12. Top Mark

#### Table 1. Top Mark Definitions

| 1 | Fairchild Logo  |
|---|---|
| 2 | Device Number   |
| 3 | DIN EN/IEC60747-5-5 Option (only appears on component ordered with this option) |
| 4 | One-Digit Year Code, e.g., "5"  |
| 5 | Digit Work Week, Ranging from "01" to "53"                                      |
| 6 | Assembly Package Code   |











#### NOTES:

- A) NO STANDARD APPLIES TO THIS PACKAGE.
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSION
- D) DRAWING FILENAME AND REVSION: MKT-N06Drev4



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor: MOC8021SR2M MOC8021M