



# **Product brief**

# XENSIV™ – 3D magnetic sensor family

TLE/TLI/TLV493D for automotive, industrial and consumer markets

Infineon's 3D magnetic sensor family TLE/TLI/TLV493D offers accurate three dimensional sensing with extremely low-power consumption. Within its small package the sensor provides direct measurement of the x-, y-, and z components of a magnetic field.

Thus the sensor family is ideally suited for the measurement of

- > 3 dimensional movement within a magnetic field
- > Linear slide movement
- > 360° angle rotation (end of shaft and out of shaft)
- Joystick movement

The TLE/TLI/TLV493D sensors provide a contactless position sensing alternative to applications which traditionally use mechanical or optical solutions. The system size for these applications can be reduced as magnetic threshold stability over temperature provides a highly accurate and more robust solution for those systems.

TLE493D-W2B6/P2B6 and TLI493D-W2BW are available in 4 different variants ending with A0, A1, A2 or A3. The underlying feature is the so called Bus mode configuration of this device. It's possible to connect up to 4 sensors to one I<sup>2</sup>C bus. The specific addressing is then done via 4 different variants.

Infineon's sensor provides a standard 2-wire digital  $I^2C$  communication interface, which enables a bi-directional communication between the sensor and microcontroller. The sensors keep the highest quality standard and environmental regulations.

## **Key applications**

- > Consumer and industry
  - Joystick e.g. finger, thumb and gaming paddles
  - E-meters e.g. anti-tampering
  - Mobile camera lens position sensing for focus and zoom
  - Control elements e.g. white goods, multifunction knob
- > Automotive
  - Control elements for infotainment/navigation systems, air conditions, multi-functional steering wheels or light switches
  - Top column module, e.g. direction indicator, wiper control
  - Gear stick position sensing

# Key features

- > 3-dimensional magnetic field sensing (Bx, By and Bz)
- > Integrated temperature sensing
- > Low-current consumption
  - 7 nA in power down mode
  - 10  $\mu\text{A}$  in low power operation at 24 Hz
- > 2.8 to 3.5 V operating supply voltage
- Digital output via 2-wire standard
  I<sup>2</sup>C interface
- > Bx, By and Bz linear magnetic field measurement up to ±160 mT
- > 12-bit data resolution for each measurement direction
- > Sensitivity 7.7 to 30.8 LSB12/mT
- > Sample rate 0.05 ... 7.8 kHz
- > TSOP6/WLB-5 package
- Operating temperature range from -40°C to 125°C














# Product summary

Parameter	TLV493D-A1B6	TLV493D-A2BW	TLI493D-A2B6	TLE493D-A2B6	TLE493D-W2B6	TLE493D-P2B6	TLI493D-W2BW	Units
Supply voltage	2.9 to 3.5	2.8 to 3.5	2.8 to 3.5	2.8 to 3.5	2.8 to 3.5	2.8 to 3.5	2.8 to 3.5	V
Typ. supply current – power down	7.0	7.0	7.0	7.0	7.0	7.0	7.0	nA
Typ. supply current – fast mode	3.7	3.4	3.4	3.4	3.4	3.4	3.4	mA
Minimum usable magnetic linear range	±130	±50, ±100 or ±160	±100 or ±160	±100 or ±160	±100 or ±160	±100 or ±160	±50, ±100 or ±160	mT
Magnetic sensitivity	10.2	7.7/15.4/30.8	7.7/15.4	7.7/15.4	7.7/15.4	7.7/15.4	7.7/15.4/30.8	LSB <sub>12</sub> /mT
x to y channel matching drift	±9	±5	±3.5	±3.5	±3.5	±1.9	±3.5	%
x/y to z channel matching drift	±15	±20	±15	±15	±15	±12	±15	%
Temperature range	-40 to 125	-20 to 85	-40 to 105	-40 to 125	-40 to 125	-40 to 125	-40 to 125	°C

Туре	Additional features	Qualification	Packing unit	Ordering code
TLV493D-A1B6	Low power	JESD47	3K pcs	SP001286056
TLI493D-A2B6	Low power	JESD47	3K pcs	SP0001689844
TLI493D-W2BW A0 TLI493D-W2BW A1 TLI493D-W2BW A2 TLI493D-W2BW A3	Pb-free and halogen free package	JESD47	4K pcs	SP005409809 SP005409807 SP005409905 SP005409903
TLI493D-W2BW A0 TLI493D-W2BW A1 TLI493D-W2BW A2 TLI493D-W2BW A3	Pb-free and halogen free package	JESD47	15K pcs	SP005409964 SP005409966 SP005409968 SP005409970
TLE493D-A2B6	Low power	AEC-Q100	3K pcs	SP001689848
TLE493D-W2B6 A0 TLE493D-W2B6 A1 TLE493D-W2B6 A2 TLE493D-W2B6 A3	Low power and wake up function	AEC-Q100/ ISO 26262 ready	3K pcs	SP001605334 SP001605340 SP001605344 SP001605348
TLE493D-P2B6 A0 TLE493D-P2B6 A1 TLE493D-P2B6 A2 TLE493D-P2B6 A3	Low power and wake up function	AEC-Q100/ ISO 26262 ready	3K pcs	SP005557415 SP005557413 SP005557411 SP005557408
TLV493D-A2BW	Pb-free and halogen free package	JESD47	15K pcs	SP005542151

Published by Infineon Technologies AG 81726 Munich, Germany

© 2021 Infineon Technologies AG. All Rights Reserved.

### Please note!

This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

### Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

## Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.