

31782

Broom, 410 mm, Soft/split,  
Green



Designed to effectively sweep flour, starch and other powders from dry areas, this Broom can be used with any Vikan handle. For use in dry areas only.

# Technical Data

<b>Item Number</b>	31782
<b>Visible bristle length</b>	60 mm
<b>Material</b>	Polypropylene Stainless Steel (AISI 304)
<b>Complies with (EC) 1935/2004 on food contact materials<sup>1</sup></b>	Yes
<b>Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice</b>	Yes
<b>FDA compliant raw material (CFR 21)</b>	Yes
<b>Complies with UK 2019 No. 704 on food contact materials</b>	Yes
<b>Meets the REACH Regulation (EC) No. 1907/2006</b>	Yes
<b>Use of phthalates and bisphenol A</b>	No
<b>Is Halal and Kosher compliant</b>	Yes
<b>Box Quantity</b>	10 Pcs.
<b>Quantity per Pallet (80 x 120 x 200 cm)</b>	480 Pcs.
<b>Quantity Per Layer (Pallet)</b>	60 Pcs.
<b>Box Length</b>	420 mm
<b>Box Width</b>	290 mm
<b>Box Height</b>	210 mm
<b>Length/Depth</b>	410 mm
<b>Width</b>	65 mm
<b>Height</b>	130 mm
<b>Net Weight</b>	0,47 kg
<b>Weight bag</b>	0,009 kg
<b>Weight cardboard</b>	0,0162 kg
<b>Tare total</b>	0,0252 kg
<b>Gross Weight</b>	0,5 kg
<b>Cubik metre</b>	0,003465 M3
<b>Max. cleaning temperature (Dishwasher)</b>	85 °C
<b>Max. usage temperature (for food contact)</b>	40 °C
<b>Max usage temperature (non food contact)</b>	60 °C
<b>Min. usage temperature<sup>3</sup></b>	-20 °C
<b>Max. drying temperature</b>	70 °C
<b>Min. pH-value in usage concentration</b>	2 pH
<b>Max. pH-value in Usage Concentration</b>	10,5 pH
<b>GTIN-13 Number</b>	5705020317828
<b>GTIN-14 Number (Box quantity)</b>	15705020317825
<b>Customs Tariff No.</b>	96039099

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact

The product is not compliant with the European Brushware Federation (FEIBP) charter due to the split filaments.

3. Do not store the product below 0° Celsius.