

Specifications	Range	Best Accuracy
Model		UT256B
AC Current (A)	200A	$\pm(2.5\%+5)$
DC Current (A)	200A	$\pm(2.5\%+5)$
AC Voltage(V)	6V/60V/600V/750V	$\pm(1.2\%+3)$
DC Voltage(V)	600mV/6V/60V/600V/1000V	$\pm(0.8\%+3)$
Resistance (Ω)	600 Ω /6k Ω /60k Ω /600k Ω /6M Ω /60M Ω	$\pm(1.0\%+2)$
Capacitance (F)	60nF/600nF/6 μ F/60 μ F/600 μ F/6mF/60mF	$\pm(4\%+20)$
Features		
Display Count		6000
Auto Range		$\sqrt{\quad}$
True RMS		$\sqrt{\quad}$
Diode	Around 3.0V	$\sqrt{\quad}$
NCV		$\sqrt{\quad}$
Data Hold		$\sqrt{\quad}$
Zero Mode		$\sqrt{\quad}$
Relative Mode		$\sqrt{\quad}$
LCD Backlight		$\sqrt{\quad}$
Auto Power Off	Around 15 Minutes	$\sqrt{\quad}$
Continuity Buzzer		$\sqrt{\quad}$
Low Battery Indication	$\leq 2.4V$	$\sqrt{\quad}$
Input Protection		$\sqrt{\quad}$
Input Impedance for DCV	$\geq 10M\Omega$	$\sqrt{\quad}$
General Characteristic		
Power	AAA 1.5V x 2	
LCD Size	36.5mm x 24mm	
Product Color	Red and Grey	
Product Net Weight	163.7g	
Product Size	210mm x 53mm x 35mm	
Standard Accessories	Batteries, Test Lead	
Standard Individual Packing	Gift Box, Carrying Bag, English Manual	
Standard Quantity Per Carton	40PCs	
Standard Carton Measurement	490mm x350 mm x 305mm (0.052 CBM Per Standard Carton)	
Standard Carton Gross Weight	15.2Kg	