

THIS SPECIFICATION COVERS OUR PRODUCT OF DYNAMIC RECEIVER UNIT FOR MOBILE TELEPHONE USE

RECEIVER ELECTROACOUSTIC CHARACTERISTICS

sound pressure level	108±3dB SPL @1KHz (0dB SPL=20μPa)
input voltage	179mV (Sine wave) measured with IEC318 coupler
resonance frequency (FO)	650±20%Hz at 400mVrms Sine Wave
measuring diagram	Shown in Fig.1
earpiece view	Show in Fig.2
typical frequency response	Shown in Fig.3.
curve	
rated noise power	20mW.
short-term max.power	50mW
distortion	<5% @ 1KHz Input 179mV
operation test	Must be free of audible noise (buzzes and rattles)
	(300 ~ 3400Hz frequency range ,input level up to 0.8Vrms)

GENERAL SPECIFICATIONS

ор	erating temperature	-20°C ~ +60°C
ran	nge	
sto	orage temperature range	-20°C ~ +60°C
dc	resistance	28±10%Ω
ЭС	impedance	32±20%Ω
din	mension	15 x 6 x 4.5 mm

TYPICAL FREQUENCY RESPONSE CURVE

FREQUENCY MEASURING CIRCUIT (RECEIVER MODE) (Fig.1)





MODEL: RC-1506S PRODUCT: Dynamic Receiver EDITION: A/2016

TYPICAL FREQUENCY RESPONSE CURVE (Continued)

EARPIECE VIEW (Fig.2)



TYPICAL FREQUENCY RESPONSE CURVE (RECEIVER MODE) (Fig.3)





TEST CLIMATIC CONDITIONS

STANDARD TEST CONDITIONS

temperature	15~35∘C
relative humidity	25%~75%(RH)
air pressure	86~106KPa

RELIABILITY TESTS

The sound pressure as specified shall neither deviate more than ± 3 dB from the initial value, nor have any significant damage after any of following testing.

 HIGH TEMPERATURE TEST	
high temperature	+65±2°C
 duration	96 hours
LOW TEMPERATURE TEST	
 low temperature	-40±2°C
 duration	96 hours
 HEAT SHOCK TEST (See in Fig.4)	
 high temperature	+65±2°C
 low temperature	-40±2°C
changeover time	< 30 seconds
 duration	1 hour
 cycle	10
HUMIDITY TEST	
 temperature	+40±2°C
 relative humidity	90~95%
 duration	2 hours
 TEMPERATURE CYCLE TEST (See in Fig.5)	
 temperature	-40°C +75°C
 duration	45 minutes 45 minutes
temperature gradient	1~3°C/min.
cycle	5
DROP TEST	
mounted with dummy set mass	100 g
 height	1.5 m
cycle	6 (1 each plain) onto the concrete board
LOAD TEST	
noise signal	White noise (EIA filter)
 input power	20mW 0.8Vrms White noise single(White noise with JIS filter) 1 minute, 10 times at intervals
duration	96 hours
 duration	96 hours



MODEL: RC-1506S PRODUCT: Dynamic Receiver EDITION: A/2016



TEST METHOD



PRODUCT EXTERNAL VIEW AND DIMENSIONS (Fig. 6)

Tolerance±0.2 (unit = mm)





MODEL: RC-1506S PRODUCT: Dynamic Receiver EDITION: A/2016

PACKING

-

