

2.7V 360F ULTRACAPACITOR CELL

BCAP0360 P270 S18
ESHSR-0360C0-002R7A1

FEATURES AND BENEFITS

- High performance product with low ESR
- Exceptional shock and vibration resistance
- Long lifetimes with up to 500,000 duty cycles*
- Compliant with UL, RoHS, and REACH requirements

TYPICAL APPLICATIONS

- Wind Turbine Pitch Control
- UPS System
- Actuators
- Emergency Lighting
- Telematics
- Security Equipment
- Backup System



PRODUCT SPECIFICATIONS

ELECTRICAL

Rated Voltage, V_R	2.7 VDC
Surge Voltage ¹	2.85 VDC
Rated Capacitance, C^3	360 F
Min. / Max. Capacitance, Initial	360 F / 432 F
Typical Capacitance, Initial ^{2,3}	375 F
Rated (Max.) ESR_{DC} , Initial ³	3.2 m Ω
Typical ESR_{DC} , Initial ^{2,3}	2.9 m Ω
Typical ESR_{DC} , Initial, 5 sec ^{2,3}	3.4 m Ω
Maximum Leakage Current ⁴	0.75 mA
Maximum Peak Current, Non-repetitive ⁵	220 A

PHYSICAL

Nominal Mass	71.4 g
--------------	--------

POWER & ENERGY

Operating Temp. Range	Standard (-40°C to 65°C) at 2.7V	Extended (-40°C to 85°C) at 2.3V
Maximum Stored Energy, E_{max} ^{6,9}	0.36 Wh	0.26 Wh
Gravimetric Specific Energy ⁶	5.1 Wh/kg	3.7 Wh/kg
Usable Specific Power ⁶	3.8 kW/kg	2.7 kW/kg
Impedance Match Specific Power ⁶	7.9 kW/kg	5.7 kW/kg

SAFETY

Certifications	RoHS, REACH, UL 810A
----------------	----------------------

TYPICAL CHARACTERISTICS

THERMAL CHARACTERISTICS

Typical Thermal Resistance (R_{th} , Housing) ⁸	8.8°C/W
Typical Thermal Capacitance (C_{th})	75.6 J/°C
Usable Continuous Current (BOL) ($\Delta T = 15$ °C) ^{8,10}	23 A
Usable Continuous Current (BOL) ($\Delta T = 40$ °C) ^{8,10}	38 A


LIFE*

Projected DC Life at Room Temperature (At rated voltage and 25°C, EOL ¹⁰)	10 years
DC Life at Standard High Temperature (At rated voltage and 65°C, EOL ¹⁰)	1,500 hours
DC Life at De-Rated Voltage & Higher Temperature (At 2.3V and 85°C, EOL ¹⁰)	1,000 hours
Projected Cycle Life at Room Temperature ⁷ (Constant current charge-discharge from V_R to $1/2V_R$ at 25°C, EOL ¹⁰)	500,000 cycles
Shelf Life (Stored uncharged at 25°C, $\leq 50\%$ RH)	4 years

*Results may vary. Additional terms and conditions, including the limited warranty, apply at the time of purchase. See the warranty details for applicable operating and use requirements.

Datasheet: 2.7V 360F ULTRACAPACITOR CELL

1. **Surge Voltage**
Absolute maximum voltage, non-repetitive. Duration not to exceed 1 second.
2. "Typical" values represent mean values of production sample.
3. **Rated Capacitance & ESR_{DC} (measure method)**
 - Capacitance: Constant current charge (10 mA/F) to V_R, 5 min hold at V_R, constant current discharge 10 mA/F to 0.1V.
e.g. in case of 2.7V 360F cell, 10 * 360 = 3,600 mA.
 - ESR_{DC}: Constant current charge (10 mA/F) to V_R, 5 min hold at V_R, constant current discharge (40 * C * V_R[mA]) to 0.1 V.
e.g. in case of 2.7V 360F cell, charge with 10 * 360 = 3,600 mA and discharge with 40 * 360 * 2.7 = 38,880 mA.



where C is the capacitance (F);
I is the absolute value of the discharge current (A);
V_R is the rated voltage (V);
V₁ is the measurement start voltage, 0.8xV_R (V);
V₂ is the measurement end voltage, 0.4xV_R (V);
t₁ is the time from start of discharge to reach V₁ (s);
t₂ is the time from start of discharge to reach V₂ (s);
ESR_{DC} is the DC-ESR (Ω);
ΔV is the voltage drop during first 10ms of discharge (V).

Typical ESR_{DC}, Initial, 5 sec tested per Maxwell Application Note, "Test Procedures for Capacitance, ESR, Leakage Current and Self-Discharge Characterizations of Ultracapacitors" available at www.maxwell.com.


4. **Maximum Leakage Current**
 - Current measured after 72 hrs at rated voltage and 25°C. Initial leakage current can be higher.
 - If applicable, module leakage current is the sum of cell and balancing circuit leakage currents.
5. **Maximum Peak Current**
 - Current needed to discharge cell/module from rated voltage to half-rated voltage in 1 second.

$$I = \frac{\frac{1}{2}V_R}{\Delta t / C + ESR_{DC}}$$

where Δt is the discharge time (sec); Δt = 1 sec in this case

- The stated maximum peak current should not be used in normal operation and is only provided as a reference value.
6. **Energy & Power (Based on IEC 62391-2)**
 - Maximum Stored Energy, E_{max} (Wh) = $\frac{\frac{1}{2}CV_R^2}{3,600}$
 - Gravimetric Specific Energy (Wh/kg) = $\frac{E_{max}}{mass}$
 - Usable Specific Power (W/kg) = $\frac{0.12V_R^2}{ESR_{DC} \times mass}$
 - Impedance Match Specific Power (W/kg) = $\frac{0.25V_R^2}{ESR_{DC} \times mass}$
 - Presented Power and Energy values are calculated based on Rated Capacitance & Rated (Max.) ESR_{DC}, Initial values.
 7. **Cycle Life Test Profile**
Cycle life varies depending upon application-specific characteristics. Actual results will vary.
 8. **Temperature Rise at Constant Current**
 - $\Delta T = I_{RMS}^2 \times ESR_{DC} \times R_{th}$
 - where ΔT: Temperature rise over ambient (°C)
I_{RMS}: Maximum continuous or RMS current (A)
R_{th}: Thermal resistance, cell to ambient (°C/W)
ESR_{DC}: Rated (Max.) ESR_{DC}(Ω).
(Note: Design should consider EOL ESR_{DC} for application temperature rise evaluation.)
 9. Per United Nations material classification UN3499, all Maxwell ultracapacitors have less than 10 Wh capacity to meet the requirements of Special Provisions 361. Both individual ultracapacitors and modules composed of those ultracapacitors shipped by Maxwell can be transported without being treated as dangerous goods (hazardous materials) under transportation regulations.
 10. **BOL: Beginning of Life, rated initial product performance**
EOL: End of Life criteria.
 - Capacitance: 80% of min. BOL rating
 - ESR_{DC}: 2x max. BOL rating

BCAP0360 P270 S18



RECOMMENDED PCB PATTERN HOLE SIZE : 2.0(±0.1)mm

When ordering, please reference the Maxwell Model Number below.

Maxwell Model Number: BCAP0360 P270 S18
Maxwell Part Number: 133524
Alternate Model Number: ESHSR-0360C0-002R7A1

The information in this document is correct at time of printing and is subject to change without notice. Images are not to scale. Products and related processes may be covered by one or more U.S. or international patents and pending applications. Please see www.maxwell.com/patents for more information.

Maxwell Technologies, Inc.
Global Headquarters
3888 Calle Fortunada
San Diego, CA 92123
USA
Tel: +1 (858) 503-3300
Fax: +1 (858) 503-3301

Maxwell Technologies, GmbH
Leopoldstrasse 244
80807 Munich
Germany
Tel: +49 (0)89 4161403 0
Fax: +49 (0)89 4161403 99

Maxwell Technologies
Shanghai Trading Co., Ltd.
Room 1005, 1006, and 1007
No. 1898, Gonghexin Road,
Jin An District, Shanghai 2000072,
P.R. China
Tel: +86 21 3852 4000
Fax: +86 21 3852 4099

Maxwell Technologies
Korea Co., Ltd.
17, Dongtangiheung-ro
681 Beon-gil, Giheung-gu,
Yongin-si, Gyeonggi-do 17102
Republic of Korea
Tel: +82 31 289 0721
Fax: +82 31 286 6767

MAXWELL TECHNOLOGIES, MAXWELL, MAXWELL CERTIFIED INTEGRATOR, ENABLING ENERGY'S FUTURE, DURABLU, NESSCAP, XP, BOOSTCAP, D CELL and their respective designs and/or logos are either trademarks or registered trademarks of Maxwell Technologies, Inc., and/or its affiliates, and may not be copied, imitated or used, in whole or in part, without the prior written permission Maxwell Technologies, Inc. All contents copyright © 2019 Maxwell Technologies, Inc. All rights reserved. No portion of these materials may be reproduced in any form, or by any means, without prior written permission from Maxwell Technologies, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Maxwell Technologies:](#)

[BCAP0360 P270 S18](#)