

SIMATIC S7-1200, ANALOG INPUT, SM 1231, 4 AI, +/-10V, +/-5V, +/-2.5V, OR 0-20MA/4-20 MA, 12 BIT + SIGN BIT (13 BIT ADC)



Supply voltage	
Rated value (DC)	Yes
<ul style="list-style-type: none"> <li>• 24 V DC</li> </ul>	
Input current	
Current consumption, typ.	45 mA
from backplane bus 5 V DC, typ.	80 mA
Power loss	
Power loss, typ.	1.5 W
Analog inputs	
Number of analog inputs	4; Current or voltage differential inputs
permissible input voltage for current input (destruction limit), max.	$\pm 35$ V
permissible input voltage for voltage input (destruction limit), max.	35 V
permissible input current for voltage input (destruction limit), max.	40 mA
permissible input current for current input (destruction limit), max.	40 mA

Cycle time (all channels) max.	625 $\mu$ s
<b>Input ranges</b>	
• Voltage	Yes; $\pm 10$ V, $\pm 5$ V, $\pm 2.5$ V
• Current	Yes; 4 to 20 mA, 0 to 20 mA
• Thermocouple	No
• Resistance thermometer	No
• Resistance	No
<b>Input ranges (rated values), voltages</b>	
• -10 V to +10 V	Yes
• Input resistance (-10 V to +10 V)	$\geq 9$ MOhm
• -2.5 V to +2.5 V	Yes
• Input resistance (-2.5 V to +2.5 V)	$\geq 9$ MOhm
• -5 V to +5 V	Yes
• Input resistance (-5 V to +5 V)	$\geq 9$ MOhm
<b>Input ranges (rated values), currents</b>	
• 0 to 20 mA	Yes
• Input resistance (0 to 20 mA)	280 $\Omega$
• 4 mA to 20 mA	Yes
• Input resistance (4 mA to 20 mA)	280 $\Omega$
<b>Analog value generation for the inputs</b>	
<b>Integration and conversion time/resolution per channel</b>	
• Resolution with overrange (bit including sign), max.	12 bit; + sign
• Integration time, parameterizable	Yes
• Interference voltage suppression for interference frequency f1 in Hz	40 dB, DC to 60 V for interference frequency 50 / 60 Hz
<b>Smoothing of measured values</b>	
• parameterizable	Yes
• Step: None	Yes
• Step: low	Yes
• Step: Medium	Yes
• Step: High	Yes
<b>Errors/accuracies</b>	
Temperature error (relative to input range), (+/-)	25 $^{\circ}$ C $\pm 0.1\%$ , to 55 $^{\circ}$ C $\pm 0.2\%$ total measurement range
<b>Basic error limit (operational limit at 25 <math>^{\circ}</math>C)</b>	
• Voltage, relative to input range, (+/-)	0.1 %
• Current, relative to input range, (+/-)	0.1 %
<b>Interference voltage suppression for f = n x (f1 +/- 1 %), f1 = interference frequency</b>	
• Common mode voltage, max.	12 V
<b>Interrupts/diagnostics/status information</b>	
Alarms	Yes

Diagnostic functions	Yes
<b>Alarms</b>	
• Diagnostic alarm	Yes
<b>Diagnostic messages</b>	
• Monitoring the supply voltage	Yes
• Wire-break	Yes
<b>Diagnostics indication LED</b>	
• for status of the inputs	Yes
• for maintenance	Yes
<b>Degree and class of protection</b>	
Degree of protection acc. to EN 60529	
• IP20	Yes
<b>Standards, approvals, certificates</b>	
CE mark	Yes
CSA approval	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
Marine approval	Yes
<b>Ambient conditions</b>	
<b>Free fall</b>	
• Fall height, max.	0.3 m; five times, in product package
<b>Ambient temperature during operation</b>	
• min.	-20 °C
• max.	60 °C
• horizontal installation, min.	-20 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-20 °C
• vertical installation, max.	50 °C
<b>Ambient temperature during storage/transportation</b>	
• min.	-40 °C
• max.	70 °C
<b>Air pressure acc. to IEC 60068-2-13</b>	
• Operation, min.	795 hPa
• Operation, max.	1 080 hPa
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa
<b>Relative humidity</b>	
• Operation at 25 °C without condensation, max.	95 %
<b>Pollutant concentrations</b>	
• SO2 at RH < 60% without condensation	SO2: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60% condensation-free

Connection method	
required front connector	Yes
Mechanics/material	
Enclosure material (front)	
• Plastic	Yes
Dimensions	
Width	45 mm
Height	100 mm
Depth	75 mm
Weights	
Weight, approx.	180 g
<b>last modified:</b>	11/28/2017