

# SF-7ES1N8A8LB3 - Cable connector



1605610

<https://www.phoenixcontact.com/us/products/1605610>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, straight long, Screw locking mechanism, M23, number of positions: 4+3+PE, contact connection type: Socket, shielded: yes, degree of protection: IP67, cable diameter range: 9 mm ... 12 mm, number of positions: 8, connection method: Crimp connection, series: SF, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1241942

## Your advantages

- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly
- Flexible use: reliably connect various cable diameters
- Molded designs with preassembled cables on one or both sides

## Commercial data

Item number	1605610
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB32
Product key	ABRBFA
Catalog page	Page 154 (C-2-2019)
GTIN	4046356253956
Weight per piece (including packing)	138.3 g
Weight per piece (excluding packing)	122 g
Customs tariff number	85366990
Country of origin	DE

# SF-7ES1N8A8LB3 - Cable connector



1605610

<https://www.phoenixcontact.com/us/products/1605610>

## Technical data

### Notes

General	Order crimp contacts 4 x Ø 1 mm, 4 x Ø 2 mm separately
Safety note	<p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none"><li>• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.</li><li>• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.</li><li>• The products are suitable for applications in plant, controller, and electrical device engineering.</li><li>• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.</li><li>• Assembled products may not be manipulated or improperly opened.</li><li>• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a>).</li><li>• When using the product in direct connection with third-party manufacturers, the user is responsible.</li><li>• For operating voltages &gt; 50 V AC, conductive connector housings must be grounded</li><li>• Ensure that the protective or functional ground has been properly connected.</li><li>• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector</li><li>• Only use tools recommended by Phoenix Contact</li><li>• The installation notes/Design In documents online on the download page at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> must be observed for this product.</li><li>• Operate the connector only when it is fully plugged in and interlocked.</li><li>• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.</li><li>• Observe the minimum bending radius of the cable. Lay the cable without twisting it.</li><li>• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting</li></ul>

# SF-7ES1N8A8LB3 - Cable connector



1605610

<https://www.phoenixcontact.com/us/products/1605610>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

## Mounting

Connection method	Crimp connection
-------------------	------------------

## Product properties

Product type	Circular connector (cable-side)
Number of positions	8
Connection profile	4+3+PE
Application	Power
Series	SF
Shielded	yes
Coding	N
Thread type	M23

## Material specifications

Seal material	FPM
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 6.6
Gasket and O-ring material	FPM
Housing material	Metal

## Connection data

### Conductor connection

Connection method	Crimp connection
-------------------	------------------

## Electrical properties

### Contact

Contact diameter	2 mm
Max. current	30 A
Nominal voltage $U_N$	630 V
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	6 kV

### Contact

Contact diameter	1 mm
Max. current	9 A
Nominal voltage $U_N$	250 V
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	4 kV

## Connector

# SF-7ES1N8A8LB3 - Cable connector



1605610

<https://www.phoenixcontact.com/us/products/1605610>

Type	straight long
------	---------------

## Connection 1

Head design	Socket
-------------	--------

## Cable/line

External cable diameter	9 mm ... 12 mm
-------------------------	----------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	3000 m

# SF-7ES1N8A8LB3 - Cable connector




1605610

<https://www.phoenixcontact.com/us/products/1605610>


## Drawings

Diagram



I = current strength, T = ambient temperature

Schematic diagram



Connector pin assignment


# SF-7ES1N8A8LB3 - Cable connector



1605610

<https://www.phoenixcontact.com/us/products/1605610>

Dimensional drawing



Dimensional drawing

# SF-7ES1N8A8LB3 - Cable connector





1605610

<https://www.phoenixcontact.com/us/products/1605610>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1605610>

 <b>cUL Recognized</b> Approval ID: E153698-20041116				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	600 V	18 A	- 12	-

 <b>UL Recognized</b> Approval ID: E153698-20041116				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	600 V	27 A	- 12	-

<b>cULus Recognized</b>				
-------------------------	--	--	--	--

# SF-7ES1N8A8LB3 - Cable connector



1605610

<https://www.phoenixcontact.com/us/products/1605610>

## Classifications

### ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------



# SF-7ES1N8A8LB3 - Cable connector



1605610

<https://www.phoenixcontact.com/us/products/1605610>

## Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

# SF-7ES1N8A8LB3 - Cable connector

1605610

<https://www.phoenixcontact.com/us/products/1605610>



## Accessories

### SF-7PS2000 - Crimp contact

1605636

<https://www.phoenixcontact.com/us/products/1605636>



Crimp contact, Socket, turned, Single contact, contact diameter: 2 mm, crimp range: 0.25 mm<sup>2</sup> ... 1 mm<sup>2</sup>, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1241952

---

### SF-7NS2000 - Crimp contact

1605631

<https://www.phoenixcontact.com/us/products/1605631>



Crimp contact, Socket, turned, Single contact, contact diameter: 2 mm, crimp range: 0.75 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1237431

## SF-7ES1N8A8LB3 - Cable connector

1605610

<https://www.phoenixcontact.com/us/products/1605610>



### SF-7QS2000 - Crimp contact

1605643

<https://www.phoenixcontact.com/us/products/1605643>



Crimp contact, Socket, turned, Single contact, contact diameter: 2 mm, crimp range: 1 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1237431

---

### SF-7MS2000 - Crimp contact

1605628

<https://www.phoenixcontact.com/us/products/1605628>



Crimp contact, Socket, turned, Single contact, contact diameter: 2 mm, crimp range: 4 mm<sup>2</sup> ... 4 mm<sup>2</sup>, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1241949

## SF-7ES1N8A8LB3 - Cable connector

1605610

<https://www.phoenixcontact.com/us/products/1605610>



### SF-6CS2000 - Crimp contact

1605562

<https://www.phoenixcontact.com/us/products/1605562>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.06 mm<sup>2</sup> ... 0.25 mm<sup>2</sup>, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1241922

---

### SF-10KS004 - Crimp contact

1607356

<https://www.phoenixcontact.com/us/products/1607356>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.14 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1241922

## SF-7ES1N8A8LB3 - Cable connector

1605610

<https://www.phoenixcontact.com/us/products/1605610>



### SF-6AS2000 - Crimp contact

1605557

<https://www.phoenixcontact.com/us/products/1605557>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.25 mm<sup>2</sup> ... 1 mm<sup>2</sup>, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1241922

---

### SF-6FS2000 - Crimp contact

1605566

<https://www.phoenixcontact.com/us/products/1605566>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.5 mm<sup>2</sup> ... 1 mm<sup>2</sup>, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1241923

## SF-7ES1N8A8LB3 - Cable connector

1605610

<https://www.phoenixcontact.com/us/products/1605610>



## SC-Z2322 - Metal protective cap

1605459

<https://www.phoenixcontact.com/us/products/1605459>

Metal dust protection cap with steel wire for power plugs with M23 knurled nuts



---

## SF-Z0064 - Color coding

1620585

<https://www.phoenixcontact.com/us/products/1620585>

Color coding, color: green



# SF-7ES1N8A8LB3 - Cable connector

1605610

<https://www.phoenixcontact.com/us/products/1605610>



## SF-Z0065 - Color coding

1620586

<https://www.phoenixcontact.com/us/products/1620586>

Color coding, color: orange



---

## SF-Z0066 - Color coding

1620587

<https://www.phoenixcontact.com/us/products/1620587>

Color coding, color: black



## SF-7ES1N8A8LB3 - Cable connector

1605610

<https://www.phoenixcontact.com/us/products/1605610>



## SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/us/products/1607456>

Torque screwdriver, series: RC



---

## SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/us/products/1607455>

Hook wrench, series: RC





# SF-7ES1N8A8LB3 - Cable connector

1605610

<https://www.phoenixcontact.com/us/products/1605610>



## SF-Z0068 - Square mounting flange

1620927

<https://www.phoenixcontact.com/us/products/1620927>



Square mounting flange, 4xM3, flange dimensions: 38 mm x 38 mm, series: SF, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1244326

---

## PROT-M23-PW-IT-IP20 - Plastic protective cap

1577207

<https://www.phoenixcontact.com/us/products/1577207>



Plastic protective cap, M23, degree of protection: IP20, series: SF

---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)