

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050842022

Status:

Active

Overview:

Description:

2.13mm Diameter MLX Pin and Socket Receptacle, 2 Circuits, Natural

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	42022
Application	Power, Wire-to-Wire
Comments	Glow Wire Equivalent Part Number 366440002. Current – Maximum per contact 20A if used with 36663 and 36664 terminal
Overview	mlx
Product Name	MLX
UPC	800754386364
Physical	
Circuits (maximum)	2
Circuits Detail	2
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.346/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	Yes
Pitch - Mating Interface	6.35mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +105°C
Electrical	
Current - Maximum per Contact	20.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	42022-2C
Reference - Drawing Numbers	
Packaging Specification	PK-42022-XX-001
Product Specification	PS-42022-0001-001
Sales Drawing	SD-42022-XX, SD-42022-XX-001
Test Summary	TS-42022-0001-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42022 Series

Mates With

42021 MLX Power Crimp Housing Plug

Use With

MLX Crimp Terminal 42023 , 42024

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

50-84-2022