

EER Cores (9598424402)



Part Number: 9598424402

98 EER CORE SET

EER cores, similar to ETD cores, have been designed to make optimum use of a given volume of ferrite material for maximum throughput power. The structure, which includes a round center post, approaches a nearly uniform cross-sectional area throughout the core and provides a winding area that minimizes winding losses.

EER cores can be supplied with the center post gapped to a mechanical dimension or an A_L value.

Weight indicated is per pair or set.

Weight: 96 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	42	± 0.70	1.654	—
B	22	± 0.20	0.866	—
C	15.2	± 0.35	0.598	—
D	15.4	± 0.20	0.606	—
E	30.5	min	1.201	min
F	15.2	± 0.35	0.598	—





Chart Legend

$\Sigma l / A$: Core Constant, l_e : Effective Path Length, A_e : Effective Cross- Sectional Area, V_e : Effective Core Volume

A_L : Inductance Factor 

Explanation of Part Numbers: Digits 1 & 2 = product class and 3 & 4 = material grade.

Electrical Properties	
A_L (nH)	4100 ±25%
A_e (cm ²)	1.87
$\Sigma l / A$ (cm ⁻¹)	5.2
l_e (cm)	9.79
V_e (cm ³)	18.26
A_{min} (cm ²)	1.81

A_L value is measured at 1 kHz, B < 10 gauss.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fair-Rite:](#)

[9598424402](#)