


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348976242](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Unsealed Header, Right-Angle, SMT, Dual Row, 24 Circuits, Gold (Au) Plating, Polarization Option C, Dark Gray, Tape and Reel

Documents:

Drawing (PDF)	Packaging Specification PK-31301-786-001 (PDF)
Product Specification PS-34791-020-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34791-020-001 (PDF)	Product Literature (PDF)



Series image - Reference only

General

Product Family	PCB Headers
Series	34897
Application	Automotive, Power, Signal, Wire-to-Board
Overview	Mini50 Connection Systems
Product Name	Mini50
UPC	889056568395

Physical

Breakaway	No
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Gray (Dark)
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	3.649/g
Number of Rows	2
Orientation	Right Angle
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	500V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-34791-020-001
Packaging Specification	PK-31301-786-001
Product Specification	PS-34791-020-001
Sales Drawing	SD-34897-001-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
benzo[ghi]perylene
tricosafuorododecanoic
acid
Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-
pen
heptacosafuorotetradecanoic
acid
dodecamethylcyclhexasiloxane
decamethylcyclopentasiloxane
benzene-1,2,4-
tricarboxylic acid 1,2-
anhydride
octamethylcyclotetrasiloxane
disodium 3,3'-[[1,1'-
biphenyl]-4,4'-
diylbis(azo)
diisopentylphthalate
methoxyacetic acid
1,2-diethoxyethane
dibutyltin dichloride
2-methylimidazole
4,4'-methylenedi-o-
toluidine
1-vinylimidazole
1,3-propanesultone
chromium trioxide
disodium 4-
amino-3-[[4'-[(2,4-
diaminophenyl)azo]
henicosafuoroundecanoic
acid
Ammonium-
pentadecafluorooctanoate
sodium
peroxometaborate

China RoHS

Disodium-octaborate
di-n-pentyl phthalate
(DPP)
4-aminoazobenzene
diethyl sulphate
propylene oxide
dimethyl sulphate
N-methylacetamide
p-(1,1-
dimethylpropyl)phenol
dicyclohexyl phthalate
dihexyl phthalate
(DnHP)
phenanthrene
dinoseb (ISO)
butyl 4-
hydroxybenzoate
o-toluidine
4-methyl-m-
phenylenediamine
ethylene thiourea
4-o-tolylazo-o-
toluidine
4-tert-butylphenol
nitrobenzene
1-bromopropane
ethylenediamine
furan
2-methoxyethyl
acetate
6-methoxy-m-toluidine
C,C'-
azodi(formamide)
1,7,7-trimethyl-3-
(phenylmethylene)bicyclo[2.2.1
4-Nonylphenol,
branched and linear,
ethoxylated
4-Heptylphenol,
branched and linear
Nonadecafluorodecanoic
acid (PFDA) and its
sodiu
2,3,3,3-tetrafluoro-2-
(heptafluoropropoxy)propio
Tris(4-nonylphenyl,
branched and linear)
phosphi
Perfluorobutane
sulfonic acid (PFBS)
and its sal
Fluoranthene
Pyrene
Benz[a]anthracene
Cadmium nitrate
Chrysene
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Reaction
products of 1,3,4-
thiadiazolidine-2,5-d
Perfluorononan-1-
oic acid
(2,2,3,3,4,4,5,5,6,6,7

4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated
hexahydro-2-benzofuran-1,3-dione
Methylhexahydrophthalic anhydride
Sodium perborate; perboric acid, sodium salt
Cadmium sulphate
reaction mass of
2-ethylhexyl 10-ethyl-4,4-dioctyl-1,2-benzenedicarboxylic acid, di-C6-10-alkyl est
5-sec-butyl-2-(2,4-dimethylcyclohex-3-en-1-yl)-5
Perfluorohexane-1-sulphonic acid and its salts
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated
2-ethylhexyl 10-ethyl-4,4-dioctyl-7-oxo-8-oxa-3, dibutylbis(pentane-2,4-dionato-O,O')tin
2-(2H-benzotriazol-2-yl)-4,6-ditertpentylphenol
Terphenyl, hydrogenated
1,2-Benzenedicarboxylic acid, dihexyl ester, bra
diisohexyl phthalate
pentacosafuorotridecanoic acid
1,2-benzenedicarboxylic acid, dipentylester, bra
2-methyl-1-(4-methylthiophenyl)-2-morpholinoprop
4,4-isobutylethylidenediphenol
2-benzyl-2-dimethylamino-4-morpholinobutyropheno
3-ethyl-2-methyl-2-(3-methylbutyl)-1,3-oxazolidi
n-pentyl-isopentylphthalate
1,3-BENZENEDIOL, TRINITRO-, LEAD SALT
Hydrazine

Disodium tetraborate
Boric acid
4,4'-Oxydianiline and
its salts
Aluminosilicate
Refractory Ceramic
Fibres
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
Acids generated from
chromium trioxide and
their
4-Nonylphenol,
branched and linear
[substances w
Trixylyl phosphate
2-ethoxyethanol
Carbonic acid,
cobalt(2+) salt (1:1)
Acetic acid, cobalt(2+)
salt
Cobalt-dinitrate
Cobalt sulphate
2-ethoxyethyl acetate
Strontium-chromate
1,2-
benzenedicarboxylic
acid; di-C7-11-
branched
N-methyl-2-
pyrrolidone
1,2,3-trichloropropane
1,2-
benzenedicarboxylic
acid; di-C6-8-
branched a
Calcium-arsenate
bis(2-methoxyethyl)
ether
potassium
hydroxyoctaoxidizincatedichromate(1-)
lead dipicrate
N,N-
dimethylacetamide
arsenic acid
2-methoxyaniline
trilead diarsenate
1,2-dichloroethane
pentazinc chromate
octahydroxide
Formaldehyde,
polymer with
benzenamine
bis(2-methoxyethyl)
phthalate
trichloroethylene
triethyl arsenate
4,4'-
diaminodiphenylmethane
dibutyl phthalate
(DBP)
bis(2-ethylhexyl)
phthalate (DEHP)

lead hydrogen
arsenate
Butylbenzylphthalate
(BBP)
2,4-dinitrotoluene
Anthracene oil;
Anthracene oil
Anthracene oil,
anthracene paste;
Anthracene Oil
Anthracene oil,
anthracene paste,
anthracene fra
Anthracene oil,
anthracene paste,
distn. lights;
Anthracene oil,
anthracene-low;
Anthracene Oil F
diisobutyl phthalate
(DIBP)
lead chromate
Lead chromate
molybdate sulfate red
Lead sulfochromate
yellow
Pitch, coal tar, high-
temp.; Pitch
Tris(2-chloroethyl)
phosphate
ammonium
dichromate
potassium chromate
potassium dichromate
sodium chromate
Boric acid, disodium
salt, hydrate
lead diazide
cadmium
Cadmium-fluoride
pyrochlore, antimony
lead yellow
lead dinitrate
cadmium chloride
Silicic acid, lead salt
lead oxide sulfate
Lead-titanium-trioxide
pentalead tetraoxide
sulphate
Trilead-dioxide-
phosphonate
tetralead trioxide
sulphate
dioxobis(stearato)trilead
Lead titanium
zirconium oxide
Borate(1-),
tetrafluoro-, lead (2+)
lead cyanamidate
cadmium hydroxide
Acetic acid, lead salt,
basic
Sulfurous acid, lead
salt, dibasic

Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
[phthalato(2-)]dioxotrilead
Fatty acids, C16-18,
lead salts
lead(II)
methanesulphonate
1,3,5-tris-[(2S
and 2R)-2,3-
epoxypropyl]-1,3,5-t
lead
phenolphthalein
dichromium
tris(chromate)
2,2'-dichloro-4,4'-
methylenedianiline
formamide
tetraethyllead
4,4'-
bis(dimethylamino)benzophenone
N,N,N',N'-
tetramethyl-4,4'-
methyldianiline
1,2-dimethoxyethane
1,2-bis(2-
methoxyethoxy)ethane
lead di(acetate)
cadmium carbonate
[4-[4,4'-
bis(dimethylamino)
benzhydrylidene]cycl
4,4'-
bis(dimethylamino)-4''-
(methylamino)trityl
bis(pentabromophenyl)
ether
Diboron-trioxide
cadmium oxide (non-
pyrophoric)
cadmium sulphide
orange lead
trilead bis(carbonate)
dihydroxide
Lead oxide
1,3,5-
tris(oxiranylmethyl)-1,3,5-
triazine-2,4,6(
[4-[[4-anilino-1-
naphthyl]]4-
(dimethylamino)phen
α,α#Bis[4-
(dimethylamino)phenyl]-4
(phenylamino)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34897 Series

Mates With

34824 Mini50 Unsealed Dual Row
Receptacle

This document was generated on 11/30/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34897-6242](#)