

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0026605020](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 396 Header, Right-Angle with Friction Lock, 2 Circuits, Tin (Sn) Plating

Documents:

3D Model	Packaging Specification PK-41792-002-001 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-26-60-5020 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-08-50-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General


Product Family	PCB Headers
Series	41792
Application	Power, Wire-to-Board
Comments	Glow Wire Equivalent Part Number 417922000
Overview	KK Interconnect Solutions
Product Name	KK 396
UPC	800753684102

Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	0.946/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.96mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	3.96mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	Yes
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	7.0A
-------------------------------	------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
January 20

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[41792](#) Series

Mates With

[2139](#) KK Crimp Housing, [41695](#) KK Crimp Housing, [6442](#) KK Crimp Housing, [2145](#) PCB Connector, [41815](#) PCB Connector, [3069](#) KK Crimp Housing

Voltage - Maximum 250V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-free Process Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 235

Material Info

Engineering Number 41792-0002

Reference - Drawing Numbers

Packaging Specification PK-41792-002-001
Product Specification PS-08-50-001
Sales Drawing SDA-41792-000
Symbol/Footprint Data SYM-26-60-5020

This document was generated on 02/15/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[26-60-5020](#)