3M Electrical Markets Division

3M[™] Cold Shrink Insulators and Cable Accessories for up to 1000 Volts


Quick & Reliable Low Voltage Insulation



3M[™] Cold Shrink Low Voltage Insulators and Cable Accessories

3M Cold Shrink insulators and accessories offer a safe, easy to install method of insulating, sealing and protecting connectors, hoses, fittings, conduit and cable. They are well suited for in-field applications because they require no special tools or heat to install.

The unique 3M cold shrink delivery system ensures consistent installation and long term reliability. With 3M cold shrink insulators and accessories you get a water resistant seal without heat, torches or adhesive; simply unwind the core to install. It's that simple.



Why move to 3M Cold Shrink Technology?

- No flame required
- Less chance of damaging cable material
- No cooling time needed before energising
- Constant radial pressure for optimised environmental performance
- Easier to use in enclosed areas
- No special site permits needed
- Fast, straightforward installation

3M[™] Cold Shrink End Caps EC-Series

3M cold shrink End Caps EC-Series are close-ended, tubular rubber sleeves that are factory expanded and loaded onto a removable core. When positioned over the end of a cable or other cylindrical object, the core is removed to provide a reliable environmental seal. Four different end caps are available to accommodate a wide range of sizes. They are easily installed and can be removed cleanly.

Applications

Environmentally seal and mechanically protect exposed cable ends using no tools, mastics or tapes

Protect cables and pipes from exposure to moisture, contamination, corrosion, ozone, ultra-violet radiation and other environmental hazards



Product				3M Order Code			Colour			Cable Diameter	
EC-1				XA003895001			Black			12 - 21 mm	
EC-2	EC-2			XA003895019			Black			16 - 30 mm	
EC-3	EC-3			XA003895027			Black			26 - 49 mm	
EC-4				XA003895035			Black			46 - 84 mm	
Cable Diameter (mm)											
	0	10	20	30	40	50	60	70	80	90	100
EC-1	1	 12	- 21	I	1	1	ľ	1	I	I	1
EC-2			16 - 30	·							
EC-3				 	26 – 49						
EC-4							46 -	84		I	

3M[™] Cold Shrink Connector Insulators 8420 and 8430 Series

3M cold shrink Connector Insulators 8420 and 8430 Series are designed using 3M's unique cold shrink delivery system. Products are supplied pre-stretched on a removable core for efficiency and ease of installation. Removal of the core (unwinding) after positioning the joint allows the product to shrink into position forming a moisture-tight seal. The live memory action of the specially formulated EPDM material promotes a permanent and durable environmental seal, and insulation, with a typical operating temperature range from -40°C to 90°C.

Important: Use cable insulation/jacket diameters and connector outer diameter for final sizing confirmation.

Applications

Primary electrical insulation for all solid dielectric (rubber and plastic) insulated wire and cable jointing rated to 1000 V

Good for repairs and environmental sealing for communication and other non-electrical applications



Product	3M Order Code	Typical Cable Size	Minimum Cable Diameter for Seal	Maximum Diameter (Cable or Connector)	Maximum Connector Length	Relaxed Tube Length
8423-6	80610839484	14 - 16 mm²	7.8 mm	14 mm	51 mm	152 mm
8424-8	80610921928	6 - 50 mm²	2.5 mm	21 mm	76 mm	203 mm
8425-8	80610921936	35 - 50 mm²	10 mm	21 mm	76 mm	203 mm
8426-9	80610927669	70 - 125 mm²	14 mm	30 mm	127 mm	229 mm
8426-11	80610927677	70 - 125 mm²	14 mm	30 mm	178 mm	279 mm
8427-6*	80610456164	-	17 mm	35 mm	51 mm	152 mm
8427-12	80610134035	125 - 200 mm²	17 mm	35 mm	203 mm	305 mm
8427-16	80610134043	125 - 200 mm ²	17 mm	35 mm	305 mm	406 mm
8428-6*	80610456172	-	24 mm	49 mm	51 mm	152 mm
8428-8	80611230212	300 - 400 mm ²	24 mm	49 mm	76 mm	203 mm
8428-12	80610154603	300 - 400 mm ²	24 mm	49 mm	203 mm	305 mm
8428-18	80610134050	300 - 400 mm ²	24 mm	49 mm	356 mm	457 mm
8429-6*	80610456180	-	32 mm	68 mm	51 mm	152 mm
8429-9	80610456313	500 mm ²	32 mm	68 mm	127 mm	229 mm
8429-12	80610921910	500 mm ²	32 mm	68 mm	203 mm	305 mm
8429-15	80610970446	500 mm ²	32 mm	68 mm	280 mm	381 mm
8429-18	80610134068	500 mm ²	32 mm	68 mm	356 mm	457 mm
8430-9*	80610839492	630 - 1000 mm ²	43 mm	94 mm	127 mm	229 mm
8430-18	80610921902	630 - 1000 mm²	43 mm	94 mm	356 mm	457 mm

Note: Insulation, connector and/or jacket can be overwrapped with Scotch® Rubber Mastic Tape 2228 to build up diameter if required.

* These sizes are not designed to be used as primary insulation. These shorter length tubes are for conduit sealing and breakouts

8424-8 contains range-extending adaptors

For 8420 and 8430 Series cold shrink tubes continuously exposed to high levels of UV radiation, 3M recommends overwrapping with Scotch[®] Super 33+[™] Vinyl Electrical Tape or Scotch[®] Self Fusing Silicone Rubber Tape 70. Other sizes of cold shrink tubes are available on request – please contact 3M.

These kits are suitable for indoor and outdoor installations, including direct burial, aerial and submersible applications. For use with three core armoured cable up to 1000 V. Connectors are not included, pre-insulated crimp connectors preferred.

3M[™] Low Voltage Inline Joint Kits 5732-5735 Series

3M Order Code

80610981740

57338061098175770 - 120 mm²29 - 84 mm573480610981765120 - 240 mm²39 - 102 mm573580610981773240 - 400 mm²39 - 102 mm

Cable Size

35 - 50 mm²

Note: If increased structural integrity is required, the joint can be overwrapped with two-half lapped layers of 3M[™] Armorcast Structural Material (purchased separately). For 3 metre long rolls, use the following number of rolls per kit: 5732 (2 rolls), 5733 & 5734 (3 rolls) and 5735 (5 rolls).

3M[™] Cold Shrink Cable Abandonment Kits CSCAK Series

3M cold shrink Cable Abandonment Kits are a complete solution to abandon low voltage polymeric cables either temporarily or permanently. Environmental sealing and mechanical protection is provided using 3M cold shrink technology, eliminating the need for heat and special tools, making a quick, simple and reliable installation.

Kit Contents

Product

5732

• Cold shrink end cap

Cold shrink tube

- Armour/earth connection components
- Full installation instructions
- Self-amalgamating insulating tape

Applications

Single and multi core low voltage polymeric power cables up to and including 1.9/3.3 kV (with or without lead sheath and/or armour)

Product	3M Order Code	Cable Diameter
CSCAK/1	TE100048780	12 - 18 mm
CSCAK/2	TE100048798	18 - 25 mm
CSCAK/3	TE100048806	25 - 42 mm
CSCAK/4	TE100048814	42 - 55 mm
CSCAK/5	TE100048822	56 - 81 mm

Medium voltage (up to 33 kV) joints and terminations using cold shrink technology are available from 3M. Please contact your 3M representative for details.



3M Australia & New Zealand

Electrical Markets Division

Building A, 1 Rivett Road	94 Apollo Drive, Albany
North Ryde NSW 2113	Auckland, New Zealand
Australia	Phone: 0800 474 787
Phone: 136 136	Fax: 0800 508 980
3MsafetyAUCS@mmm.com	3MNZITB@mmm.com

www.3M.com.au

3M is a trademark of the 3M Company. © 3M 2013 All Rights Reserved. Please recycle.

www.3M.co.nz

Important Notice

The information may not be valid for any use not referred to in this document or use of the product in combination with other materials. For these reasons, it is important that customers carry out their own test to satisfy themselves as to the suitability of the product for their own intended applications.

Disclaimer

The information on this Document is based on our experience and is correct to the best of our knowledge at the date of publication, but we do not accept any liability for any loss or damage arising from this 3M product, whether, indirect, special, incidental or consequential regardless of the legal theory asserted (except as required by law).

Product Source/Origin: The 3M supply location does not necessarily represent the Country of Origin for the product. If you require 3M product Country of Origin information, contact your 3M Customer Service Representative for assistance.





Cable Diameter

24 - 61 mm