

T350, Tantalum, MnO2 Tantalum, Commercial Grade, 22 uF, 10%, 6.3 VDC, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 2.54mm



| General Information | |
|---------------------|---|
| Supplier: | KEMET |
| Series: | T350 |
| Dielectric: | MnO2 Tantalum |
| Style: | Radial |
| Description: | Radial, Solid Tantalum, Conformal, Dipped |
| Features: | Low Leakage |
| RoHS: | Yes |
| Termination: | Tin |
| Notes: | Longest Lead Is Positive |

| Dimensions | |
|------------|------------------|
| D | 5mm |
| H | 8.6mm |
| S | 2.54mm +/-0.38mm |
| LL | 12.7mm +/-1.26mm |
| F | 0.5mm +/-0.05mm |

| Specifications | |
|------------------------|---|
| Capacitance: | 22 uF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 6.3 VDC (85C), 4 VDC (125C), 0.063 VDC (125C Reverse) |
| Temperature Range: | -55/+125C |
| Dissipation Factor: | 6.00% |
| Leakage Current: | 1.1 uA |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging: | Bulk, Bag |
| Packaging Quantity: | 1000 |