

	ITEM ①	ITEM ②	ITEM ③	ITEM 4	ITEM (5)	ITEM 6	ITEM ⑦
PART NUMBER	BODY	CONTACT	INTERFACE	INSULATOR	INSULATOR	CRIMP SLEEVE	END CAP
133-9402-101	COPPER ALLOY GOLD PL .00005 MIN OVER COPPER PL .00005 MIN	COPPER ALLOY GOLD PL .00005 MIN OVER COPPER PL .00005 MIN	COPPER ALLOY GOLD PL .00005 MIN OVER COPPER PL .00005 MIN	TEFLON	TEFLON	COPPER ALLOY GOLD PL .00005 MIN OVER COPPER PL .00005 MIN	COPPER ALLOY GOLD PL .00005 MIN OVER COPPER PL .00005 MIN



DRAWING NO.



NOTES:

1. SPECIFICATIONS:

IMPEDANCE: 50 OHMS

WORKING VOLTAGE: 250 VRMS MAX AT SEA LEVEL DIELECTRIC WITHSTANDING VOLTAGE: 750 VRMS MIN AT SEA LEVEL INSULATION RESISTANCE: 10000 MEGOHM MIN CONTACT RESISTANCE:

CENTER CONTACT - INITIAL 5 MILLIOHM MAX, AFTER ENVIRONMENTAL 15 MILLIOHM MAX

OUTER CONDUCTOR - GOLD PLATED INITIAL 1 MILLIOHM MAX, AFTER ENVIRONMENTAL 1.5 MILLIOHM MAX

NICKEL PLATED INITIAL 2.5 MILLIOHM MAX, AFTER ENVIRONMENTAL 3.5 MILLIOHM MAX
BODY TO CABLE - GOLD PLATED INITIAL 1 MILLIOHM MAX, AFTER

ENVIRONMENTAL NOT APPLICABLE

NICKEL PLATED INITIAL 2.5 MILLIOHM MAX, AFTER ENVIRONMENTAL NOT APPLICABLE

CORONA LEVEL: 250 VOLTS MINIMUM AT 70,000 FEET

INSERTION LOSS: .2 DB MAX AT 1 GHz

RF LEAKAGE: -70 DB AT 2.5 GHz RF HIGH POTENTIAL WITHSTANDING VOLTAGE: 500 VRMS AT 4 AND 7 MHz

MECHANICAL:


ENGAGE/DISENGAGE FORCE: 5.6 LBS MAX ENGAGEMENT 1.0/8.0 LBS MIN/MAX DISENGAGEMENT CONTACT RETENTION FORCE: 2.3 LBS MIN AXIAL FORCE CONTACT RETENTION TORQUE: NOT APPLICABLE COUPLING MECHANISM RETENTION: NOT APPLICABLE CABLE ACCEPTABILITY: RG 178, RG 196

CABLE HEX CRIMP SIZE: .105
CABLE RETENTION: 10 LBS MIN AXIAL FORCE
DURABILITY: 500 CYCLES MIN

ENVIRONMENTAL:

(MEETS OR EXCEEDS THE APPLICABLE PARAGRAPH OF MIL-PRF-39012) THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION F OPERATING TEMPERATURE: -65 DEG C TO 165 DEG C CORROSION: MIL-STD-202, METHOD 101, CONDITION B SHOCK: MIL-STD-202, METHOD 213, CONDITION B VIBRATION: MIL-STD-202, METHOD 204, CONDITION B MOISTURE RESISTANCE: MIL-STD-202, METHOD 106

2. CONNECTOR MARKED "NM" FOR NON-MAGNETIC



CABLE STRIP DIMENSIONS

4:1

CUSTOMER DRAWING

THIS DRAWING TO BE INTERPRETED PER ASME Y 14.5M - 1994

'μSTATION'

COMPANY CONFIDENTIAL

				COMPANI CONTIDENTIAL
TOLERANCE UNLESS OTHERWISE SPECIFIED		drawn by RJB	DATE 2-5-08	Cinch Connectivity Solutions P.O. Box 1732 Waseca, MN 56093
DECIMALS m	ım ——	CHECKED BY	DATE	a bel group 1-800-247-8256
.XXX — —	.XXX ———		2-6-08 DATE	TITLE PLUG ASSEMBLY,
MATL		APPROVED BY TJS	2-6-08	RIGHT ANGLE CABLÉD, NON-MAGNETIC MCX, RG 178
FINISH		RELEASE DATE 2-6-08		SHEET DRAWING NO.
		U/M INCH	SCALE 10:1	2 OF 2 (- 133-9402-101/110

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cinch Connectivity Solutions: 133-9402-101