


**DESCRIPTION**

The UM7000 and UM7100 series offer moderately high power handling in combination with reasonably low levels of both series resistance and capacitance. The UM7200 series offers the lowest series resistance, but the highest capacitance of the group. The differences in specified performance for each of the series, results from different I-region thickness. The three series have broad applicability in many RF and microwave switch and attenuator circuits. Additionally, the UM7100 in leaded versions is usually the most cost-effective diode choice in high volume usage.

**KEY FEATURES**

- Voltage ratings to 1000V (UM7000)
- Average power dissipation to 10 W
- Series resistance as low as 0.25  $\Omega$
- Carrier lifetime greater than 2.5  $\mu$ s
- Low capacitance
- Low conductance (High  $R_p$ )
- Compatible with automated assembly
- RoHS compliant packaging Available<sup>1</sup> (Use UMX7202B, etc.)

**IMPORTANT:**

For the most current data, consult MICROSEMI's website: [www.MICROSEMI.com](http://www.MICROSEMI.com)


<sup>1</sup> The UM7000 series of products can be supplied with a RoHS compliant finish (UMX7000) or with a 90/10 Sn/Pb finish. Stud Packages C/CR/D/DR are supplied with a RoHS complaint Gold finish Consult factory for details.

**ABSOLUTE MAXIMUM RATINGS AT 25° C (UNLESS OTHERWISE SPECIFIED)**

| Package   | Conditions   | ( $P_D$ ) Power Dissipation (W)        | ( $\Theta$ ) Thermal Resistance ( $^{\circ}$ C/W) |
|-----------|--|--|---|
| <b>A</b>  | 25 $^{\circ}$ C Pin Temperature                        | 10                                     | 15V   |
| <b>B</b>  | ½ in. total length to 25 $^{\circ}$ C Contact Free Air | 5.5                                    | 27.5  |
| <b>E</b>  |  | 1.5                                    |   |
| <b>C</b>  | 25 $^{\circ}$ C Stud Temperature                       | 10                                     | 15  |
| <b>D</b>  | 25 $^{\circ}$ C Stud Temperature                       | 7.5                                    | 20  |
| <b>SM</b> | 25 $^{\circ}$ C End Cap Temperature                    | 8                                      | 17  |
| ALL       | 1 $\mu$ s pulse (Single)                               | 100KW                                  | 60 kW<br>35 kW<br>20 kW                           |
| ALL       | Storage Temperature ( $T_{OP}$ )                       | -65 $^{\circ}$ C to + 175 $^{\circ}$ C |   |
| ALL       | Operating Temperature ( $T_{OP}$ )                     | -65 $^{\circ}$ C to + 175 $^{\circ}$ C |   |


**APPLICATIONS/BENEFITS**

- Isolated stud package available
- Surface mount package available
- Soldering temperature: 260  $^{\circ}$ C for 10 seconds maximum





# UM7000 / UM7100 / UM7200

HIGH POWER PIN DIODES

RoHS Compliant Versions Available



## VOLTAGE RATINGS





@ 25°C (unless otherwise specified)





| Part Number |        |        | Reverse Voltage @ 10uA (V) |
|-------------|--------|--------|----------------------------|
| UM7001      | UM7101 | UM7201 | 100                        |
| UM7002      | UM7102 | UM7202 | 200                        |
| -           | UM7104 | UM7204 | 400                        |
| UM7006      | -      | -      | 600                        |
| -           | UM7108 | -      | 800                        |
| UM7010      | -      | -      | 1000                       |



## ELECTRICAL PARAMETERS @ 25°C (unless otherwise specified)



| Parameter                | Symbol | Conditions                                     | UM7000 | UM7100 | UM7200 | Units |
|--------------------------|--------|--|--------|--------|--------|-------|
| Reverse Current (Max)    | $I_R$  | At rated voltage                               | 10     | 10     | 10     | uA    |
| Series Resistance(Max)   | $R_S$  | $I_F = 100 \text{ mA}$ , $F = 100 \text{ MHz}$ | 1.0    | 0.6    | 0.25   | Ohm   |
| Capacitance (Max)        | $C_T$  | $V_R = 100 \text{ V}$ , $F = 1 \text{ MHz}$    | 0.9    | 1.2    | 2.2    | pF    |
| Parallel Resistance(Min) | $R_P$  | $V_R = 100 \text{ V}$ , $F = 100 \text{ MHz}$  | 200k   | 150k   | 70k    | Ohms  |
| Carrier Lifetime(Min)    | $T_L$  | $I_F = 10 \text{ mA}$                          | 2.5    | 2.0    | 1.5    | uS    |
| I-Region Width (Min)     | W      | -  | 150    | 80     | 40     | um    |







See following pages for performance graphs and mechanical data.

**TYPICAL RS VS IF**

**TYPICAL RP VS VOLTAGE**

**IF VS VF**

**CAPACITANCE VS VOLTAGE**





**POWER RATING**
**POWER RATING STUD MOUNTED DIODES  
TYPICAL**

**TYPICAL RP VS VOLTAGE**
**UM7100  
TYPICAL**

**POWER RATING**
**POWER RATING AXIAL LEADED DIODES  
TYPICAL**

**CAPACITANCE VS VOLTAGE**
**UM7100  
TYPICAL**


**I/V VS TEMP**

**TYPICAL RP VS VOLTAGE**

**THERMAL IMPEDANCE**

 PULSE THERMAL IMPEDANCE VERSUS WIDTH  
TYPICAL

**CAPACITANCE VS VOLTAGE**


**PACKAGE STYLE 'A'**
**STYLE "A"**

**PACKAGE STYLE 'B'**
**STYLE "B"**

**PACKAGE STYLE 'C'**
**STYLE "C"**

**PACKAGE STYLE 'CR'**
**STYLE "CR"**

**PACKAGE STYLE 'D'**

**PACKAGE STYLE 'DR'**


RoHS Compliant Versions Available


**PACKAGE STYLE 'E'**

**PACKAGE STYLE 'SM'**

**STYLE 'SM' FOOTPRINT**

**NOTES:**

- 1 These dimensions will match the terminals and provide for additional solder fillets at the outboard ends at least as wide as the terminals themselves, assuming accuracy of placement within 0.005"
- 2 If the mounting method chosen requires use of an adhesive separate from the solder compound, a round (or square) spot of cement as shown should be centrally located.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microsemi:](#)

[UM7006B](#) [UM7010CR](#) [UM7010SM](#) [UM7104B](#) [UM7104DR](#) [UM7108B](#) [UM7104D](#)