
### BES 516-325-G-S4-C BES01C7





- PNP
- Normally open (NO)
- 4.00 mm
- Flush (shielded)
- Connector, M12x1-S04









### General attributes

Approvals / Conformity

Basic standard
Enclosure Type per IEC 60529
Function indicator
Operating distance marking

Operating distance marking Polarity reversal protected Power indicator Protection Class Short circuit protected

MTTF

## Electrical attributes

Connection type
Eff. operating current le
Eff. operating voltage Ue DC
Electrical version
Load capacitance max. (at Ue)
Max. no-load cur. lo undamped
Minimum operating current Im
No-load current lo damped max.
Operating voltage UB max. DC [V]
Operating voltage UB min. DC [V]
Rated insulation voltage Ui
Rated short circuit current
Ripple max. (% of Ue)
Switching freq. f max. (at Ue)

cULus CE EAC IEC 60947-5-2 IP68 according to BWN PR 20 Yes

Yes
Yes
No
II
Yes
640 a

Connector 200 mA 24.0 V DC, direct current 0.500 µF 3.0 mA 0 mA 6.0 mA 30.0 V

6.0 mA 30.0 V 10.0 V 250 VAC 100 A

2000 Hz





# Mechanical attributes

Ambient temperature Ta max.
Ambient temperature Ta min.
Assured operating distance Sa
Connector type
Depth
Diameter d1
Eff. operating distance Sr
Housing material
Mech. installation condition
Mounting length
Rated operating distance Sn [mm]

Sensing face material
Surface protection
Tightening torque

Normally open (NO) PNP 2.5 V

PNP 2.5 V

70 °C
-25 °C
3.20 mm
M12x1-S04
70.0 mm
M12x1
4.00 mm
CuZn
Flush (shielded)
54.5 mm
4.00 mm
LCP
Nickel-free coating

Nickel-free coating 10 Nm

### Remarks

The sensor is functional again after the overload has been eliminated.

For further information on MTTF/B10d, please refer to the MTTF / B10d Certificate.

Specification of the MTTF value and the B10d value do not represent any binding quality and/or life expectancy guarantees.



