



TERMINAL MATERIAL:COPPER

Wire Range A.W.G.	Wire Range mm ²	Item No. Brazed seam	Item No. Butted seam	d1 inch(mm)	d2 inch(mm)	L inch(mm)	t inch(mm)	Box (piece)	Carton (piece)
22 - 16	0.5 - 1.5	S1.25-3B	S1.25-3	0.075 (1.90)	0.126 (3.20)	0.630 (16.00)	0.030 (0.75)	5,000	30,000
22 - 16	0.5 - 1.5	S1.25-3.5SB	S1.25-3.5S	0.075 (1.90)	0.146 (3.70)	0.630 (16.00)	0.030 (0.75)	5,000	30,000
22 - 16	0.5 - 1.5	S1.25-3.5B	S1.25-3.5	0.075 (1.90)	0.146 (3.70)	0.630 (16.00)	0.030 (0.75)	5,000	30,000
22 - 16	0.5 - 1.5	S1.25-4SB	S1.25-4S	0.075 (1.90)	0.169 (4.30)	0.630 (16.00)	0.030 (0.75)	5,000	30,000

22 - 16	0.5 - 1.5	S1.25-4B	S1.25-4	0.075 (1.90)	0.169 (4.30)	0.630 (16.00)	0.030 (0.75)	5,000	30,000
22 - 16	0.5 - 1.5	S1.25-5B	S1.25-5	0.075 (1.90)	0.209 (5.30)	0.630 (16.00)	0.030 (0.75)	5,000	30,000
22 - 16	0.5 - 1.5	S1.25-6B	S1.25-6	0.075 (1.90)	0.252 (6.40)	0.669 (17.00)	0.030 (0.75)	4,000	24,000
22 - 16	0.5 - 1.5	S1.25-6SB	S1.25-6S	0.075 (1.90)	0.252 (6.40)	0.669 (17.00)	0.030 (0.75)	4,000	24,000
16 - 14	1.5 - 2.5	S2-3B	S2-3	0.098 (2.50)	0.126 (3.20)	0.630 (16.00)	0.031 (0.80)	5,000	30,000
16 - 14	1.5 - 2.5	S2-3.5SB	S2-3.5S	0.098 (2.50)	0.146 (3.70)	0.630 (16.00)	0.031 (0.80)	5,000	30,000
16 - 14	1.5 - 2.5	S2-3.5B	S2-3.5	0.098 (2.50)	0.146 (3.70)	0.630 (16.00)	0.031 (0.80)	5,000	30,000
16 - 14	1.5 - 2.5	S2-4SB	S2-4S	0.098 (2.50)	0.169 (4.30)	0.630 (16.00)	0.031 (0.80)	5,000	30,000
16 - 14	1.5 - 2.5	S2-4B	S2-4	0.098 (2.50)	0.169 (4.30)	0.630 (16.00)	0.031 (0.80)	5,000	30,000
16 - 14	1.5 - 2.5	S2-5B	S2-5	0.098 (2.50)	0.209 (5.30)	0.630 (16.00)	0.031 (0.80)	5,000	30,000
16 - 14	1.5 - 2.5	S2-6B	S2-6	0.098 (2.50)	0.252 (6.40)	0.669 (17.00)	0.031 (0.80)	4,000	24,000
16 - 14	1.5 - 2.5	S2-6SB	S2-6S	0.098 (2.50)	0.252 (6.40)	0.669 (17.00)	0.031 (0.80)	4,000	24,000
16 - 14	1.5 - 2.5	S2-8B	S2-8	0.098 (2.50)	0.331 (8.40)	0.870 (22.10)	0.031 (0.80)	4,000	24,000
14 - 12	2.5 - 4	S3.5-4B	S3.5-4	0.134 (3.40)	0.169 (4.30)	0.709 (18.00)	0.031 (0.80)	2,000	12,000
14 - 12	2.5 - 4	S3.5-5B	S3.5-5	0.134 (3.40)	0.209 (5.30)	0.709 (18.00)	0.031 (0.80)	2,000	12,000
12 - 10	4 - 6	S5.5-3B	S5.5-3	0.142 (3.60)	0.126 (3.20)	0.768 (19.50)	0.039 (1.00)	2,000	12,000
12 - 10	4 - 6	S5.5-3.5SB	S5.5-3.5S	0.142 (3.60)	0.146 (3.70)	0.768 (19.50)	0.039 (1.00)	2,000	12,000
12 - 10	4 - 6	S5.5-3.5B	S5.5-3.5	0.142 (3.60)	0.146 (3.70)	0.728 (18.50)	0.039 (1.00)	2,000	12,000
12 - 10	4 - 6	S5.5-4B	S5.5-4	0.142 (3.60)	0.169 (4.30)	0.768 (19.50)	0.039 (1.00)	2,000	12,000
12 - 10	4 - 6	S5.5-4SB	S5.5-4S	0.142 (3.60)	0.165 (4.20)	0.768 (19.50)	0.039 (1.00)	2,000	12,000
12 - 10	4 - 6	S5.5-5B	S5.5-5	0.142 (3.60)	0.209 (5.30)	0.768 (19.50)	0.039 (1.00)	2,000	12,000
12 - 10	4 - 6	S5.5-6B	S5.5-6	0.142 (3.60)	0.252 (6.40)	0.909 (23.10)	0.039 (1.00)	1,500	9,000
12 - 10	4 - 6	S5.5-6SB	S5.5-6S	0.142 (3.60)	0.252 (6.40)	0.906 (23.00)	0.039 (1.00)	1,500	9,000
12 - 10	4 - 6	S5.5-8B	S5.5-8	0.142 (3.60)	0.331 (8.40)	0.984 (25.00)	0.039 (1.00)	1,500	9,000

