Surface Mount Multilayer Ceramic Chip Capacitors (SMD MLCCs)



#### **Overview**

KEMET's COG dielectric features a 125°C maximum operating temperature and is considered "stable." The Electronics Components, Assemblies & Materials Association (EIA) characterizes COG dielectric as a Class I material. Components of this classification are temperature compensating and are suited for resonant circuit applications or those where Q and stability of capacitance characteristics are required. COG exhibits no change in capacitance with respect to time and voltage and boasts a negligible change in capacitance with reference to ambient temperature. Capacitance change is limited to  $\pm 30$  ppm/°C from -55°C to +125°C.

## **Benefits**

- -55°C to +125°C operating temperature range
- · Lead (Pb)-free, RoHS, and REACH compliant
- EIA 0201, 0402, 0603, 0805, 1206, 1210, 1808, 1812, 1825, 2220, and 2225 case sizes
- DC voltage ratings of 10 V, 16 V, 25 V, 50 V, 100 V, 200 V, and 250 V
- Capacitance offerings ranging from 0.5 pF up to 0.47  $\mu F$
- Available capacitance tolerances of ±0.10 pF, ±0.25 pF, ±0.5 pF, ±1%, ±2%, ±5%, ±10%, and ±20%
- · No piezoelectric noise
- Extremely low ESR and ESL
- · High thermal stability
- High ripple current capability



Ordering	Information
----------	-------------

С	1206	С	104	J	3	G	Α	С	TU
Ceramic	Case Size (L" x W")	Specification/ Series <sup>1</sup>	Capacitance Code (pF)	Capacitance Tolerance <sup>2</sup>	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish <sup>3</sup>	Packaging/ Grade (C-Spec)
	0201 0402 0603 0805 1206 1210 1808 1812 1825 2220 2225	C = Standard	Two significant digits and number of zeros. Use 9 for 1.0 – 9.9 pF Use 8 for 0.5 – .99 pF e.g., 2.2 pF = 229 e.g., 0.5 pF = 508	C = ±0.25 pF D = ±0.5 pF	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	G = COG	A = N/A	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table"

<sup>1</sup> Flexible termination option is available. Please see FT-CAP product bulletin C1062\_C0G\_FT-CAP\_SMD

<sup>2</sup> Additional capacitance tolerance offerings may be available. Contact KEMET for details.

<sup>3</sup> Additional termination finish options may be available. Contact KEMET for details.



## Packaging C-Spec Ordering Options Table

Packaging Type <sup>1</sup>	Packaging/Grade Ordering Code (C-Spec)
Bulk Bag/Unmarked	Not required (Blank)
7" Reel/Unmarked	TU
13" Reel/Unmarked	7411 (EIA 0603 and smaller case sizes) 7210 (EIA 0805 and larger case sizes)
7" Reel/Unmarked/2 mm pitch <sup>2</sup>	7081
13" Reel/Unmarked/2 mm pitch <sup>2</sup>	7082

<sup>1</sup> Default packaging is "Bulk Bag". An ordering code C-Spec is not required for "Bulk Bag" packaging.

<sup>1</sup> The terms "Marked" and "Unmarked" pertain to laser marking option of capacitors. All packaging options labeled as "Unmarked" will contain capacitors that have not been laser marked. The option to laser mark is not available on these devices. For more information see "Capacitor Marking".

<sup>2</sup> The 2 mm pitch option allows for double the packaging quantity of capacitors on a given reel size. This option is limited to EIA 0603 (1608 metric) case size devices. For more information regarding 2 mm pitch option see "Tape & Reel Packaging Information".

#### Benefits cont.

- · Preferred capacitance solution at line frequencies and into the MHz range
- No capacitance change with respect to applied rated DC voltage
- Negligible capacitance change with respect to temperature from -55°C to +125°C
- · No capacitance decay with time
- · Non-polar device, minimizing installation concerns
- · 100% pure matte tin-plated termination finish allowing for excellent solderability
- SnPb plated termination finish option available upon request (5% Pb minimum)

#### **Applications**

Typical applications include critical timing, tuning, circuits requiring low loss, circuits with pulse, high current, decoupling, bypass, filtering, transient voltage suppression, blocking and energy storage.

## **Qualification/Certification**


Commercial Grade products are subject to internal qualification. Details regarding test methods and conditions are referenced in Table 4, Performance and Reliability.

#### **Environmental Compliance**

Lead (Pb)-free, RoHS, and REACH compliant without exemptions.



# **Dimensions – Millimeters (Inches)**



EIA Size Code	Metric Size Code	L Length	W Width	T Thickness	B Bandwidth	S Separation Minimum	Mounting Technique
0201	0603	0.60 (0.024) ±0.03 (0.001)	0.30 (0.012) ±0.03 (0.001)		0.15 (0.006) ±0.05 (0.002)	N/A	Solder Reflow
0402	1005	1.00 (0.040) ±0.05 (0.002)	0.50 (0.020) ±0.05 (0.002)		0.30 (0.012) ±0.10 (0.004)	0.30 (0.012)	Only
0603	1608	1.60 (0.063) ±0.15 (0.006)	0.80 (0.032) ±0.15 (0.006)		0.35 (0.014) ±0.15 (0.006)	0.70 (0.028)	
0805	2012	2.00 (0.079) ±0.20 (0.008)	1.25 (0.049) ±0.20 (0.008)		0.50 (0.02) ±0.25 (0.010)	0.75 (0.030)	Solder Wave or Solder Reflow
1206	3216	3.20 (0.126) ±0.20 (0.008)	1.60 (0.063) ±0.20 (0.008)		0.50 (0.02) ±0.25 (0.010)		
1210	3225	3.20 (0.126) ±0.20 (0.008)	2.50 (0.098) ±0.20 (0.008)	See Table 2 for Thickness	0.50 (0.02) ±0.25 (0.010)		
1808	4520	4.70 (0.185) ±0.50 (0.020)	2.00 (0.079) ±0.20 (0.008)		0.60 (0.024) ±0.35 (0.014)		
1812	4532	4.50 (0.177) ±0.30 (0.012)	3.20 (0.126) ±0.30 (0.012)		0.60 (0.024) ±0.35 (0.014)	N/A	Solder Reflow
1825	4564	4.50 (0.177) ±0.30 (0.012)	6.40 (0.252) ±0.40 (0.016)		0.60 (0.024) ±0.35 (0.014)		Only
2220	5650	5.70 (0.224) ±0.40 (0.016)	016) ±0.40 (0.016)		0.60 (0.024) ±0.35 (0.014)		
2225	5664	5.60 (0.220) ±0.40 (0.016)	6.40 (0.248) ±0.40 (0.016)		0.60 (0.024) ±0.35 (0.014)		



## **Electrical Parameters/Characteristics**

Item	Parameters/Characteristics
Operating Temperature Range	-55°C to +125°C
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	±30 ppm/°C
Aging Rate (Maximum % Capacitance Loss/Decade Hour)	0%
<sup>1</sup> Dielectric Withstanding Voltage (DWV)	250% of rated voltage (5±1 seconds and charge/discharge not exceeding 50 mA)
<sup>2</sup> Dissipation Factor (DF) Maximum Limit at 25°C	0.1%
<sup>3</sup> Insulation Resistance (IR) Limit at 25°C	1,000 megohm microfarads or 100 GΩ (Rated voltage applied for 120±5 seconds at 25°C)

<sup>1</sup>DWV is the voltage a capacitor can withstand (survive) for a short period of time. It exceeds the nominal and continuous working voltage of the capacitor.

<sup>2</sup> Capacitance and dissipation factor (DF) measured under the following conditions:

1 MHz ±100 kHz and 1.0 Vrms ±0.2 V if capacitance  $\leq$  1,000 pF

1 kHz ±50 Hz and 1.0 Vrms ±0.2 V if capacitance > 1,000 pF

<sup>3</sup> To obtain IR limit, divide  $M\Omega$ - $\mu$ F value by the capacitance and compare to G $\Omega$  limit. Select the lower of the two limits.

Capacitance and Dissipation Factor (DF) measured under the following conditions:

Note: When measuring capacitance it is important to ensure the set voltage level is held constant. The HP4284 and Agilent E4980 have a feature known as Automatic Level Control (ALC). The ALC feature should be switched to "ON."

## **Post Environmental Limits**

	High Temperatu	ıre Life, Biased	Humidity, Mois	ture Resistance	
Dielectric	Rated DC Voltage	Capacitance Value	Dissipation Factor (Maximum %)	Capacitance Shift	Insulation Resistance
COG	All	All	0.5	0.3% or ±0.25 pF	10% of Initial Limit



## Table 1A - Capacitance Range/Selection Waterfall (0201 - 1206 Case Sizes)

		Case Size/	C0201C	C C0402C	C0603C	C0805C	C1206C
	Сар	Series	CU201C	, 04020	C0003C	C0805C	C1200C
Сар	Code	Voltage Code	8 4 3		8 4 3 5 1 2 A	8 4 3 5 1 2 A	8 4 3 5 1 2 A
	Coue	Rated Voltage (VDC)	10 16 25	-0 16 50 50 100 250 250	10 16 50 50 200 250	10 16 50 50 100 250	10 16 25 50 100 250
		Capacitance Tolerance			duct Availability and Chip ee Table 2 for Chip Thickr	ness Dimensions	
0.50 & 0.75 pF		B C D		BB BB BB BB		DN DN DN DN DN DN DN	
0.75 pF 1.0 - 9.1 pF*	758 109 - 919*	B C D B C D		BB BB BB BB BB BB BB BB		DN DN DN DN DN DN DN DN DN DN DN DN DN DN	EB EB EB EB EB EB
1.0 = 9.1 pF** 1.1 pF	119 - 919.	B C D		BB BB BB BB		DN DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
1.2 pF	129	BCD		BB BB BB BB		DN DN DN DN DN DN DN	
1.3 pF	139	BCD		BB BB BB BB	CF CF CF CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
1.5 pF	159	BCD		BB BB BB BB		DN DN DN DN DN DN DN	
1.6 pF	169	BCD		BB BB BB BB	CF CF CF CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
1.8 pF	189	BCD		BB BB BB BB	CF CF CF CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
2.0 pF	209	BCD		BB BB BB BB	CF CF CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
2.2 pF	229	B C D		BB BB BB BB		DN DN DN DN DN DN DN	
2.4 pF	249	BCD		BB BB BB BB		DN DN DN DN DN DN DN	
2.7 pF	279	BCD		BB BB BB BB		DN DN DN DN DN DN DN	
3.0 pF	309	BCD		BB BB BB BB	CF CF CF CF CF CF CF		
3.3 pF	339	B C D		BB BB BB BB		DN DN DN DN DN DN DN	
3.6 pF 3.9 pF	369 399	B C D B C D		BB BB BB BB BB BB BB BB		DN DN DN DN DN DN DN DN DN DN DN DN DN DN	
4.3 pF	439	BCD		BB BB BB BB	CF CF CF CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
4.3 pr 4.7 pF	479	BCD		BB BB BB BB			
5.1 pF	519	BCD		BB BB BB BB	CF CF CF CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
5.6 pF	569	B C D		BB BB BB BB		DN DN DN DN DN DN DN	
6.2 pF	629	BCD		BB BB BB BB	CF CF CF CF CF CF CF	DN DN DN DN DN DN DN	
6.8 pF	689	BCD		BB BB BB BB		DN DN DN DN DN DN DN	
7.5 pF	759	BCD		BB BB BB BB	CF CF CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB
8.2 pF	829	B C D		BB BB BB BB	CF CF CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB
9.1 pF	919	BCD		BB BB BB BB	CF CF CF CF CF CF CF		
10 pF	100		AB1 AB1 AB			DN DN DN DN DN DN DN	
11 pF	110	FGJK		BB BB BB BB	CF CF CF CF CF CF CF	DN DN DN DN DN DN DN	
12 pF	120		AB <sup>2</sup> AB <sup>2</sup> AB				
13 pF	130	FGJK		BB BB BB BB	CF CF CF CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB
15 pF	150	F G J K M F G J K M	AB <sup>2</sup> AB <sup>2</sup> AB	<sup>12</sup> BB BB BB BB BB BB BB BB	CF CF CF CF CF CF CF CF CF CF CF CF CF CF	DN DN DN DN DN DN DN DN DN DN DN DN DN DN	
16 pF 18 pF	160 180		AB <sup>2</sup> AB <sup>2</sup> AB			DN DN DN DN DN DN DN DN DN DN DN DN DN DN	
20 pF	200	FGJKI		BB BB BB BB	CF CF CF CF CF CF CF CF	DN DN DN DN DN DN DN DN	
20 pF	220		AB <sup>2</sup> AB <sup>2</sup> AB			DM DM DM DM DN DN DN	
24 pF	240	FGJKI		BB BB BB BB	CF CF CF CF CF CF CF		
27 pF	270		AB <sup>2</sup> AB <sup>2</sup> AB			DN DN DN DN DN DN DN	
30 pF	300	FGJKI		BB BB BB BB	CF CF CF CF CF CF CF		EB EB EB EB EB EB EB
33 pF	330		AB <sup>2</sup> AB <sup>2</sup> AB			DN DN DN DN DN DN DN	
36 pF	360	FGJK		BB BB BB BB		DN DN DN DN DN DN DN	
39 pF	390		AB <sup>2</sup> AB <sup>2</sup> AB			DN DN DN DN DN DN DN	
43 pF	430	FGJK				DN DN DN DN DN DN DN	
47 pF	470					DN DN DN DN DN DN DN	
51 pF	510	FGJK		BB BB BB BB		DN DN DN DN DN DN DN	
56 pF	560					DN DN DN DN DN DN DN	
62 pF	620	FGJK		BB         BB         BB         BB           B <sup>2</sup> BB         BB         BB         BB		DN DN DN DN DN DN DN DN DN DN DN DN DN DN	
68 pF 75 pF	680 750	F G J K I		BB BB BB BB BB		DN DN DN DN DN DN DN DN DN DN DN DN DN DN	
82 pF	820			<sup>2</sup> BB BB BB BB		DN DN DN DN DN DN DN DN DN DN DN DN DN	
91 pF	910	F G J K I		BB BB BB BB		DN DN DN DN DN DN DN	
100 pF	101			<sup>2</sup> BB BB BB BB BB BB BB			
		Rated Voltage (VDC)			10         10           16         9           25         25           50         9           100         9           250         9           250         9           250         9	10       16       16       25       50       100       200       250       250	10 1 16 1 25 25 1 100 1 100 1 250 1 250 1
Сар	Cap Code	Voltage Code	8 4 3		8 4 3 5 1 2 A	8 4 3 5 1 2 A	8 4 3 5 1 2 A
-		Case Size/Series	C0201C	C0402C	C0603C	C0805C	C1206C
				·	10 20 22 24 27 20 22		

\*Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82, and 91). xx<sup>1</sup> Available only in D, J, K, M tolerance

xx<sup>2</sup> Available only in J, K, M tolerance.

These products are protected under US Patents 7,172,985 & 7,670,981, other patents pending, and any foreign counterparts.

© KEMET Electronics Corporation • P.O. Box 5928 • Greenville, SC 29606 • 864-963-6300 • www.kemet.com



## Table 1A – Capacitance Range/Selection Waterfall (0201 – 1206 Case Sizes) cont.

	0	Case Size/ Series	CO	20	1C			C0	40	2C					CO	60	<b>3C</b>	;				C	)80	)5C					<b>C</b> 1	20	60		
Сар	Сар	Voltage Code	8	4         3         8         4         3         5         1         2         A           9         1         20         1         2         2         1											3	5	1	2	A	8	4	3	5	1	2	A	8	4	3	5	1	2	A
	Code	Rated Voltage (VDC)	10	16	25	10	16	25	50	00	00	250	9	16	25	50	100	200	250	10	16	25	50	100	200	250	5	16	25	50	10	200	250
		Capacitance Tolerance										Pre	odu				ity a	and	Chi nick	p Tl nes	nick s Di	ness men	sion	des Is									
110 - 180 pF*	111 - 181*	FGJKM				BB	BB	BB	BB	BB	BB	BB		CF	CF		CF					I DN							EB				EB
200 – 270 pF* 300 pF	201 - 271* 301	F G J K M F G J K M				BB BB		BB BB	BB BB	BB BB	BB BD	BB BD	CF CF	CF CF	CF CF	CF CF						I DN I DN							EB EB		EB EB		EB EB
330 pF	331	FGJKM				BB		BB	BB	BB	BD			CF	CF	CF		-															
360 pF	361	F G J K M				BB		BB		BB			CF	CF	CF	CF			_			I DN		-	-			-	_	-			EB
390 pF	391	F G J K M				BB	BB	BB	BB	BB			CF	CF	CF	CF	CF	CF	CF	D	N DN	I DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	EB	EB
430 pF	431	F G J K M				BB	BB		BB	BB			CF	CF	CF	CF						I DN											
470 pF	471	F G J K M				BB		BB		BB			CF	CF	CF	CF		-				I DN							EB				
510 pF	511	F G J K M				BB	_		BB			_	CF	CF	CF	CF	CF		_		_	I DN	_	_	_	_		_	_	_	_	_	_
560 pF	561	FGJKM				BB		BB	BB				CF	CF	CF	CF		-				I DN											
620 pF 680 pF	621 681	F G J K M F G J K M				BB BB		BB BB	BB BB				CF CF	CF CF	CF CF	CF CF	-	-	-			I DN I DN									EB		
750 pF	751	FGJKM				BB		BB		BB			CF	CF	CF	CF	-	-													EB		
820 pF	821	FGJKM				BB		BB		BB			CF	CF	CF	CF		-	-										EB		EB		
910 pF	911	FGJKM				BB		BB		BB			CF	CF	CF	CF	CF	CF	_		N DN	I DN	DN	DP	DP	DP	EB	-	_	-			_
1,000 pF	102	F G J K M				BB		BB		BB			CF	CF	CF	CF	CF				N DN		DN						EB			EB	
1,100 pF	112	F G J K M				BB		BB	BB				CF	CF	CF	CF	CF	-				I DN							EB				
1,200 pF	122	FGJKM				BB		BB	BB				CF	CF	CF	CF	CF					I DN				DN			EB				
1,300 pF	132	FGJKM				BB		BB	BB				CF	CF	CF	CF	CF		_		_	_	_	_	_	DN			_		_	_	
1,500 pF 1,600 pF	152 162	F G J K M F G J K M				BB BB		BB BB	BB				CF CF	CF CF	CF CF	CF CF	-	1.1	-	I DF				DP DP			EB						EC ED
1,800 pF 1,800 pF	182	FGJKM				BB		BB					CF	CF	CF	CF	-		-								EB						
2,000 pF	202	FGJKM				BB		BB					CF	CF	CF	CF	-										EB						
2,200 pF	222	FGJKM				BB	BB						CF	CF.	CF	CF	-	-	-			I DN											EE
2,400 pF	242	F G J K M											CF	CF	CF	CF	CF			D	N DN	I DN	DN	DN	DN	DN	EB	EB	EB	EB	EC	EC	EC
2,700 pF	272	F G J K M											CF	CF	CF	CF				D			DN			DN			EB		EC	EC	
3,000 pF	302	F G J K M											CF	CF	CF	CF				DF						DN							
3,300 pF	332	FGJKM											CF	CF	CF	CF				DF						DN							
3,600 pF	362	FGJKM						_					CF	CF	CF	CF	_			DF	_	_	_	_	_	_	EC	_	_	_	_	_	_
3,900 pF 4,300 pF	392 432	F G J K M F G J K M											CF CF	CF CF	CF CF	CF CF				DE			DE				EC EC				EF EC		
4,300 pF	432	FGJKM											CF	CF	CF	CF				DE						DP							
5,100 pF	512	FGJKM											CF	CF	CF	CF				D			DE				ED						
5,600 pF	562	FGJKM											CF	CF.	CF	CF				DI						DP.							
6,200 pF	622	F G J K M											CF	CF	CF	CF				DI	N DN	I DN	DN	DN	DG	DG	EB	EB	EB	EB	EB	EB	EB
6,800 pF	682	F G J K M											CF	CF	CF	CF				D		I DN							EB			EB	
7,500 pF	752	F G J K M											CF	CF	CF					D		I DN											
8,200 pF	822	FGJKM											CF	CF	CF					D						DG							-
9,100 pF	912 103	F G J K M											CF CF	CF CF	CF					D	_	I DN I DN	-	_	-		EC ED		EC	EC ED		EC EC	_
10,000 pF 12,000 pF	103	F G J K M F G J K M												CF													EB			ED		ED	
15,000 pF	123	FGJKM											CF	CF	CF												EB			EB		EF	
18,000 pF	183	FGJKM																										EB	EB	EB	EB	EH	EH
22,000 pF	223	F G J K M																		DF	DF	P DP	DF				EB	EB	EB	EB	EC	EH	EH
27,000 pF	273	F G J K M																				DF					EB	EB	EB	EB	EE		
33,000 pF	333	FGJKM																				DG								EB			
39,000 pF	393	FGJKM																				DG					EC			EE			
47,000 pF	473	FGJKM																		DC	i   DC	G DG					EC	EC ED		EE	EH		
56,000 pF 68,000 pF	563 683	F G J K M																												EH			
82,000 pF	823	FGJKM																												EH			
0.10 µF	104	FGJKM																										EH					
		Rated Voltage (VDC)	10	16	25	10	16	25	50	100	200	250	10	16	25	50	100	200	250	6	: 1	25	20	100	200	250			25		100	200	250
Cap	Cap Code	Voltage Code	8																														
		Case Size/Series	C0201C C0402C					C0603C				C0805C					C1206C																

\*Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82, and 91). xx<sup>1</sup> Available only in D, J, K, M tolerance xx<sup>2</sup> Available only in J, K, M tolerance.

These products are protected under US Patents 7,172,985 & 7,670,981, other patents pending, and any foreign counterparts.

© KEMET Electronics Corporation • P.O. Box 5928 • Greenville, SC 29606 • 864-963-6300 • www.kemet.com

6



## Table 1B - Capacitance Range/Selection Waterfall (1210 - 2225 Case Sizes)

		Case Size/			<b>C1</b>	21(	າດ				C18	080			218	120			218	250			222	20	C		222	25	C
	Сар	Series		1		210		1	1			1				1				1				-	-		,		
Сар	Code	Voltage Code	8	4	3	5	1	2	A	5	1	2	A	5	1	2	A	5	1	2	A	5	1	2	A	5	1	2	A
	Coue	Rated Voltage (VDC)	9	16	25	50	100	200	250	50	100	200	250	50	100	200	250	50	100	200	250	50	100	200	250	50	100	200	250
		Capacitance										luct	Avai			ind C	Chip	Thic ess I		ss C	odes	S							
1.0 - 9.1 pF*	109 - 919*	Tolerance B C D	FB	FB	FB	FB	FB	FB	FB		36	eid	Die 4	2 101	տոր	5 1 11	CKII		Jiiie	:11510	115								
10 - 91 pF*	100 - 910*	FGJKN		FB	FB	FB	FB	FB	FB																				
100 - 300 pF*	101 - 301*	FGJKM	I FB	FB	FB	FB	FB	FB	FB													1				1			
330 - 430 pF*	331 - 431*	FGJKM	I FB	FB	FB	FB	FB	FB	FB	LF	LF	LF	LF																
470 - 910 pF*	471 - 911*	FGJKN		FB	FB	FB	FB	FB	FB	LF	LF	LF	LF	GB	GB	_	_												
1,000 pF	102	FGJKN		FB	FB	FB	FB	FB	FB	LF	LF	LF	LF	GB	GB	GB	GB												
1,100 pF	112	FGJKN		FB	FB	FB	FB	FB	FB	LF	LF	LF	LF	GB	GB	GB	GB												
1,200 pF	122	FGJKN		FB	FB	FB	FB	FB	FB	LF	LF	LF	LF	GB	GB	GB	GB												
1,300 pF	132	FGJKN		FB	FB	FB	FB	FC	FC	LF	LF	LF	LF	GB	GB	GB	GB								1				
1,500 pF	152	FGJKN	-	FB	FB	FB	FB	FE	FE	LF	LF	LF	LF	GB	GB	GB	GB												
1,600 pF	162	FGJKN		FB	FB	FB	FB	FE	FE	LF	LF	LF	LF	GB	GB	GB	GB												
1,800 pF	182	FGJKN		FB	FB	FB	FB	FE	FE FE	LF LF	LF LF	LF LF	LF	GB	GB	GB	GB												
2,000 pF	202 222	F G J K N F G J K N		FB FB	FB FB	FB FB	FC FC	FE FG	FG	LF	LF	LF	LF LF	GB GB	GB GB	GB GB	GB GB												
2,200 pF	242			FB	FB	FB FB	FC	FC	FC	LF	LF	LF	LF	GB	GB	GB	GB												
2,400 pF 2,700 pF	242	F G J K N F G J K N		FB	FB	FB FB	FC	FC	FC	LF	LF	LF	LF	GB	GR	GB	GB												
2,700 pF 3,000 pF	302	FGJKN		FB	FB	FB	FC	FF	FF	LF	LF	L.L.		00											1				
3,300 pF	332	FGJKN		FB	FB	FB	FF	FF	FF	LF	LF			GB	GR	GB	GB								1				
3,600 pF	362	FGJKN		FB	FB	FB	FF	FF	FF	LF	LF			00	00	00	00												
3,900 pF	392	FGJKN		FB	FB	FB	FF	FF	FF	LF	LF			GB	GB	GB	GB	НВ	НВ	НВ	НВ				1				
4,300 pF	432	F G J K M	-	FB	FB	FB	FF	FF	FF	LF	LF			0.5	0.5	0.5	0.5												
4,700 pF	472	FGJKN		FF	FF	FF	FG	FG	FG	LF	LF			GB	GB	GD	GD	НВ	НВ	HB	НВ					KE	KE	KE	KE
5,100 pF	512	FGJKN		FB	FB	FB	FG	FG	FG					-												KE	KE	KE	KE
5,600 pF	562	FGJKN	I FB	FB	FB	FB	FG	FG	FG					GB	GB	GH	GH	HB	HB	HB	HB					KE	KE	KE	KE
6,200 pF	622	FGJKM	I FB	FB	FB	FB	FG	FB	FB													I I				KE	KE	KE	KE
6,800 pF	682	FGJKN	I FB	FB	FB	FB	FG	FB	FB					GB	GB	GJ	GJ	HB	HB	HB	HB	JE	JE	JB		KE	KE	KE	KE
7,500 pF	752	FGJKN	I FC	FC	FC	FC	FC	FB	FB																	KE	KE	KE	KE
8,200 pF	822	FGJKN		FC	FC	FC	FC	FB	FB					GB	GH	GB	GB	HB	HB	HB	HB	JE	JE	JB		KE	KE	KE	KE
9,100 pF	912	FGJKN		FE	FE	FE	FE	FB	FB													1			1	KE	KE	KE	
10,000 pF	103	FGJKN	-	FF	FF	FF	FF	FB	FB					GB	GH	GB		HB	HB		HE	JE	JE	JB		KE	KE	KE	_
12,000 pF	123	FGJKN		FG	FG	FG	FB	FB	FB					GB	GG	GB	GB	HB	HB	HE	HE		JE	JB		KE	KE	KE	
15,000 pF	153	FGJKN		FG	FG	FG	FB	FC	FC					GB		GB	GB	HB	HB			JE	JE	JB		KE	KE	KE	KE
18,000 pF	183	FGJKN		FB	FB	FB	FB	FC	FC					GB	GB	GB	GB	HB	HE			JE	JE	JB		KE	KE		
22,000 pF	223	FGJKN		FB	FB	FB	FB	FF	FF					GB	GB	GB	GB	HB	HE			JE	JB	JB		KE	KE		
27,000 pF	273	FGJKN	-	FB	FB	FB	FB	FG	FG					GB	GB	GB	GB	HB	HG			JE	JB	JB		KE	KE		
33,000 pF	333	F G J K N F G J K N		FB	FB	FB	FB	FH	FH					GB	GB	GB	GB					JB	JB	JB JB	1	KE			
39,000 pF	393 473	F G J K N F G J K N		FB FB	FB FB	FB FB	FE FE	FH FJ	FH FJ					GB GB	GB GB	GB GD	GB GD					JB JB	JB JB	JB	1				
47,000 pF		F G J K N		FB	FB	FB FB	FF	гJ	гJ					GB	GB	GD	GD					JB	JB	JB	1				
56,000 pF 68,000 pF	563 683	F G J K N		FB	FB	FB	FG							GB	GB	GK						JB	JB	JB	1				
82,000 pF	823	F G J K N	-	FC	FC	FF	FH							GB		GM						JB	JB	JB					
0.10 µF	104		I FE	FE			FM							GB		GM						JB	JB	JD					
0.12 µF	124	FGJKN				FH	1 IVI								GH	OW	OW					JB		JD					
0.12 µF	154	FGJKN			FH										GN							JB		JG					
0.18 µF	184	FGJKN		FJ	FJ									GH								JB		JG					
0.22 µF	224	F G J K N	FK	FK										GK								JB		JL					
0.27 µF	274	F G J K N	1																			JB	JF	1	1				
0.33 µF	334	FGJKN	II.																			JD	JG		1				
0.39 µF	394	F G J K N	1																			JG			1	1			
0.47 µF	474	FGJKN																				JG							
		Rated Voltage (VDC)	9	16	25	50	100	200	250	50	100	200	250	50	100	200	250	50	100	200	250	50	100	200	250	50	100	200	250
Сар	Cap	Voltage Code	8	4	3	5	1	2	A	5	1	2		5		2	A	5	1	2	A	5	1	2	A	5	1	2	A
Cap	Code	Case Size/Series		I					1		C18				C18		1			25C				200			C22		
		I	1	C1210C C18																		L	_	01)					

\*Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82, and 91). These products are protected under US Patents 7,172,985 & 7,670,981, other patents pending, and any foreign counterparts.

7



## Table 2A – Chip Thickness/Tape & Reel Packaging Quantities

Thickness	Case	Thickness ±	Paper Q	uantity <sup>1</sup>	Plastic	Quantity			
Code	Size <sup>1</sup>	Range (mm)	7" Reel	13" Reel	7" Reel	13" Reel			
AB	0201	0.30±0.03	15,000	0	0	0			
BB	0402	0.50±0.05	10,000	50,000	0	0			
BD	0402	0.55±0.05	10,000	50,000	0	0			
CF	0603	0.80±0.07	4,000	15,000	0	0			
СН	0603	0.85±0.07	4,000	10,000	0	0			
DM	0805	0.70±0.20	4,000	15,000	0	0 0			
DN	0805		0.78±0.10 4,000 15,000 0						
DP	0805	0.90±0.10	4,000	15,000	0	0			
DE	0805	1.00±0.10	0	0	2,500	10,000			
DF	0805	1.10±0.10	0	0	2,500	10,000			
DG EB	0805 1206	1.25±0.15	0	0	2,500	10,000 10,000			
EC	1206	0.78±0.10 0.90±0.10	0 0	0 0	4,000 4,000	10,000			
ED	1206	1.00±0.10	0	0	2,500	10,000			
EE	1200	1.10±0.10	0	0	2,500	10,000			
EF	1200	1.20±0.15	0	0	2,500	10,000			
EH	1200	1.60±0.20	0	0	2,000	8,000			
FB	1210	0.78±0.10	0	0	4,000	10,000			
FC	1210	0.90±0.10	0	0	4,000	10,000			
FE	1210	1.00±0.10	0 0	0 0	2,500	10,000			
FF	1210	1.10±0.10	0	0	2,500	10,000			
FG	1210	1.25±0.15	Ő	0 0	2,500	10,000			
FH	1210	1.55±0.15	0	0	2,000	8,000			
FM	1210	1.70±0.20	0	0	2,000	8,000			
FJ	1210	1.85±0.20	0	0	2,000	8,000			
FK	1210	2.10±0.20	0	0	2,000	8,000			
NC	1706	1.00±0.15	0			10,000			
LF	1808	1.00±0.15	0	0	2,500	10,000			
GB	1812	1.00±0.10	0	0	1,000	4,000			
GD	1812	1.25±0.15	0	0	1,000	4,000			
GH	1812	1.40±0.15	0	0	1,000	4,000			
GG	1812	1.55±0.10	0	0	1,000	4,000			
GK	1812	1.60±0.20	0	0	1,000	4,000			
GJ	1812	1.70±0.15	0	0	1,000	4,000			
GN	1812	1.70±0.20	0	0	1,000	4,000			
GM	1812	2.00±0.20	0	0	500	2,000			
HB	1825	1.10±0.15	0	0	1,000	4,000			
HE HG	1825 1825	1.40±0.15	0 0	0 0	1,000	4,000			
		1.60±0.20			1,000	4,000			
JB JD	2220 2220	1.00±0.15 1.30±0.15	0	0	1,000 1,000	4,000 4,000			
JD JE	2220	1.30±0.15 1.40±0.15	0	0	1,000	4,000 4,000			
JF	2220	1.50±0.15	0	0	1,000	4,000			
JG	2220	1.70±0.15	0	0	1,000	4,000			
JL	2220	2.00±0.20	0 0	Ő	500	2,000			
KE	2225	1.40±0.15	0	0	1,000	4,000			
Thickness	Case	Thickness ±	7" Reel	13" Reel	7" Reel	13" Reel			
Code	Size <sup>1</sup>	Range (mm)	Paper Q	uantity <sup>1</sup>	Plastic	l Quantity			

Package quantity based on finished chip thickness specifications.

<sup>1</sup> If ordering using the 2 mm Tape and Reel pitch option, the packaging quantity outlined in the table above will be doubled. This option is limited to EIA 0603 (1608 metric) case size devices. For more information regarding 2 mm pitch option see "Tape & Reel Packaging Information".



## Table 2B – Bulk Packaging Quantities

Deeker		Loose Pa	ackaging
Раскау	ing Type	Bulk Bag	(default)
Packagin	g C-Spec <sup>1</sup>	N/	Ά²
Case	Size	Packaging Quantities (	pieces/unit packaging)
EIA (in)	Metric (mm)	Minimum	Maximum
0402	1005		
0603	1608		
0805	2012		50,000
1206	3216		
1210	3225	1	
1808	4520		
1812	4532		
1825	4564		20,000
2220	5650		
2225	5664		

<sup>1</sup> The "Packaging C-Spec" is a 4 to 8 digit code which identifies the packaging type and/or product grade. When ordering, the proper code must be included in the 15th through 22nd character positions of the ordering code. See "Ordering Information" section of this document for further details. Commercial Grade product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging. Contact KEMET if you require a bulk bag packaging option for Automotive Grade products.

<sup>2</sup> A packaging C-Spec (see note 1 above) is not required for "Bulk Bag" packaging (excluding Anti-Static Bulk Bag and Automotive Grade products). The 15th through 22nd character positions of the ordering code should be left blank. All product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging.



### Table 3 – Chip Capacitor Land Pattern Design Recommendations per IPC-7351


EIA Size Code	Metric Size Code	I	Maxi	sity Lev mum (I rotrusio		)		Media	sity Lev an (Nor rotrusio	ninal)	)			sity Lev mum (L rotrusio	.east)	)
ooue	ooue	C	Y	X	V1	V2	C	Y	X	V1	V2	C	Y	X	V1	V2
0201	0603	0.38	0.56	0.52	1.80	1.00	0.33	0.46	0.42	1.50	0.80	0.28	0.36	0.32	1.20	0.60
0402	1005	0.50	0.72	0.72	2.20	1.20	0.45	0.62	0.62	1.90	1.00	0.40	0.52	0.52	1.60	0.80
0603	1608	0.90	1.15	1.10	4.00	2.10	0.80	0.95	1.00	3.10	1.50	0.60	0.75	0.90	2.40	1.20
0805	2012	1.00	1.35	1.55	4.40	2.60	0.90	1.15	1.45	3.50	2.00	0.75	0.95	1.35	2.80	1.70
1206	3216	1.60	1.35	1.90	5.60	2.90	1.50	1.15	1.80	4.70	2.30	1.40	0.95	1.70	4.00	2.00
1210	3225	1.60	1.35	2.80	5.65	3.80	1.50	1.15	2.70	4.70	3.20	1.40	0.95	2.60	4.00	2.90
1210 <sup>1</sup>	3225	1.50	1.60	2.90	5.60	3.90	1.40	1.40	2.80	4.70	3.30	1.30	1.20	2.70	4.00	3.00
1808	4520	2.30	1.75	2.30	7.40	3.30	2.20	1.55	2.20	6.50	2.70	2.10	1.35	2.10	5.80	2.40
1812	4532	2.15	1.60	3.60	6.90	4.60	2.05	1.40	3.50	6.00	4.00	1.95	1.20	3.40	5.30	3.70
1825	4564	2.15	1.60	6.90	6.90	7.90	2.05	1.40	6.80	6.00	7.30	1.95	1.20	6.70	5.30	7.00
2220	5650	2.75	1.70	5.50	8.20	6.50	2.65	1.50	5.40	7.30	5.90	2.55	1.30	5.30	6.60	5.60
2225	5664	2.70	1.70	6.90	8.10	7.90	2.60	1.50	6.80	7.20	7.30	2.50	1.30	6.70	6.50	7.00

#### <sup>1</sup> Only for capacitance values $\geq$ 22 $\mu$ F

**Density Level A:** For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes. KEMET only recommends wave soldering of EIA 0603, 0805 and 1206 case sizes.

**Density Level B:** For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes. **Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC Standard 7351 (IPC-7351).

Image below based on Density Level B for an EIA 1210 case size.





## **Soldering Process**

#### **Recommended Soldering Technique:**


- Solder wave or solder reflow for EIA case sizes 0603, 0805 and 1206
- · All other EIA case sizes are limited to solder reflow only

#### **Recommended Reflow Soldering Profile:**

KEMET's families of surface mount multilayer ceramic capacitors (SMD MLCCs) are compatible with wave (single or dual), convection, IR or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/ J-STD-020 standard for moisture sensitivity testing. These devices can safely withstand a maximum of three reflow passes at these conditions.

Profile Feature	Termination Finish			
Tomereature	SnPb	100% Matte Sn		
Preheat/Soak				
Temperature Minimum (T <sub>Smin</sub> )	100°C	150°C		
Temperature Maximum (T <sub>Smax</sub> )	150°C	200°C		
Time ( $t_s$ ) from $T_{smin}$ to $T_{smax}$	60 – 120 seconds	60 – 120 seconds		
Ramp-Up Rate $(T_L to T_P)$	3°C/second maximum	3°C/second maximum		
Liquidous Temperature $(T_L)$	183°C	217°C		
Time Above Liquidous $(t_L)$	60 – 150 seconds	60 – 150 seconds		
Peak Temperature (T <sub>P</sub> )	235°C	260°C		
Time Within 5°C of Maximum Peak Temperature (t <sub>P</sub> )	20 seconds maximum	30 seconds maximum		
Ramp-Down Rate $(T_{P} to T_{L})$	6°C/second maximum	6°C/second maximum		
Time 25°C to Peak Temperature	6 minutes maximum	8 minutes maximum		

Note 1: All temperatures refer to the center of the package, measured on the capacitor body surface that is facing up during assembly reflow.





## Table 4 – Performance & Reliability: Test Methods and Conditions


Stress	Reference	Test or Inspection Method
Terminal Strength	JIS-C-6429	Appendix 1, Note: Force of 1.8 kg for 60 seconds.
Board Flex	JIS-C-6429	Appendix 2, Note: Standard termination system – 2.0 mm (minimum) for all except 3 mm for COG. Flexible termination system – 3.0 mm (minimum).
		Magnification 50 X. Conditions:
Solderability	J-STD-002	a) Method B, 4 hours at 155°C, dry heat at 235°C
Soluerability	J-STD-002	b) Method B at 215°C category 3
		c) Method D, category 3 at 260°C
Temperature Cycling	JESD22 Method JA-104	1,000 Cycles (-55°C to +125°C). Measurement at 24 hours +/- 4 hours after test conclusion.
Biased Humidity	MIL-STD-202 Method 103	Load Humidity: 1,000 hours 85°C/85% RH and rated voltage. Add 100 K ohm resistor. Measurement at 24 hours +/- 4 hours after test conclusion. Low Volt Humidity: 1,000 hours 85°C/85% RH and 1.5 V. Add 100 K ohm resistor.
		Measurement at 24 hours +/- 4 hours after test conclusion.
Moisture Resistance	MIL-STD-202 Method 106	t = 24 hours/cycle. Steps 7a and 7b not required. Measurement at 24 hours +/- 4 hours after test conclusion.
Thermal Shock	MIL-STD-202 Method 107	–55°C/+125°C. Note: Number of cycles required – 300, maximum transfer time – 20 seconds, dwell time – 15 minutes. Air – Air.
High Temperature Life	MIL-STD-202 Method 108 /EIA-198	1,000 hours at 125°C (85°C for X5R, Z5U and Y5V) with 2 X rated voltage applied.
Storage Life	MIL-STD-202 Method 108	150°C, 0 VDC for 1,000 hours.
Vibration	MIL-STD-202 Method 204	5 g's for 20 minutes, 12 cycles each of 3 orientations. Note: Use 8" X 5" PCB 0.031" thick 7 secure points on one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from 10 – 2,000 Hz
Mechanical Shock	MIL-STD-202 Method 213	Figure 1 of Method 213, Condition F.
Resistance to Solvents	MIL-STD-202 Method 215	Add aqueous wash chemical, OKEM Clean or equivalent.

## Storage and Handling

Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature–reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 70% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within 1.5 years of receipt.



## Construction



## **Capacitor Marking (Optional):**

Laser marking option is not available on:


- COG, Ultra Stable X8R and Y5V dielectric devices
- · EIA 0402 case size devices
- EIA 0603 case size devices with Flexible Termination option.
- KPS Commercial and Automotive grade stacked devices.

These capacitors are supplied unmarked only.



## **Tape & Reel Packaging Information**

KEMET offers multilayer ceramic chip capacitors packaged in 8, 12 and 16 mm tape on 7" and 13" reels in accordance with EIA Standard 481. This packaging system is compatible with all tape-fed automatic pick and place systems. See Table 2 for details on reeling quantities for commercial chips.



## Table 5 – Carrier Tape Configuration, Embossed Plastic & Punched Paper (mm)

	Таре	Embosse	d Plastic	Punched Paper		
EIA Case Size	-	7" Reel	13" Reel	7" Reel	13" Reel	
		Pitch (P <sub>1</sub> )*		Pitch (P <sub>1</sub> )*		
01005 - 0402	8			2	2	
0603	8			2/4	2/4	
0805	8	4	4	4	4	
1206 - 1210	8	4	4	4	4	
1805 - 1808	12	4	4			
≥ 1812	12	8	8			
KPS 1210	12	8	8			
KPS 1812 and 2220	16	12	12			
Array 0612	8	4	4			

\*Refer to Figures 1 and 2 for W and P<sub>1</sub> carrier tape reference locations. \*Refer to Tables 6 and 7 for tolerance specifications.

#### New 2 mm Pitch Reel Options\*

Packaging Ordering Code (C-Spec)	Packaging Type/Options
C-3190	Automotive grade 7" reel unmarked
C-3191	Automotive grade 13" reel unmarked
C-7081	Commercial grade 7" reel unmarked
C-7082	Commercial grade 13" reel unmarked


\* 2 mm pitch reel only available for 0603 EIA case size. 2 mm pitch reel for 0805 EIA case size under development.

#### Benefits of Changing from 4 mm to 2 mm Pitching Spacing

- Lower placement costs.
- Double the parts on each reel results in fewer reel changes and increased efficiency.
- Fewer reels result in lower packaging, shipping and storage costs, reducing waste.



## Figure 1 – Embossed (Plastic) Carrier Tape Dimensions



# Table 6 – Embossed (Plastic) Carrier Tape Dimensions

Metric will govern

	Constant Dimensions – Millimeters (Inches)								
Tape Size	D <sub>0</sub>	D <sub>1</sub> Minimum Note 1	E <sub>1</sub>	P <sub>0</sub>	P <sub>2</sub>	R Reference Note 2	S <sub>1</sub> Minimum Note 3	T Maximum	T <sub>1</sub> Maximum
8 mm		1.0 (0.039)				25.0 (0.984)			
12 mm	1.5 +0.10/-0.0 (0.059 +0.004/-0.0)	1.5	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	30	0.600 (0.024)	0.600 (0.024)	0.100 (0.004)
16 mm		(0.059)				(1.181)			
	Variable Dimensions – Millimeters (Inches)								
Tape Size     Pitch     B1 Maximum Note 4     E2 Minimum     F     P1     T2 Maximum     W Maximum     A0,B0 & K0							& K <sub>0</sub>		
8 mm	Single (4 mm)	4.35 (0.171)	6.25 (0.246)	3.5 ±0.05 (0.138 ±0.002)	4.0 ±0.10 (0.157 ±0.004)	2.5 (0.098)	8.3 (0.327)		
12 mm	Single (4 mm) and double (8 mm)	8.2 (0.323)	10.25 (0.404)	5.5 ±0.05 (0.217 ±0.002)	8.0 ±0.10 (0.315 ±0.004)	4.6 (0.181)	12.3 (0.484)	Not	ie 5
16 mm	Triple (12 mm)	12.1 (0.476)	14.25 (0.561)	7.5 ±0.05 (0.138 ±0.002)	12.0 ±0.10 (0.157 ±0.004)	4.6 (0.181)	16.3 (0.642)		

1. The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of the embossment location and the hole location shall be applied independently of each other.

2. The tape with or without components shall pass around R without damage (see Figure 6.)

3. If S<sub>1</sub> < 1.0 mm, there may not be enough area for a cover tape to be properly applied (see EIA Standard 481, paragraph 4.3, section b.)

4. B, dimension is a reference dimension for tape feeder clearance only.

5. The cavity defined by  $A_{\mu}$ ,  $B_{\mu}$  and  $K_{\mu}$  shall surround the component with sufficient clearance that:

(a) the component does not protrude above the top surface of the carrier tape.

(b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.

(c) rotation of the component is limited to 20° maximum for 8 and 12 mm tapes and 10° maximum for 16 mm tapes (see Figure 3.)

(d) lateral movement of the component is restricted to 0.5 mm maximum for 8 and 12 mm wide tape and to 1.0 mm maximum for 16 mm tape (see Figure 4.)


(e) for KPS product,  $A_{a}$  and  $B_{a}$  are measured on a plane 0.3 mm above the bottom of the pocket.

(f) see addendum in EIA Standard 481 for standards relating to more precise taping requirements.

© KEMET Electronics Corporation • P.O. Box 5928 • Greenville, SC 29606 • 864-963-6300 • www.kemet.com



## Figure 2 – Punched (Paper) Carrier Tape Dimensions



# Table 7 – Punched (Paper) Carrier Tape Dimensions

Metric will govern

	Constant Dimensions – Millimeters (Inches)							
Tape Size	D <sub>0</sub>	E <sub>1</sub>	P <sub>0</sub>	P <sub>2</sub>	T <sub>1</sub> Maximum	G Minimum	R Reference Note 2	
8 mm	1.5 +0.10 -0.0 (0.059 +0.004 -0.0)	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	0.10 (0.004) maximum	0.75 (0.030)	25 (0.984)	
	Variable Dimensions – Millimeters (Inches)							
Tape Size	Tape Size         Pitch         E2 Minimum         F         P1         T Maximum         W Maximum         A0B0							
8 mm	Half (2 mm)	6.25	3.5 ±0.05	2.0 ±0.05 (0.079 ±0.002)	1.1	8.3 (0.327)	Note 1	
8 mm	Single (4 mm)	(0.246)	(0.138 ±0.002)	4.0 ±0.10 (0.157 ±0.004)	(0.098)	8.3 (0.327)	NOLE I	

1. The cavity defined by  $A_{\alpha}$ ,  $B_{\alpha}$  and T shall surround the component with sufficient clearance that:

a) the component does not protrude beyond either surface of the carrier tape.

b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.

c) rotation of the component is limited to 20° maximum (see Figure 3.)

d) lateral movement of the component is restricted to 0.5 mm maximum (see Figure 4.)

e) see addendum in EIA Standard 481 for standards relating to more precise taping requirements.

2. The tape with or without components shall pass around R without damage (see Figure 6.)



## **Packaging Information Performance Notes**


- 1. Cover Tape Break Force: 1.0 kg minimum.
- 2. Cover Tape Peel Strength: The total peel strength of the cover tape from the carrier tape shall be:

Tape Width	Peel Strength
8 mm	0.1 to 1.0 newton (10 to 100 gf)
12 and 16 mm	0.1 to 1.3 newton (10 to 130 gf)


The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be  $165^{\circ}$  to  $180^{\circ}$  from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of  $300 \pm 10$  mm/minute.

**3. Labeling:** Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. *Refer to EIA Standards 556 and 624*.


#### Figure 3 – Maximum Component Rotation



## Figure 4 – Maximum Lateral Movement




## Figure 5 – Bending Radius





## **Figure 6 – Reel Dimensions**



Note: Drive spokes optional; if used, dimensions B and D shall apply.


## Table 8 – Reel Dimensions

Metric will govern

	Constant Dimensions — Millimeters (Inches)							
Tape Size	А	B Minimum	С	D Minimum				
8 mm	178 ±0.20		13.0 +0.5/-0.2 (0.521 +0.02/-0.008)	20.2 (0.795)				
12 mm	(7.008 ±0.008) or	1.5 (0.059)						
16 mm	330 ±0.20 (13.000 ±0.008)							
	Variable Dimensions – Millimeters (Inches)							
Tape Size	N Minimum	W <sub>1</sub>	W <sub>2</sub> Maximum	W <sub>3</sub>				
8 mm		8.4 +1.5/-0.0 (0.331 +0.059/-0.0)	14.4 (0.567)					
12 mm	50 (1.969)	12.4 +2.0/-0.0 (0.488 +0.078/-0.0)	18.4 (0.724)	Shall accommodate tape width without interference				
16 mm		16.4 +2.0/-0.0 (0.646 +0.078/-0.0)	22.4 (0.882)					



## Figure 7 – Tape Leader & Trailer Dimensions



# Figure 8 – Maximum Camber





## **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit www.kemet.com/sales.

### Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.

KEMET is a registered trademark of KEMET Electronics Corporation.