

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 1825058, 1825058
 © COPYRIGHT 1825058 By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	S2	REVISED PER ECO-15-006450	28APR2015	NK	RH
	S3	REVISED PER ECO-16-018654	15MAY2017	RK	PO

SPECIFICATIONS:


MATERIAL
 BASE, PPS, UL94V-0, BLACK
 COVER, PPS, UL94V-0, BLACK
 ACTUATOR, PA6T, UL94V-0, WHITE
 FIXED CONTACT/TERMINAL, CU ALLOY-GOLD FLASH OVER NICKEL
 MOVING CONTACT, CU ALLOY, PLATE-GOLD FLASH/NICKEL

ELECTRICAL
 MAX CONTACT RATING SWITCHING, 100MILLIAMP @ 24 VDC
 MIN CONTACT RATING SWITCHING, .1MICROAMP @ 1 MILLIVOLT
 MAX CONTACT NON-SWITCHING, 1AMP @ 5 VDC
 INITIAL CONTACT RESISTANCE, 50 MILLIOHMS MAX.
 CONTACT RESISTANCE (AFTER ENVIRONMENTAL TEST), 100 MILLIOHMS
 CONTACT RESISTANCE (AFTER GAS TEST), 300 MILLIOHMS
 INSULATION RESISTANCE, 1,000 MEGOHMS MIN. @ 100 VDC
 DIELECTRIC STRENGTH, 500 VAC RMS @ SEA LEVEL
 LIFE EXPECTANCY, 1,000 CYCLES

MECHANICAL
 OPERATING FORCE, LESS THAN 800 GRAMS
 CONTACT PRESSURE, 280,000 PSI

ENVIRONMENTAL
 OPERATING TEMPERATURE, -30 TO +85 DEGREES C
 STORAGE TEMPERATURE, -45 TO +105 DEGREES C
 CLEANING, AQUEOUS OR SOLVENT
 SOLDER HEAT RESISTANCE, PER 109-201, COND B, SWITCH "OFF".
 SOLDERABILITY PER JIS C 0050 & JIS C 0053

- SWITCHES TO BE RECEIVED IN THE "OFF" POSITION AND PACKAGED IN CLEAR TUBES TO ACCOMMODATE AUTO-INSERTION.
- TOP SURFACE TO BE CLEARLY MARKED AS SHOWN.
- SWITCHES TO BE BLACK WITH WHITE ACTUATORS AND MARKINGS.
- △ TERMINAL OPTION: OLD T&B P/N ADExxS, SA OR SB
 S= OUTSIDE "L" TERMINALS; SA= INSIDE "L" TERMINALS;
 SB= BUTT TERMINALS.
- ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS).
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.
- △ TAPE AND REEL PACKING PER PAGE 3 SPECIFICATIONS.




SEE SHEET 2 FOR PART NUMBER TABLE AND MOUNTING OPTIONS


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.S.VISWESWARA 10FEB05	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK M.SARVER			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.SARVER	PRODUCT SPEC		
0 PLC ± - 1 PLC ± - 2 PLC ± 0.30[012] 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC		RESTRICTED TO	
MATERIAL		WEIGHT	SIZE A2	CAGE CODE -	DRAWING NO C-1825058
FINISH		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 3
				REV S3	

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 1825058, 1825058
 © COPYRIGHT 1825058 By - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




SURFACE MOUNT S (OUTSIDE "L")



RECOMMENDED PAD LAYOUT



SURFACE MOUNT SA (INSIDE "L")



RECOMMENDED PAD LAYOUT

OBSOLETE	ADE12STR04	3.61 [.142]	32.51 [1.280]	12	4-1825058-1	
	ADE10STR04	3.50 [.138]	27.30 [1.075]	10	4-1825058-0	
	ADE09STR04	3.50 [.138]	24.54 [.978]	9	3-1825058-9	
	ADE08STR04	3.50 [.138]	22.30 [.878]	8	3-1825058-8	
OBSOLETE	ADE07STR04	3.50 [.138]	19.76 [.778]	7	3-1825058-7	
OBSOLETE	ADE06STR04	3.50 [.138]	17.22 [.678]	6	3-1825058-6	
OBSOLETE	ADE05STR04	3.50 [.138]	14.68 [.578]	5	3-1825058-5	
OBSOLETE	ADE04STR04	3.50 [.138]	12.14 [.478]	4	3-1825058-4	
OBSOLETE	ADE03STR04	3.50 [.138]	9.60 [.378]	3	3-1825058-3	
△7	ADE04SATR04	3.50 [.138]	7.00 [.276]	2	3-1825058-2	
OBSOLETE	ADE12SB04	3.61 [.142]	32.51 [1.280]	12	3-1825058-0	
OBSOLETE	ADE12SA04	3.61 [.142]	32.51 [1.280]	12	2-1825058-9	
OBSOLETE	ADE12S04	3.61 [.142]	32.51 [1.280]	12	2-1825058-8	
OBSOLETE	ADE10SB04	3.50 [.138]	27.30 [1.075]	10	2-1825058-7	
OBSOLETE	ADE10SA04	3.50 [.138]	27.30 [1.075]	10	2-1825058-6	
	ADE10S04	3.50 [.138]	27.30 [1.075]	10	2-1825058-5	
	ADE09SB04	3.50 [.138]	24.54 [.978]	9	2-1825058-4	
	ADE09SA04	3.50 [.138]	24.54 [.978]	9	2-1825058-3	
	ADE09S04	3.50 [.138]	24.54 [.978]	9	2-1825058-2	
OBSOLETE	ADE08SB04	3.50 [.138]	22.30 [.878]	8	2-1825058-1	
	ADE08SA04	3.50 [.138]	22.30 [.878]	8	2-1825058-0	
	ADE08S04	3.50 [.138]	22.30 [.878]	8	1-1825058-9	
OBSOLETE	ADE07SB04	3.50 [.138]	19.76 [.778]	7	1-1825058-8	
△6	ADE07SA04	3.50 [.138]	19.76 [.778]	7	1-1825058-7	
	ADE07S04	3.50 [.138]	19.76 [.778]	7	1-1825058-6	
OBSOLETE	ADE06SB04	3.50 [.138]	17.22 [.678]	6	1-1825058-5	
OBSOLETE	ADE06SA04	3.50 [.138]	17.22 [.678]	6	1-1825058-4	
	ADE06S04	3.50 [.138]	17.22 [.678]	6	1-1825058-3	
OBSOLETE	ADE05SB04	3.50 [.138]	14.68 [.578]	5	1-1825058-2	
△6	ADE05SA04	3.50 [.138]	14.68 [.578]	5	1-1825058-1	
	ADE05S04	3.50 [.138]	14.68 [.578]	5	1-1825058-0	
OBSOLETE	ADE04SB04	3.50 [.138]	12.14 [.478]	4	1825058-9	
OBSOLETE	ADE04SA04	3.50 [.138]	12.14 [.478]	4	1825058-8	
	ADE04S04	3.50 [.138]	12.14 [.478]	4	1825058-7	
△6	OBSOLETE	ADE03SB04	3.50 [.138]	9.60 [.378]	3	1825058-6
OBSOLETE	ADE03SA04	3.50 [.138]	9.60 [.378]	3	1825058-5	
	ADE03S04	3.50 [.138]	9.60 [.378]	3	1825058-4	
OBSOLETE	ADE02SB04	3.50 [.138]	7.00 [.276]	2	1825058-3	
OBSOLETE	ADE02SA04	3.50 [.138]	7.00 [.276]	2	1825058-2	
	ADE02S04	3.50 [.138]	7.00 [.276]	2	1825058-1	
	T&B P/N	DIM H	DIM L	POSITION	PART NO.	






THIS DRAWING IS A CONTROLLED DOCUMENT. DWN B.S.VISWESWARA 10FEB05
 CHK M.SARVER
 APVD M.SARVER
 PRODUCT SPEC
 APPLICATION SPEC
 WEIGHT -

STE TE Connectivity
 DIP SWITCH, ADE-SMT SERIES

SIZE A2 CAGE CODE - DRAWING NO. C-1825058 RESTRICTED TO -
 SCALE 4:1 SHEET 2 OF 3 REV S3

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 1825058, 1825058
 © COPYRIGHT 1825058 By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



	DESCRIPTION	MATERIAL	DIMENSION	FINISH	REMARKS
1	REEL	SIDE: CARDBOARD CORE: STYLOFOAM	MENTIONED BELOW		
2	EMBOSSSED TAPE	-	MENTIONED BELOW	ANTISTATIC	BLACK
3	TOP COVER TAPE	-	MENTIONED BELOW	ANTISTATIC	TRANSPARENT

4P	$\phi 330.00 \pm 2.10$ [12.992 ± .082]	$\phi 100$ [3.940]	$24.40 \begin{smallmatrix} +2.00 \\ -0.000 \end{smallmatrix}$ [.960 ± .000]	30.40 [1.997]
NO OF POSITION	A	N (MIN)	W1	W2 (MAX)

4P	$\phi 1.50 \begin{smallmatrix} +0.10 \\ -0.000 \end{smallmatrix}$ [.059 ± .003]	4.00 ± 0.10 [.157 ± .003]	16.00 ± 0.10 [.629 ± .003]	2.00 ± 0.15 [.078 ± .005]	11.50 ± 0.10 [.453 ± .003]	7.40 ± 0.10 [.291 ± .003]
NO OF POSITION	D1	P0	P1	P2	F	K

4P	24.00 ± 0.30 [.944 ± .011]	12.90 ± 0.10 [.507 ± .003]	1.75 ± 0.10 [.068 ± .003]	0.50 ± 0.05 [.020 ± .001]	12.14 ± 0.50 [.477 ± .020]	$\phi 1.50 \begin{smallmatrix} +0.10 \\ -0.000 \end{smallmatrix}$ [.059 ± .003]
NO OF POSITION	W	B	E	T	L	DO

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN B.S.VISWESWARA 10FEB05
 CHK M.SARVER
 APVD M.SARVER
 PRODUCT SPEC
 APPLICATION SPEC
 WEIGHT -

STE TE Connectivity
 DIP SWITCH, ADE-SMT SERIES

SIZE A2 CAGE CODE - DRAWING NO C-1825058 RESTRICTED TO -
 SCALE 4:1 SHEET 3 OF 3 REV S3