

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0010897100**  
**Status:** **Active**  
**Overview:** C-Grid Connector Products  
**Description:** 2.54mm Pitch C-Grid Breakaway Header, Dual Row, Vertical, High Temperature, 10 Circuits, 0.76µm Gold (Au) Selective Plating, Tin (Sn) PC Tail Plating, 2.72mm PC Tail

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-70280-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-70873-0353-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**


CSA	LR19980
UL	E29179

**General**

Product Family	PCB Headers
Series	<u>70280</u>
Application	Board-to-Board, Signal, Wire-to-Board
Overview	<u>C-Grid Connector Products</u>
Product Name	C-Grid
UPC	800755021684

**Physical**

Breakaway	Yes
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.598/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.79mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.813µm
Plating min - Termination	2.032µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
D(2020)4578-DC (25  
June 2020)  
henicosaflluoroundecanoic  
acid  
disodium 4-  
amino-3-[[4'-[(2,4-  
diaminophenyl)azo]  
chromium trioxide  
1,3-propanesultone  
1-vinylimidazole  
4,4'-methylenedi-o-  
toluidine  
dibutyltin dichloride  
methoxyacetic acid  
diisopentylphthalate  
disodium 3,3'-[[1,1'-  
biphenyl]-4,4'-  
diylbis(azo)  
octamethylcyclotetrasiloxane  
benzene-1,2,4-  
tricarboxylic acid 1,2-  
anhydride  
decamethylcyclopentasiloxane  
dodecamethylcyclohexasiloxane  
heptacosaflluorotetradecanoic  
acid  
tricosaflluorododecanoic  
acid  
di-n-pentyl phthalate  
(DPP)  
6-methoxy-m-toluidine  
furan  
1-bromopropane  
nitrobenzene  
4-o-tolylazo-o-  
toluidine  
ethylene thiourea

**China RoHS**

**Electrical**

Current - Maximum per Contact 3.0A  
Voltage - Maximum 250V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 030  
Lead-free Process Capability SMC&WAVE  
Max. Cycles at Max. Process Temperature 003  
Process Temperature max. C 260

**Material Info**

Engineering Number A-70280-0085

**Reference - Drawing Numbers**

Packaging Specification PK-70873-0353-001  
Product Specification PS-70280-001  
Sales Drawing SDA-70280-0001-4000-

4-methyl-m-phenylenediamine  
o-toluidine  
butyl 4-hydroxybenzoate  
dinoseb (ISO)  
dihexyl phthalate (DnHP)  
dicyclohexyl phthalate  
N-methylacetamide  
dimethyl sulphate  
diethyl sulphate  
4-aminoazobenzene  
Fatty acids, C16-18, lead salts  
[phthalato(2-)]dioxotrilead  
Silicic acid (H<sub>2</sub>Si<sub>2</sub>O<sub>5</sub>), barium salt (1:1), lead-  
Perfluorohexane-1-sulphonic acid and its salts  
5-sec-butyl-2-(2,4-dimethylcyclohex-3-en-1-yl)-5  
1,2-benzenedicarboxylic acid, di-C<sub>6</sub>-10-alkyl est  
Cadmium sulphate  
Sodium perborate; perboric acid, sodium salt  
hexahydro-2-benzofuran-1,3-dione  
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated  
Perfluorononan-1-oic acid  
(2,2,3,3,4,4,5,5,6,6,7  
Reaction  
products of 1,3,4-thiadiazolidine-2,5-d  
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o  
Chrysene  
Cadmium nitrate  
Pyrene  
Tris(4-nonylphenyl, branched and linear)  
phosphi  
2,3,3,3-tetrafluoro-2-(heptafluoropropoxy)propio  
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated  
Trixylyl phosphate  
Zirconia  
Aluminosilicate  
Refractory Ceramic  
Fibr  
Aluminosilicate  
Refractory Ceramic  
Fibres  
Boric acid

Disodium tetraborate  
Hydrazine  
1,3-BENZENEDIOL,  
TRINITRO-, LEAD  
SALT  
n-pentyl-  
isopentylphthalate  
3-ethyl-2-methyl-2-  
(3-methylbutyl)-1,3-  
oxazolidi  
1,2-  
benzenedicarboxylic  
acid, dipentylester,  
bra  
pentacosafuorotridecanoic  
acid  
1,2-  
Benzenedicarboxylic  
acid, dihexyl ester,  
bra  
Terphenyl,  
hydrogenated  
2-(2H-benzotriazol-2-  
yl)-4-(tert-butyl)-6-  
(sec-b  
2-(2H-benzotriazol-2-  
yl)-4,6-  
ditertpentylphenol  
dibutylbis(pentane-2,4-  
dionato-O,O')tin  
2-ethylhexyl 10-  
ethyl-4,4-dioctyl-7-  
oxo-8-oxa-3,  
disodium octaborate  
sodium  
peroxometaborate  
ammoniumpentadecafluorooctanoate  
pentazinc chromate  
octahydroxide  
1,2-dichloroethane  
trilead diarsenate  
2-methoxyaniline  
arsenic acid  
N,N-  
dimethylacetamide  
lead dipicrate  
potassium  
hydroxyoctaoxidizincatedichromate(1-)  
bis(2-methoxyethyl)  
ether  
calcium arsenate  
1,2-  
benzenedicarboxylic  
acid; di-C6-8-  
branched a  
N-methyl-2-  
pyrrolidone  
1,2-  
benzenedicarboxylic  
acid; di-C7-11-  
branched  
2-ethoxyethyl acetate  
cobalt sulphate  
cobalt di(acetate)  
cobalt carbonate

tetraboron disodium  
heptaoxide, hydrate  
sodium chromate  
potassium dichromate  
potassium chromate  
ammonium  
dichromate  
tris(2-chloroethyl)  
phosphate  
Lead sulfochromate  
yellow  
Lead chromate  
molybdate sulfate red  
lead chromate  
Anthracene oil,  
anthracene-low;  
Anthracene Oil F  
Anthracene oil,  
anthracene paste,  
distn. lights;  
Anthracene oil,  
anthracene paste,  
anthracene fra  
Anthracene oil,  
anthracene paste;  
Anthracene Oil  
Butylbenzylphthalate  
(BBP)  
lead hydrogen  
arsenate  
bis(2-ethylhexyl)  
phthalate (DEHP)  
dibutyl phthalate  
(DBP)  
4,4'-  
diaminodiphenylmethane  
triethyl arsenate  
Sulfurous acid, lead  
salt, dibasic  
Acetic acid, lead salt,  
basic  
cadmium hydroxide  
Lead titanium  
zirconium oxide  
dioxobis(stearato)trilead  
tetralead trioxide  
sulphate  
trilead dioxide  
phosphonate  
pentalead tetraoxide  
sulphate  
lead oxide sulfate  
Silicic acid, lead salt  
cadmium chloride  
lead dinitrate  
pyrochlore, antimony  
lead yellow  
cadmium fluoride  
cadmium  
lead  
 $\alpha,\alpha'$ Bis[4-  
(dimethylamino)phenyl]-4  
(phenylamino)

[4-[[4-anilino-1-naphthyl][4-(dimethylamino)phenyl,3,5-tris(oxiranylmethyl)-1,3,5-triazine-2,4,6(Lead oxide trilead bis(carbonate) dihydroxide orange lead cadmium sulphide cadmium oxide (non-pyrophoric) diboron trioxide bis(pentabromophenyl) ether 4,4'-bis(dimethylamino)-4''-(methylamino)trityl [4-[4,4'-bis(dimethylamino)benzhydrylidene]cycl cadmium carbonate 1,2-dimethoxyethane 4,4'-bis(dimethylamino)benzophenone dichromium tris(chromate) phenolphthalein lead diazide bis(2-methoxyethyl) phthalate Formaldehyde, polymer with benzenamine

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[70280 Series](#)

This document was generated on 10/14/2020

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**