



RS Part Number: **9143957**
 Europa Part Number: **ECPF08**
 Specifications and dimensions

- Three Phase Monitor
- Phase Failure
- Over/Under voltage



Features	
Height	90mm
Width	18mm
Depth	64mm
Weight	0.064Kg
Cover ingress protection	IP40 cover; IP20 terminals
Standards	EN 60255-6
	EN 61010-1
Output contact	10AAC1; SPCO
Voltage Range	220-230-240-380-400-415-440-460
Rated supply Frequency	45 - 65 Hz
Measuring Range	176 - 552 V
Threshold Adjustment Voltage	2% - 20% Un selectable
Threshold Adjustment Asymmetry	8%
Hysteresis	2%
Phase Failure Value	70% of Un selectable
Time Delay	2s
Reset Time	1s
Electrical life AC1	1 x 10 ⁶
Mechanical life	1 x 10 ⁷
Operating temperature	,-20°C to +55°C
Maximum Cable	2.5mm ²

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>