

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022057028](#)
Status: **Active**
Overview:
Description: KK 254 Wire-to-Board Header, Right-Angle, with Friction Lock, 2 Circuits

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	7395
Application	Signal, Wire-to-Board
Overview	kk_interconnect_solutions
Product Name	KK 254
UPC	800753739451

Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural (White)
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.254/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.80mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V

Solder Process Data

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
January 20

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[7395 Series](#)

Mates With

[2695](#) KK Crimp Terminal Housing, [6471](#)
KK Crimp Terminal Housing, [7720](#) KK IDT
Double Cantilever

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	A-7395-2B
--------------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-7478-001-000
Product Specification	PS-10-07-001, PS-99020-0088-001
Sales Drawing	SD-7395-001

This document was generated on 02/12/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION