

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022057035](#)
Status: **Active**
Overview:
Description: 2.50mm Pitch, Mini-SPOX PCB Header, Single Row, Through Hole, Tin Plating, Friction Lock, 3 Circuits, Bag, 3.50mm PC Tail Length

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	5268
Application	Signal, Wire-to-Board
Overview	minispox
Product Name	Mini-SPOX
UPC	800753592766

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	344.400/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.50mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Material Info

Engineering Number	5268-03A
--------------------	----------

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[5268](#) Series

Mates With

Mini-SPOX Receptacle Housing [5264](#)

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

SPK-5268-001-001

52641001-PS-000, PS-5264-001-001

52680001-SD-000

This document was generated on 05/18/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION