

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022057048](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK 254 Wire-to-Board Header, Right-Angle, with Friction Lock, 4 Circuits](#)

Documents:

3D Model	Product Specification PS-99020-0088-001 (PDF)
Drawing (PDF)	Packaging Specification PK-7478-001-000 (PDF)
Product Specification PS-10-07-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	7395
Application	Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK 254
UPC	800753739499

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural (White)
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.524/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.80mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[7395 Series](#)

Mates With

[2695](#) KK Crimp Terminal Housing, [6471](#)
KK Crimp Terminal Housing, [7720](#) KK IDT
Double Cantilever

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 500V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-free Process Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 235

Material Info

Engineering Number AE-7395-4B

Reference - Drawing Numbers

Packaging Specification PK-7478-001-000
Product Specification PS-10-07-001, PS-99020-0088-001
Sales Drawing SD-7395-001

This document was generated on 07/17/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION