

# 3.2x1.6mm SMD CHIP LED LAMP

Part Number: KP-3216SGC

Super Bright Green


### **Features**


- 3.2mmx1.6mm SMT LED, 1.1mm thickness.
- Low power consumption.
- Wide viewing angle.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 2000pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.


# **Description**

The Super Bright Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.


# **Package Dimensions**











- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.2(0.0079") unless otherwise noted.
- 3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice. 4.The device has a single mounting surface. The device must be mounted according to the specifications.





SPEC NO: DSAA6437 **REV NO: V.15B** DATE: FEB/29/2012 PAGE: 1 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.H.Wu ERP: 1203000404

# **Selection Guide**

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
			Min.	Тур.	201/2
KP-3216SGC	Super Bright Green (GaP)	Water Clear	5	12	120°

## Notes:

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
   Luminous intensity/ luminous Flux: +/-15%.
   Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

# Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Super Bright Green	565		nm	IF=20mA
λD [1]	Dominant Wavelength	Super Bright Green	568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Super Bright Green	30		nm	IF=20mA
С	Capacitance	Super Bright Green	15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Super Bright Green	2.2	2.5	V	I==20mA
lR	Reverse Current	Super Bright Green		10	uA	V <sub>R</sub> =5V


- Notes:
  1.Wavelength: +/-1nm.
  2.Forward Voltage: +/-0.1V.
  3.Wavelength value is traceable to the CIE127-2007 compliant national standards.

# Absolute Maximum Ratings at TA=25°C

Absolute maximum Natings at 1A 25 5					
Parameter	Super Bright Green	Units			
Power dissipation	62.5	mW			
DC Forward Current	25	mA			
Peak Forward Current [1]	140	mA			
Reverse Voltage	5	V			
Operating Temperature	-40°C To +85°C				
Storage Temperature	-40°C To +85°C				

Note: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAA6437 **REV NO: V.15B** DATE: FEB/29/2012 PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.H.Wu ERP: 1203000404





RELATIVE INTENSITY Vs. WAVELENGTH


Super Bright Green


**KP-3216SGC** 











**REV NO: V.15B** 

APPROVED: WYNEC CHECKED: Allen Liu

SPEC NO: DSAA6437

DATE: FEB/29/2012 DRAWN: Y.H.Wu


ERP: 1203000404

PAGE: 3 OF 5

# **KP-3216SGC**

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.



- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.


  2.Don't cause stress to the epoxy resin while it is exposed to high temperature.

  3.Number of reflow process shall be 2 times or less.


# **Recommended Soldering Pattern** (Units: mm; Tolerance: ± 0.1)



# **Reel Dimension**




# **Tape Dimensions** (Units: mm)





**SPEC NO: DSAA6437 REV NO: V.15B DATE: FEB/29/2012** PAGE: 4 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.H.Wu ERP: 1203000404

# **PACKING & LABEL SPECIFICATIONS**

# **KP-3216SGC**







SPEC NO: DSAA6437 **APPROVED: WYNEC** 

**REV NO: V.15B CHECKED: Allen Liu** 

DATE: FEB/29/2012 DRAWN: Y.H.Wu

PAGE: 5 OF 5 ERP: 1203000404