



REV	ECN	DATE	DESCRIPTION
A	32059	11/10/04	RELEASE DRAWING



- NOTES:
1. DIMENSIONS ARE INCHES[MILIMETERS]
 2. REPLACE " XX " IN THE PART NUMBER WITH THE TOTAL NUMBER OF PINS
 3. MATERIAL:
PINS: PHOSPHOR BRONZE 3/4 HARD
INSULATOR: HIGH TEMP THERMOPLASTIC UL 94V-0
PLATING:
0.000050 GOLD OVER
0.000050 NICKEL OVERALL
0.000100 TIN/DIPPED ON TAIL
 4. UNLESS OTHERWISE SPECIFIED ALL TOLERANCES ARE ±.005 (.13mm)
 5. PLATING TRANSITION AREA LESS THAN .015[.38]

THIS DRAWING AND THE INFORMATION THERE IN IS THE PROPERTY OF THE MUELLER ELECTRIC COMPANY AND MAY BE USED SOLELY FOR THE PROPOSE FOR WHICH IT IS SUBMITTED. IT IS TO BE TREATED IN CONFIDENCE. IT MAY NOT BE CIRCULATED, REPRODUCED OR DIVULGE TO OTHER PARTIES WITHOUT WRITTEN CONSENT OF MUELLER ELECTRIC INC. IT MUST BE RETURNED UPON REQUEST.

APPROVAL BLOCK		MUELLER ELECTRIC CO.	
YOUR SIGNATURE INDICATES APPROVAL OF THIS PART PER THIS DRAWING. NON-STANDARD, CUSTOMER SPECIFIC ORDERS ARE NON-RETURNABLE AND NON-CANCELABLE		1583 E. 31st ST. CLEVELAND, OH 44114	
SCALE: 8.000	DWG SIZE: B	APPROVED BY:	DRAWN BY: BILLXIE
REV DATE: 11/10/04		EDITED BY:	
PART NUMBER: SPEGXX-042-05-D-XX-MIL		FILE:	SPEGXX-042-05-D-XX-MIL
DESCRIPTION: DUAL ROW STRAIGHT HEADER		REV: A	SHEET NO. 1 OF 1
TOLERANCE: X, Y = ±0.1 X, XX = ±0.01 X, XXX = ±0.005 Y = ±0.1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[SPEG042-05D36](#)