



JKL PART NUMBER	- A - LENGTH	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mA rms)	BRIGHTNESS (CANDELA/m <sup>2</sup> )	*RATED LIFE (HRS) TYPICAL
BF2261-24B	61±1.5	RGB HIGH OUTPUT WHITE 8400° KELVIN	600 @ 0°C	200	5 ± 1	38,000±10%	50,000
BF22140-24B	140±3.0		990 @ 0°C	330	5 ± 1	38,000±10%	50,000
BF22160-24B	160±3.0		1065 @ 0°C	355	5 ± 1	38,000±10%	50,000
BF22258-24B	258 <sup>+3.0</sup> <sub>-0.0</sub>		1600 @ 0°C	535	5 ± 1	38,000±10%	50,000

\*NOTE: RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

		<b>METRIC</b> DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		<b>JKL COMPONENTS CORPORATION</b>			
D RATED LIFE HRS. TO TYPICAL & 20,000 TO 50,000 8/19/09 C ADD MINIMUM TO RATED LIFE HRS. 7/16/09 B ADD BF2261-24B 6/19/04 A CORRECTION ON LENGTH DIM. 10/7/03 RELEASED TO CAD MULTI LIST 8/18/03		THIRDS ANGLE PROJECTION DRAWN BY L. WENGSTROM APPV'D BY L.R. DATE 8/19/09		TITLE <b>MINIATURE COLD CATHODE FLUORESCENT LAMP</b>		SIZE <b>A</b> FSCM NO. <b>55335</b> DRAWING NO. <b>BF 22-24B</b>	
REV. NO. DESCRIPTION/ECO NUMBER APPV'D DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE <b>NONE</b>		RELEASED DATE 8/18/03 REVISION DATE 8/19/09 REV. NO. <b>D</b> SHEET <b>1</b> OF <b>1</b>	