

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039281163](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Family Power Connectors](#)  
**Description:** [Mini-Fit Jr. Vertical Header, 4.20mm Pitch, Dual Row, 16 Circuits, without Snap-in Plastic Peg PCB Lock, Tin, Natural](#)

**Documents:**

|   |   |
|---|---|
| <a href="#">3D Model (PDF)</a>                                  | <a href="#">Packaging Specification PK-5566-000 (PDF)</a>     |
| <a href="#">3D Model</a>  | <a href="#">Packaging Specification PK-5566-003-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                   | <a href="#">Test Summary TS-5556-002-001 (PDF)</a>            |
| <a href="#">Product Specification PS-5556-001-001 (PDF)</a>     | <a href="#">RoHS Certificate of Compliance (PDF)</a>          |
| <a href="#">Application Specification AS-5557-001-001 (PDF)</a> |   |

**Agency Certification**


|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |   |
|----------------|---|
| Product Family | PCB Headers   |
| Series         | <a href="#">5566</a>  |
| Application    | Power, Wire-to-Board  |
| Comments       | The 5566 header should be used with standard Mini-Fit female terminals. If increased amperage of up to 13A per circuit is needed, please consider using the Mini-Fit Plus HCS family <a href="#">45750</a> terminals with <a href="#">46015</a> headers; . See Molex Product specification PS-5666-001 for current de-rating information. |
| Overview       | <a href="#">Mini-Fit Family Power Connectors</a>  |
| Product Name   | Mini-Fit Jr.  |
| UPC            | 800753581630  |

**Physical**

|                                |          |
|--------------------------------|----------|
| Breakaway                      | No       |
| Circuits (Loaded)              | 16       |
| Circuits (maximum)             | 16       |
| Color - Resin                  | Natural  |
| Durability (mating cycles max) | 30       |
| First Mate / Last Break        | No       |
| Flammability                   | 94V-2    |
| Glow-Wire Capable              | No       |
| Guide to Mating Part           | No       |
| Keying to Mating Part          | None     |
| Lock to Mating Part            | Yes      |
| Material - Metal               | Brass    |
| Material - Plating Mating      | Tin      |
| Material - Plating Termination | Tin      |
| Material - Resin               | Nylon    |
| Net Weight                     | 4.234/g  |
| Number of Rows                 | 2        |
| Orientation                    | Vertical |
| PC Tail Length                 | 3.50mm   |
| PCB Locator                    | Yes      |
| PCB Retention                  | None     |
| PCB Thickness - Recommended    | 1.60mm   |
| Packaging Type                 | Bag      |
| Pitch - Mating Interface       | 4.20mm   |
| Pitch - Termination Interface  | 4.20mm   |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5566 Series](#)

**Mates With**

[5557](#) Mini-Fit Jr. Receptacle Housing, Mini-Fit TPA2 Receptacle Housing [172708](#)

|                                |                |
|--------------------------------|----------------|
| Plating min - Mating           | 0.889µm        |
| Plating min - Termination      | 0.889µm        |
| Polarized to Mating Part       | Yes            |
| Polarized to PCB               | Yes            |
| Shrouded                       | Fully          |
| Stackable                      | No             |
| Surface Mount Compatible (SMC) | No             |
| Temperature Range - Operating  | -40° to +105°C |
| Termination Interface: Style   | Through Hole   |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 9.0A |
| Voltage - Maximum             | 600V |

**Solder Process Data**

|  |      |
|--|------|
| Duration at Max. Process Temperature (seconds) | 005  |
| Lead-free Process Capability                   | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |
| Process Temperature max. C                     | 240  |

**Material Info**

|                    |          |
|--------------------|----------|
| Engineering Number | 5566-16A |
|--------------------|----------|

**Reference - Drawing Numbers**

|                           |                              |
|---------------------------|------------------------------|
| Application Specification | AS-5557-001-001              |
| Packaging Specification   | PK-5566-000, PK-5566-003-001 |
| Product Specification     | PS-5556-001-001              |
| Sales Drawing             | SD-5566-002-000              |
| Test Summary              | TS-5556-002-001              |

This document was generated on 01/20/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**