

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2002181700](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 16 AWG, Large and Small Insulation Grips

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Mini-Fit TPA2
Tool Type	Hand Crimp Tool
UPC	191128448642
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents [2002181700-000](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207129](#) Series

Application Tooling | **FAQ**

Description | **Product #**

Mini-Fit TPA2/ Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	1727181111
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag	1727181112
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Brass, Pre- Plated Tin (Sn), 16 AWG, 1.98-2.55mm	1727181121

Insulation Diameter,
Reel
Mini-Fit TPA2/ 1727181122
Sigma Female Crimp
Terminal, Brass, Pre-
Plated Tin (Sn), 16
AWG, 1.98-2.55mm
Insulation Diameter,
Bag
Mini-Fit TPA2/ 1727182111
Sigma Female Crimp
Terminal, Phosphor
Bronze, Pre-Plated
Tin (Sn), 16 AWG,
2.55-3.14mm
Insulation Diameter,
Reel
Mini-Fit TPA2/ 1727182112
Sigma Female Crimp
Terminal, Phosphor
Bronze, Pre-Plated
Tin (Sn), 16 AWG,
2.55-3.14mm
Insulation Diameter,
Bag
Mini-Fit TPA2/ 1727182121
Sigma Female Crimp
Terminal, Brass, Pre-
Plated Tin (Sn), 16
AWG, 2.55-3.14mm
Insulation Diameter,
Reel
Mini-Fit TPA2/ 1727182122
Sigma Female Crimp
Terminal, Brass, Pre-
Plated Tin (Sn), 16
AWG, 2.55-3.14mm
Insulation Diameter,
Bag
Mini-Fit TPA2/ 1727651121
Sigma Male Crimp
Terminal, Brass, Pre-
Plated Tin (Sn), 16
AWG, 1.98-2.55mm
Insulation Diameter,
Reel
Mini-Fit TPA2/ 1727651122
Sigma Male Crimp
Terminal, Brass, Pre-
Plated Tin (Sn), 16
AWG, 1.98-2.55mm
Insulation Diameter,
Bag
Mini-Fit TPA2/ 1727652121
Sigma Male Crimp
Terminal, Brass, Pre-
Plated Tin (Sn), 16
AWG, 2.55-3.14mm
Insulation Diameter,
Reel
Mini-Fit TPA2/ 1727652122
Sigma Male Crimp
Terminal, Brass, Pre-
Plated Tin (Sn), 16
AWG, 2.55-3.14mm

Insulation Diameter, Bag	
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post- Plated Gold (Au), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2029881141</u>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post- Plated Gold (Au), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag	<u>2029881142</u>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post- Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2029881241</u>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post- Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag	<u>2029881242</u>
Mini-Fit TPA2/ Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2030701141</u>
Mini-Fit TPA2/ Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2030701241</u>

This document was generated on 07/07/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION