



preci-dip

PCB CONNECTORS

**SERIES
351**

351-PP-1NN-00-XXX101

Single row

2.54 mm, Straight solder tail, Pin Ø 0.47 mm

Pin connectors, solder tail.



TECHNICAL SPECS.:

| | |
|----------------------------|--|
| Insulator | Black glass filled polyester PCT-GF30-FR |
| Flammability | UL 94V-O |
| Contact | Brass CuZn36Pb3 (C36000) |
| Connecting pin Ø | 0.47 mm |
| Mechanical life | Min. 500 cycles |
| Rated current | 3 A |
| Dielectric strength | Min. 1000 V RMS |

ORDERING INFORMATION:

| PP Plating code | Termination | Connecting pin |
|-----------------|--------------|----------------|
| 10 | Gold 0.25 µm | Gold 0.25 µm |
| 80 | Tin | Tin |

NN number of poles. Replace NN with the requested number of poles, e.g. 451-10-2NN-00-003101 for a double row version with 8 pins becomes 451-10-208-00-003101.

TECHNICAL ASSISTANCE

GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP socket and pin connectors. Please see individual catalog page for additional and product specific technical data.

| | |
|-----------------------------|---------------------------------|
| Operating temperature range | -55 ... +125 °C |
| Climatic category (IEC) | 55/125/21 |
| Operating humidity range | annual mean 75 % |
| Max working voltage | 100 VRMS/150 VDC (2.54 mm grid) |

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442

MECHANICAL CHARACTERISTICS:

| | |
|-----------------------------------|---|
| Clip retention | Min. 40 N (no displacement under axial force applied) |
| Contact (sleeve / clip) retention | Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2 |

ELECTRICAL CHARACTERISTICS:

| | |
|---|---------------------------|
| Insulation resistance between any two adjacent contacts | Min. 10'000 M at 500 V AC |
| Capacitance between any two adjacent contacts | Max. 1 pF |

Air and creepage distances between any two adjacent contacts :

| SERIES | 3xx/4xx/7xx | 80x | 83x | 85x | 86x |
|--------|-------------|------------|-----|-----------|-----|
| mm | 0.7 | 0.85 / 0.7 | 0.5 | 0.4 / 0.5 | 0.5 |

ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
 - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
 - 2) Sulfur dioxide (SO₂) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO₂, 25 °C, 75 %rH
 - 3) Hydrogen sulfide (H₂S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H₂S, 25 °C, 75 %rH

SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

PCB HOLE DIMENSIONS

- 2 mm grid: Finished hole \varnothing : $0.7 + 0.09/-0.06$ mm | Drilled hole \varnothing : 0.8 ± 0.02 mm
- 2.54 mm grid: Finished hole \varnothing : $1 + 0.09/-0.06$ mm | Drilled hole \varnothing : 1.15 ± 0.02 mm

PCB HOLE PLATING

- PCB surface finish: Hole plating
- Tin: 5-15 μm tin over min. 25 μm copper
- Copper: min. 25 μm copper
- Gold over nickel: 0.05-0.2 μm gold over 2.5-5 μm nickel over min. 25 μm copper

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Preci-dip:

[351-10-109-00-003101](#) [351-10-107-00-003101](#) [351-10-112-00-016101](#) [351-10-123-00-016101](#) [351-10-122-00-016101](#) [351-10-121-00-016101](#) [351-10-161-00-003101](#) [351-10-160-00-003101](#) [351-80-109-00-003101](#) [351-10-106-00-004101](#) [351-80-104-00-003101](#) [351-80-103-00-003101](#) [351-80-102-00-003101](#) [351-10-164-00-003101](#) [351-10-163-00-003101](#) [351-10-162-00-003101](#) [351-80-111-00-003101](#) [351-10-157-00-003101](#) [351-80-108-00-003101](#) [351-80-120-00-003101](#) [351-80-106-00-003101](#) [351-80-105-00-003101](#) [351-80-117-00-003101](#) [351-80-116-00-003101](#) [351-80-115-00-003101](#) [351-80-114-00-003101](#) [351-80-113-00-003101](#) [351-80-112-00-003101](#) [351-10-137-00-003101](#) [351-10-136-00-003101](#) [351-10-147-00-003101](#) [351-80-107-00-003101](#) [351-10-134-00-003101](#) [351-80-118-00-003101](#) [351-10-143-00-003101](#) [351-10-142-00-003101](#) [351-10-141-00-003101](#) [351-10-140-00-003101](#) [351-10-139-00-003101](#) [351-10-138-00-003101](#) [351-10-149-00-003101](#) [351-10-148-00-003101](#) [351-10-158-00-003101](#) [351-10-146-00-003101](#) [351-10-159-00-003101](#) [351-10-144-00-003101](#) [351-10-155-00-003101](#) [351-10-154-00-003101](#) [351-10-153-00-003101](#) [351-10-152-00-003101](#) [351-10-151-00-003101](#) [351-10-150-00-003101](#) [351-80-147-00-003101](#) [351-80-119-00-003101](#) [351-80-158-00-003101](#) [351-10-145-00-003101](#) [351-80-121-00-003101](#) [351-10-156-00-003101](#) [351-80-153-00-003101](#) [351-80-152-00-003101](#) [351-80-151-00-003101](#) [351-80-150-00-003101](#) [351-80-149-00-003101](#) [351-80-148-00-003101](#) [351-80-159-00-003101](#) [351-80-144-00-003101](#) [351-80-157-00-003101](#) [351-80-145-00-003101](#) [351-80-155-00-003101](#) [351-80-154-00-003101](#) [351-10-102-00-004101](#) [351-80-164-00-003101](#) [351-80-163-00-003101](#) [351-80-162-00-003101](#) [351-80-161-00-003101](#) [351-80-160-00-003101](#) [351-80-123-00-003101](#) [351-80-122-00-003101](#) [351-80-134-00-003101](#) [351-80-156-00-003101](#) [351-10-104-00-004101](#) [351-10-103-00-004101](#) [351-80-129-00-003101](#) [351-80-128-00-003101](#) [351-80-127-00-003101](#) [351-80-126-00-003101](#) [351-80-125-00-003101](#) [351-80-124-00-003101](#) [351-80-135-00-003101](#) [351-10-133-00-003101](#) [351-80-133-00-003101](#) [351-80-146-00-003101](#) [351-80-131-00-003101](#) [351-80-130-00-003101](#) [351-80-141-00-003101](#) [351-80-140-00-003101](#) [351-80-139-00-003101](#) [351-80-138-00-003101](#) [351-80-137-00-003101](#) [351-80-136-00-003101](#)