



MATERIALS:

Body: Brass, Center Contact: Gold plated brass

Outer Contact: Tarnish Resistant gold plated Beryllium Copper.

Dielectric: Teflon

Gasket/Seals: Silicone rubber

Resistor: Deposited carbon film

Marking: "Pomona 3840"

Label: "TERM, *Ω 1/2W"

RATINGS:

Frequency Range: DC to 500 MHz

Resistance Tolerance: $\pm 1\%$

Power: 1/2W @ 70°C Max

ORDERING INFORMATION: Model 3840-*

*= Resistance Value 50, 75

Ordering Example: 3840-50 = 50 Ohms

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

10/01/07

D1094113
Rev. 100

Sales: 800-490-2361 Fax: 425-446-5844
Technical Support: technicalsupport@pomonatest.com

www.pomonaelectronics.com

Page 1 of 1