



ISO9001:2008 Certified

**Mechanical Specifications (mm)**

D:	16.0	± max
T:	6.0	± max
Lead Diameter	0.8	± nom
S:	7.8	± nom
L:	38.0	± nom
Coating Lead Run Down (straight Leads)	5.0	± max
B:	5.00	± nom
C:	3.45	± nom



**Electrical Specifications**

Resistance:	220.0 Ω	± 25 %
Max Steady State Current upto 65°C:	2.00	A
Max Rec. Energy Rating:	40	J
Actual Failure Instantaneous Energy:	80	J
Maximum Capacitance @ 120 VAC:	3,473	µf
Maximum Capacitance @ 240 VAC:	868	µf
Resistance @ 100% Max Current:	0.90	Ω
Resistance @ 50% Max Current:	1.90	Ω
Body Temperature at 100% Max Current:	191.00	°c
Dissipation Constant:	18.0	mw/°c
Thermal Time Constant:	45	Sec.
Material Type (for Beta and Curve):	L	

<b>SL15 22102</b>	
Date: 07/15/2010	Drawn by: Erin Landis
Ametherm, Inc. 3111 N. Deer Run Road Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: a

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SL15 22102](#)