

1. Features

- Typical 1dB bandwidth of 10.85 MHz
- High attenuation
- Single Ended Operation
- Surface Mounted Package (SMD)

RoHS Compliant

Tested by SGS Testing Korea


2. Electrical Specifications

Source and Load Impedance = 50Ω


Operating Temperature : +25°C

		Minimum	Typical	Maximum
Center Frequency (fo)	MHz	-	125.0	-
Insertion Loss	dB	-	24.0	26.0
1dB Bandwidth	MHz	10.7	10.85	-
3dB Bandwidth	MHz	-	11.32	-
40dB Bandwidth	MHz	-	13.3	13.4
Amplitude Ripple (fo ± 5.14 MHz)	dB	-	0.55	1.0
Group Delay Variation (fo ± 5.14 MHz)	nsec	-	40	100
Absolute Delay	usec	-	2.07	-
Ultimate Rejection	dB	50	55	-
Temperature Coefficient of Frequency	ppm/°C	-	-18	-

S1365 Package Dimension



Matching Schematic



Dimensions shown are nominal in millimeters

Body : Al₂O₃

Lid : Kovar, Ni Plated

Termination : Au plating 0.3 ~ 1.0um, over a 1.27 ~ 8.89um Ni Plating

Pin Configuration

Pin Configuration			
Input	11	Ground	6,12
Output	5	Others	Ground

3. Typical Performance (at +25°C)

