



Micro Commercial Components 20736 Marilla Street Chatsworth CA 91311

Phone: (818) 701-4933 Fax: (818) 701-4939 SL54 THRU SL510

Features

- Lead Free Finish/RoHS Compliant(Note 1) ("P" Suffix designates RoHS Compliant. See ordering information)
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- High Surge forward current capability
- Extremely Low Thermal Resistance
- Halogen free available upon request by adding suffix "-HF"

Maximum Ratings

- Operating Temperature: -55°C to +150°C
- Storage Temperature: -55°C to +150°C
- Maximum Thermal Resistance; 15°C/W Junction To Lead


MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
SL54	SL54	40V	28V	40V
SL56	SL56	60V	42V	60V
SL510	SL510	100V	70V	100V


Electrical Characteristics @ 25°C Unless Otherwise Specified

Average Forward Current	$I_{F(AV)}$	5.0A	T _A = 75°C
Peak Forward Surge Current	I _{FSM}	100A	8.3ms, half sine
Maximum Instantaneous Forward Voltage			
SL54	V_{F}	.45V	I _{FM} = 5.0A;
SL56 SL510		.50V .70V	T _a = 25°C
Maximum DC Reverse Current At Rated DC Blocking Voltage	I _R	.5mA	T _a = 25°C


Note: 1. High Temperature Solder Exemptions Applied, see EU Directive Annex 7a.

5 Amp Schottky Rectifier 40~100 Volts





DIMENSIONS						
	INCHES		MM			
DIM	MIN	MAX	MIN	MAX	NOTE	
Α	.260	.280	6.60	7.11		
В	.220	.245	5.59	6.22		
С	.006	.012	0.15	0.31		
D	.030	.060	0.76	1.52		
Е	.305	.320	7.75	8.13		
F	.079	.103	2.00	2.62		
G	.108	.128	2.75	3.25		
Н	.002	.008	0.050	0.203		





Characteristics(Typical)

FIG1 Forward Current Dearting Curve




FIG2:Surge Forward Current Capadility




FIG3: Forward Voltage





FIG4:Typical Reverse Characteristics





Ordering Information:

Device	Packing	
Part Number-TP	Tape&Reel: 3Kpcs/Reel	

Note: Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Micro Commercial Components (MCC): SL54-TP SL510-TP