


VF-SI/TR5/1AT - Fuse set



2901005

<https://www.phoenixcontact.com/us/products/2901005>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Fuse set, number: 8 Pcs., fuse type: Fuse (TR5), nominal current: 1 A, tripping characteristic: slow-blow (T)

Commercial Data

Item number	2901005
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to Order (non-returnable)
Sales Key	C421
Product Key	CK21Z1
GTIN	4046356556361
Weight per Piece (including packing)	5.7 g
Weight per Piece (excluding packing)	0.77 g
Customs tariff number	85361010
Country of origin	CN

VF-SI/TR5/1AT - Fuse set

2901005

<https://www.phoenixcontact.com/us/products/2901005>



Technical Data

Product properties

Product type	Fuse
Number of fuses in the set	8

Electrical properties

Tripping characteristic	slow-blow (T)
Rated voltage	250 V
Maximum power dissipation for nominal condition	0.44 W
Nominal current I_N	1 A
Fuse rating	TR5
Fuse	Fuse

Dimensions

Dimensions	8.5 x 8 mm
------------	------------

VF-SI/TR5/1AT - Fuse set

2901005

<https://www.phoenixcontact.com/us/products/2901005>



Approvals



EAC

Approval ID: RU C-DE.BL08.B.00724

VF-SI/TR5/1AT - Fuse set



2901005

<https://www.phoenixcontact.com/us/products/2901005>

Classifications

ECLASS

ECLASS-9.0	27142002
ECLASS-10.0.1	27142002
ECLASS-11.0	27142002

ETIM

ETIM 8.0	EC002704
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

VF-SI/TR5/1AT - Fuse set



2901005

<https://www.phoenixcontact.com/us/products/2901005>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com