


Features


- Compact and space-saving
- High flexibility due to modular assembly
- Easy and quick assembly
- Hood consists of two parts
- It is easy to realise a cable-to-cable housing, by screwing hood and bulkhead mounted housing together
- Suitable for two single modules of the Han-Modular® series
















Technical characteristics

Specifications	DIN EN 61 984
Hoods/housings	
Material	aluminium die-cast / zinc die-cast
Surface	powder coated
Locking element	Han-Easy Lock®
Hoods/housings seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 in locked position	IP65
Mating cycles	≥ 500
PE contact	
- conductor cross-section	10 mm ² / AWG 8
- stripping length	10 mm
- tightening torque	1 Nm



- ① Cable entry
- ② Hood
- ③ Carrier hood
- ④ Bulkhead mounted housing
- ⑤ Angled housing



Identification	Part number	Cable entry metric	Drawing	Dimensions in mm
Hood top entry 	19 14 002 0400 19 14 002 0401 19 14 002 0402	M20 M25 M32		
side entry 	19 14 002 0501	M25		
Carrier hood 	09 14 002 0311	-		
Bulkhead mounted housing 	09 14 002 0301	-		
Angled housing NEW 	09 14 002 0950 19 14 002 0952	- M32		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19140020952](#) [09140020950](#)