


DMOI - DGOI series - 304 Stainless steel with thermoplastic hose - Food grade



Description					
Reference	ID/OD (mm)	Length (m)	Coupler	Swivel inlet BSPP male thread	Weight (kg)
DMOI 1610LS	16 x 24	10	ELS 09	G 1/2	20
DGOI 1615LS	16 x 24	15	ELS 09	G 1/2	25



Dimensions			
Reference	A mm	B mm	C mm
DMOI 1610LS	485	475	237
DGOI 1615LS	485	475	237