
D2SW Sealed Subminiature Basic Switch

Sealed Subminiature Basic Switch Conforming to IP67 (Excluding the terminals on terminal models)


- Use of epoxy resin assures stable sealing, making this switch ideal for places subject to water spray or excessive dust.
- Ideal for automobiles, automatic vending machines, refrigerators, ice-making equipment, bath equipment, hot-water supply systems, air conditioners, and industrial equipments, which require high environmental resistance.
- Models available with UL, cUL, and VDE safety standard compliance.



D 2 S W

RoHS Compliant

Model Number Legend



D2SW


List of Models

| | | | Ratings | | 0.1 A |
|------------------------------|------------------|---------------------------------------|--------------|-------------|--------------|
| Actuator | | Terminals | Contact form | 3 A | 0.1 A |
| | Solder terminals | | | D2SW-3H | D2SW-01H |
| | | Quick-connect terminals (#110) | SPDT | D2SW-3T | D2SW-01T |
| | | PCB terminals | | D2SW-3D | D2SW-01D |
| Pin plunger | | | SPDT | D2SW-3M | D2SW-01M |
| | | Molded lead wire terminals (300 mm) | SPST-NC | D2SW-3-2M | D2SW-01-2M |
| | | | SPST-NO | D2SW-3-3M | D2SW-01-3M |
| | | Molded lead wire terminals (1,000 mm) | SPDT | D2SW-3M-0 | D2SW-01M-0 |
| | | Solder terminals | | D2SW-3L1H | D2SW-01L1H |
| | | Quick-connect terminals (#110) | SPDT | D2SW-3L1T | D2SW-01L1T |
| | | PCB terminals | | D2SW-3L1D | D2SW-01L1D |
| Hinge lever | ~ | Molded lead wire terminals (300 mm) | SPDT | D2SW-3L1M | D2SW-01L1M |
| | <u>~</u> . | | SPST-NC | D2SW-3L1-2M | D2SW-01L1-2M |
| | | | SPST-NO | D2SW-3L1-3M | D2SW-01L1-3M |
| | | Molded lead wire terminals (1,000 mm) | SPDT | D2SW-3L1M-0 | D2SW-01L1M-0 |
| | | Solder terminals | | D2SW-3L2H | D2SW-01L2H |
| | A A | Quick-connect terminals (#110) | SPDT | D2SW-3L2T | D2SW-01L2T |
| | | PCB terminals | | D2SW-3L2D | D2SW-01L2D |
| Hinge roller lever | | | SPDT | D2SW-3L2M | D2SW-01L2M |
| | | Molded lead wire terminals (300 mm) | SPST-NC | D2SW-3L2-2M | D2SW-01L2-2M |
| | | | SPST-NO | D2SW-3L2-3M | D2SW-01L2-3M |
| | | Molded lead wire terminals (1,000 mm) | SPDT | D2SW-3L2M-0 | D2SW-01L2M-0 |
| | | Solder terminals | | D2SW-3L3H | D2SW-01L3H |
| | | Quick-connect terminals (#110) | SPDT | D2SW-3L3T | D2SW-01L3T |
| | | PCB terminals | - | D2SW-3L3D | D2SW-01L3D |
| Simulated roller hinge lever | \sim | | SPDT | D2SW-3L3M | D2SW-01L3M |
| | <u>~</u> | Molded lead wire terminals (300 mm) | SPST-NC | D2SW-3L3-2M | D2SW-01L3-2M |
| | | | SPST-NO | D2SW-3L3-3M | D2SW-01L3-3M |
| | | Molded lead wire terminals (1,000mm) | SPDT | D2SW-3L3M-0 | D2SW-01L3M-0 |

Safety Standard Approved Models

| Ratings | | | | 3 A | 0.1 A |
|------------------------|--|-------------------------------------|--------------|------------|-------------|
| Actuator | | Terminals | Contact form | 3 A | 0.1 A |
| | | Solder terminals | | D2SW-3HS | D2SW-01HS |
| Pin plunger | | Quick-connect terminals (#110) | | D2SW-3TS | D2SW-01TS |
| | | PCB terminals | | D2SW-3DS | D2SW-01DS |
| | | Molded lead wire terminals (300 mm) | | D2SW-3MS | D2SW-01MS |
| | | Solder terminals | | D2SW-3L1HS | D2SW-01L1HS |
| Llings Jours | | Quick-connect terminals (#110) | | D2SW-3L1TS | D2SW-01L1TS |
| Hinge lever | ~ | PCB terminals | | D2SW-3L1DS | D2SW-01L1DS |
| | | Molded lead wire terminals (300 mm) | SPDT | D2SW-3L1MS | D2SW-01L1MS |
| | | Solder terminals | 5PD1 - | D2SW-3L2HS | D2SW-01L2HS |
| Hinge roller lever | 6 | Quick-connect terminals (#110) | | D2SW-3L2TS | D2SW-01L2TS |
| Hillige toller level | and the second s | PCB terminals | | D2SW-3L2DS | D2SW-01L2DS |
| | | Molded lead wire terminals (300 mm) | | D2SW-3L2MS | D2SW-01L2MS |
| | | Solder terminals | | D2SW-3L3HS | D2SW-01L3HS |
| Simulated roller hinge | ~ | Quick-connect terminals (#110) | | D2SW-3L3TS | D2SW-01L3TS |
| lever | <u> </u> | PCB terminals | | D2SW-3L3DS | D2SW-01L3DS |
| | | Molded lead wire terminals (300 mm) | | D2SW-3L3MS | D2SW-01L3MS |

Contact Form



Separator (Sold Separately), Terminal Connector (Sold Separately) => Refer to "Basic Switch Common Accessories"

Contact Specifications

| Item | Model | D2SW-3 models | D2SW-01 models | |
|--|----------------------|-----------------|----------------|--|
| | Specification | Rivet | Crossbar | |
| Contact | Material | Silver | Gold alloy | |
| | Gap (standard value) | 0.5 mm | | |
| Inrush | NC | 20 A max. | 1 A max. | |
| current NO | | 10 A max. | 1 A max. | |
| Minimum applicable load (reference value) * | | 160 mA at 5 VDC | 1 mA at 5 VDC | |

* Please refer to "Using Micro Loads" in "Precautions" for more information on the minimum applicable load.

Ratings

| Model | Item Rated voltage | Resistive load |
|------------------|-----------------------|----------------|
| D2SW-3 models | 250 VAC 125 VAC | 2 A 3 A |
| models | 30 VDC | 3 A |
| D2SW-01 | 125 VAC | 0.1 A |
| models | 30 VDC | 0.1 A |

Note. The above rating values apply under the following test conditions.

(1) Ambient temperature: 20±2°C

(2) Ambient humidity: 65±5%

(3) Operating frequency: 30 operations/min

Approved Safety Standards

UL (UL61058-1)/cUL (CSA C22.2 No.61058-1)

The terminal specification for models with UL/cUL safety standard certification is "HS", "TS", "DS" or "MS."

| Rated voltage | Model | D2SW-3 | D2SW-01 |
|--------------------|-------|------------|------------|
| 125 VAC 250 VAC | | 3 A 2 A | 0.1 A - |
| 30 VDC | | 3 A | 0.1 A |

VDE (EN61058-1)

The models in the *List of Models* on the previous page are not certified for VDE standards.

Contact your OMRON representative if you require certified models.


| Rated voltage Mo | del D2 | 2SW-3 | D2SW-01 |
|---------------------------|-----------|----------------|-------------------|
| 125 VAC | | - | 0.1 A |
| 250 VAC | | 2 A | - |
| 30 VDC | | 2 A | 0.1 A |
| Testing conditions: D2SW- | 3E4 (30.0 | 00 operations) | T85 (0°C to 85°C) |

D2SW-01 5E4 (50,000 operations) T85 (0°C to 85°C) D2SW-01 5E4 (50,000 operations) T85 (0°C to 85°C)


0.5

Terminals and Shapes (Unit: mm)


Solder terminals




<PCB Mounting Dimensions (Reference)> 3-1.35 dia. to 1.5 holes



•Quick-connect terminals (#110)



PCB terminals



D 2 S W

Characteristics

| Item Model | | D2SW-3 models | D2SW-01 models | |
|---|--|--|--|--|
| Permissible o | perating speed | 0.1 mm to 1 m/s (for pin plunger models) | | |
| Permissible | Mechanical | 300 operations/min | | |
| operating frequency | Electrical | 60 operations/min | | |
| Insulation res | istance | 100 m Ω min. (at 500 VE | C with insulation tester) | |
| | For terminal models | 30 mΩ max. | 50 m Ω max. | |
| Contact resistance | For molded lead wire models (300mm) | 50 m Ω max. | 70 m Ω max. | |
| (initial value) | For molded lead wire models (1,000mm) | 200 m Ω max. | $250 \text{ m}\Omega$ max. | |
| | Between terminals of the same polarity | 1,000 VAC 50/60 Hz for 1 min | 600 VAC 50/60 Hz for 1 min | |
| Dielectric strength *1 | Between current-carrying metal parts and ground | 1,500 VAC 50/ | 60 Hz for 1 min | |
| onongin i | Between terminals and non-current-carrying metal parts | 1,500 VAC 50/60 Hz for 1 min | | |
| Vibration resistance *2 | Malfunction | 10 to 55 Hz, 1.5 mm double amplitude | | |
| Shock | Destruction | 1,000 m/s² {app | rox. 100G} max. | |
| resistance | Malfunction *2 | 300 m/s² {appi | rox. 30G} max. | |
| | Mechanical | 5,000,000 operations m | nin. (60 operations/min) | |
| Durability * 3 | Electrical | 200,000 operations min. (30 operations/min) (125 VAC 3 A) 100,000 operations min. (30 operations/min) (250 VAC 2 A) | 200,000 operations min. (30 operations/min) | |
| Degree of | For terminal models | IEC IP67 (excluding the terminals on terminal mod | | |
| protection | For molded lead wire models | IEC IP67 | | |
| Degree of protection against electric shock | | Class I | | |
| Proof tracking index (PTI) | | 175 | | |
| Ambient operating temperature | | -40°C to +85°C (at ambient humidity of 60% max.) (with no icing or condensation) | | |
| Ambient oper | ating humidity | 95% max. (for +5°C to +35°C) | | |
| Weight | | Approx. 2 g (for pin plunger models with terminals) | | |

Note. The data given above are initial values.

- *1. The values for dielectric strength shown are for models with a Separator (refer to "Basic Switch Common Accessories").
- *2. For the pin plunger models, the above values apply for use at the free position and total travel position. For the lever models, they apply at the total travel position. Close or open circuit of the contact is 1 ms max.

*3. For testing conditions, consult your OMRON sales representative.

Mounting Holes (Unit: mm)

2-2.4 dia. mounting holes or M2.3 screw holes

Dimensions (Unit: mm) slash Operating Characteristics

Models with terminals

D

2 S

Ŵ


The illustrations and dimensions are for models with solder terminals. Refer to "Terminals and Shapes" of the previous page for models with quick-connect terminals (#110) and PCB terminals.

0.5

6

(Note. The dimensions not described are the same as those of models with pin plungers.)


The 🗌 is replaced with the code for the terminal that you need. See the "List of Models" for available combinations of models.



| Operating Force | OF | Max. | 1.77 N {180 gf} |
|-----------------------|----|------|-----------------|
| Releasing Force | RF | Min. | 0.29 N {30 gf} |
| Pretravel | PT | Max. | 0.6 mm |
| Overtravel | OT | Min. | 0.5 mm |
| Movement Differential | MD | Max. | 0.1 mm |
| Operating Position | OP | | 8.4±0.3 mm |

●Hinge Lever Models D2SW-3L1□ D2SW-01L1□






| Operating Force | OF | Max. | 0.59 N {60 gf} |
|-----------------------|----|------|----------------|
| Releasing Force | RF | Min. | 0.06 N {6 gf} |
| Overtravel | OT | Min. | 1.0 mm |
| Movement Differential | MD | Max. | 0.8 mm |
| Free Position | FP | Max. | 13.6 mm |
| Operating Position | OP | | 8.8±0.8 mm |

●Simulated Roller Hinge Lever Models D2SW-3L3□








| Operating Force | OF | Max. | 0.59 N {60 gf} |
|-----------------------|----|------|----------------|
| Releasing Force | RF | Min. | 0.06 N {6 gf} |
| Overtravel | OT | Min. | 1.0 mm |
| Movement Differential | MD | Max. | 0.8 mm |
| Free Position | FP | Max. | 15.5 mm |
| Operating Position | OP | | 10.7±0.8 mm |

●Hinge Roller Lever Models D2SW-3L2□ D2SW-01L2□






| OF | Max. | 0.59 N {60 gf} |
|----|----------------------|--|
| RF | Min. | 0.06 N {6 gf} |
| ОТ | Min. | 1.0 mm |
| MD | Max. | 0.8 mm |
| FP | Max. | 19.3 mm |
| OP | | 14.5±0.8 mm |
| | RF OT MD FP | RF Min. OT Min. MD Max. FP Max. |

Note 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions. Note 2. The operating characteristics are for operation in the A direction (\clubsuit).

(Models with lead wires)

Pin plunger models are shown as representatives. Dimensions and operation characteristics of other actuator models are the same as those of terminal models. The illustration and drawing shown is the SPDT model. SPST-NC model and SPST-NO model are omitted in the illustration below.



Note 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions. Note 2. The operating characteristics are for operation in the A direction (\clubsuit).

5

Precautions

★Please refer to "Basic Switches Common Precautions" for correct use.

Cautions

Degree of Protection

Do not use the Switch underwater.

The Switch was tested and found to meet the conditions necessary to meet the following standard, however, the test checks for water intrusion after immersion for a specified time period, not for switching operation underwater.

JIS C0920:

Degrees of protection provided by enclosures of electrical apparatus (IP Code)

IEC 60529:

Degrees of protection provided by enclosures (IP Code) Degree of protection:IP67

(check water intrusion after immersion for 30 min submerged 1 m underwater)

Protection Against Chemicals

Prevent the Switch from coming into contact with oil or chemicals.

Otherwise, damage to or deterioration of Switch materials may result.

Soldering

Connecting to Solder Terminals

When soldering the lead wire to the terminal, first insert the lead wire conductor through the terminal hole and then conduct soldering.

Complete the soldering at the iron tip temperature between 350 to 400°C within 5 seconds, and do not apply any external force for 1 minute after soldering. Soldering at a excessively high temperature or soldering for more than 5 seconds may deteriorate the characteristics of the Switch.

- Connecting to Quick-connect Terminals
 Wire the quick-connect terminals (#110) with receptacles.
 Insert the terminals straight into the receptacles. Applying excessive external force laterally may cause deformation of terminals and may damage the housings.
- Connecting to PCB terminals

When using automatic soldering baths, we recommend soldering at $260\pm5^{\circ}$ C within 5 seconds. Make sure that the liquid surface of the solder does not flow over the edge of the board.

When soldering terminals manually, complete the soldering at the iron tip temperature between 350 to 400°C within 5 seconds, and do not apply any external force for 1 minute after soldering. When applying solder, keep the solder away from the case of the Switch and do not allow solder or flux to flow into the case.


Correct Use

Mounting

Use M2.3 mounting screw with plane washers or spring washers to securely mount the Switch. Tighten the screws to a torque of 0.23 to 0.26 N·m {2.3 to 2.7 kgf·cm}.

Operating Body

With the pin plunger models, set the Switch so that the plunger can be pushed in from directly above. Since the plunger is covered with a rubber cap, applying a force from lateral directions may cause damage to the plunger or reduction in the sealing capability.



Handling


Handle the Switch carefully so as not to break the sealing rubber.

Using Micro Loads

Using a model for ordinary loads to open or close the contact of a micro load circuit may result in faulty contact. Use models that operate in the following range. However, even when using micro load models within the following operating range, if inrush current occurs when the contact is opened or closed, it may increase the contact wear and so decrease durability. Therefore, insert a contact protection circuit where necessary. The N-level reference value applies for the minimum applicable load. This value indicates the malfunction reference level for the reliability level of 60% (λ_{60}).

(JIS C5003)

The equation, $\lambda_{60}=0.5\times10^{-6}$ /operations indicates that the estimated malfunction rate is less than $\frac{1}{2,000,000}$ operations with a reliability level of 60%.



W

Please check each region's Terms & Conditions by region website.

OMRON Corporation Electronic and Mechanical Components Company

Regional Contact

Americas https://www.components.omron.com/ Asia-Pacific https://ecb.omron.com.sg/ Korea https://www.omron-ecb.co.kr/

Europe http://components.omron.eu/ China https://www.ecb.omron.com.cn/ Japan https://www.omron.co.jp/ecb/

© OMRON Corporation 2007-2020 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

Cat. No. C097-E1-06 0120 (0207)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

D2SW-01L1MS D2SW-3HS D2SW-3TS D2SW-3MS D2SW-01L2TS D2SW-3L2MS D2SW-3L2HS D2SW-01L2MS D2SW-01L3MS D2SW-01L3TS D2SW-3L1HS D2SW-3L1TS D2SW-3L1MS D2SW-3L3HS D2SW-3L3MS D2SW-3DS D2SW-3L1DS D2SW-3L3TS D2SW-3L3DS D2SW-3L2TS D2SW-3L2DS D2SW-01HS D2SW-01TS D2SW-01DS D2SW-01MS D2SW-01L1HS D2SW-01L1DS D2SW-01L3HS D2SW-01L3DS D2SW-01L2DS D2SW-01L2H D2SW-01L3-3MS D2SW-3-2MS D2SW-3-3MS D2SW-3L1-3M D2SW-3L1H D2SW-3L1T D2SW-3L2D D2SW-3L2H D2SW-3L3M D2SW-3T D2SW-01L2HS D2SW-01L1-3MS D2SW-01L1H D2SW-3L3-3MS D2SW-3L2T D2SW-3MS-0 D2SW-3L12DS D2SW-3L3T D2SW-3D D2SW-3L3H D2SW-01D D2SW-01L3H D2SW-01H D2SW-3-3MS-0 D2SW-3H-0