


# NLC-MOD-USB

Order No.: 2701195



Serial connection to PC's USB port for data transfer or software configuration

## Commercial data

EAN	 4 046356 325400
Pack	1
Customs tariff	85366990
Gross weight in pieces	39.80 g
Country of Origin	IN
Catalog page information	Page 16 (AX-2011)

## Product notes

WEEE/RoHS-compliant since:  
17/04/2008



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

## Product description

Slot 1 option module. Connects the Nanoline controller to a Type A USB port. Functions as a serial device and requires special driver included on nanoNavigator CD.

## Technical data

### Interfaces

Interface	USB
Connection method	USB Type B
Transmission length	2 m

---

## Supply

Supply voltage	24 V DC (Power available via logic module)
Max. current consumption	18 mA
Typical current consumption	10 mA

## General data

Width	24.5 mm
Height	25.5 mm
Depth	49 mm
Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

## Certificates



Certification

cULus Listed

Certifications applied for:

Certification Ex:

---

## Accessories

Item	Designation	Description
<b>General</b>		
2701289	NLC-MOD-CAP	Replacement cover for slot 1 in base unit.
2701247	NLC-PC/USB-CBL 2M	<b>Cable</b> , serial

---

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG,England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;