


1 A sensitive gate SCR thyristor



Features

- On-state rms current, 1 A
- Narrow sensitive gate current from 30 μ A to 150 μ A
- Repetitive peak off-state voltage, 600 V
- Non-repetitive surge peak off-state voltage, 750 V
- Compact and ultraflat SMBflat-3L package with creepage distance of 3.4 mm

Applications

- Ground-fault circuit interrupter (GFCI, RCB, RCD)
- Arc-fault circuit interrupter (AFCI)
- Overvoltage crowbar protection in power supplies
- Capacitive ignition circuits
- Low consumption triggering switches

Description

Thanks to highly sensitive triggering levels, the 1 A X0115MUF SCR thyristor is suitable for all applications where available gate current is limited. The X0115MUF offers a high blocking voltage of 600 V, and a surge peak voltage of 750 V, ideal for applications like ground fault circuit interrupter (GFCI) and arc fault circuit interrupters (AFCI).

The surface mount SMBflat-3L package allows modern, compact, SMD based designs for automated manufacturing. Its 3.4 mm creepage distance guarantees a 250 V functional isolation (UL 840) at a level 2 pollution degree.

Product status link

[X0115MUF](#)

Product summary

| | |
|-------------------|--------|
| $I_{T(RMS)}$ | 1 A |
| V_{DRM}/V_{RRM} | 600 V |
| $T_{j(max.)}$ | 125 °C |

1 Characteristics

Table 1. Absolute maximum ratings (limiting values)

| Symbol | Parameters | | Value | Unit | |
|---------------------|--|--------------------|----------------|-------------|------------------|
| $I_{T(RMS)}$ | On-state RMS current (180° conduction angle) | | 1 | A | |
| $I_{T(AV)}$ | Average on-state current (180° conduction angle) | | | | |
| I_{TSM} | Non repetitive surge peak on-state current (T_j initial = 25 °C) | $t_p = 8.3$ ms | 12 | A | |
| | | $t_p = 10$ ms | | | |
| I^2t | I^2t value for fusing | $t_p = 10$ ms | $T_j = 25$ °C | 0.60 | A ² s |
| di/dt | Critical rate of rise of on-state current $I_G = 2 \times I_{GT}$, $t_r \leq 100$ ns | F = 60 Hz | $T_j = 25$ °C | 75 | A/ μ s |
| V_{DRM} / V_{RRM} | Repetitive peak off-state voltage | | $T_j = 125$ °C | 600 | V |
| V_{DSM} / V_{RSM} | Non repetitive surge peak off-state voltage | $t_p = 10$ ms | $T_j = 25$ °C | 750 | V |
| I_{GM} | Peak forward gate current | $t_p = 20$ μ s | $T_j = 125$ °C | 1.2 | A |
| $P_{G(AV)}$ | Average gate power dissipation | | $T_j = 125$ °C | 0.2 | W |
| T_{stg} | Storage junction temperature range | | | -40 to +150 | °C |
| T_j | Operating junction temperature range | | | -40 to +125 | °C |

Table 2. Electrical characteristics ($T_j = 25$ °C, unless otherwise specified)

| Symbol | Parameters | Value | | Unit |
|----------|---|-------|-----|------------|
| I_{GT} | $V_D = 12$ V, $R_L = 140$ Ω | Min. | 30 | μ A |
| | | Max. | 150 | |
| V_{GT} | | Max. | 0.8 | V |
| V_{GD} | $V_D = V_{DRM}$, $R_L = 3.3$ k Ω , $R_{GK} = 1$ k Ω , $T_j = 125$ °C | Min. | 0.2 | V |
| V_{RG} | $I_{RG} = 10$ μ A | Min. | 5 | V |
| I_H | $I_T = 50$ mA, $R_{GK} = 1$ k Ω | Max. | 5 | mA |
| I_L | $I_G = 1.2 I_{GT}$, $R_{GK} = 1$ k Ω | Max. | 6 | mA |
| dV/dt | $V_D = 67\%$ V_{DRM} , $R_{GK} = 1$ k Ω , $T_j = 125$ °C | Min. | 80 | V/ μ s |

Table 3. Static characteristics

| Symbol | Test conditions | Value | | Unit |
|---------------------|---|----------------|-----------|------------|
| V_T | $I_{TM} = 2.0$ A, $t_p = 380$ μ s | $T_j = 25$ °C | Max. 1.40 | V |
| V_{TO} | Threshold on-state voltage | $T_j = 125$ °C | Max. 0.90 | V |
| R_d | Dynamic resistance | $T_j = 125$ °C | Max. 230 | m Ω |
| I_{DRM} / I_{RRM} | $V_D = V_{DRM}$, $V_R = V_{RRM}$, $R_{GK} = 1$ k Ω | $T_j = 25$ °C | Max. 1 | μ A |
| | | $T_j = 125$ °C | 150 | μ A |

Table 4. Thermal resistance

| Symbol | Parameters | Value | Unit |
|---------------|---|-------|------|
| $R_{th(j-l)}$ | Junction to lead (DC) | 15 | °C/W |
| $R_{th(j-a)}$ | Junction to ambient (DC) for 5 cm ² copper surface | 75 | |

1.1 Characteristics (curves)

Figure 1. Maximum average power dissipation versus average on-state current




Figure 2. On-state characteristics (maximum values)




Figure 3. Average and D.C. on-state current versus ambient temperature for $1 \text{ cm}^2 \text{ S}_{Cu}$ surface




Figure 4. Average and D.C. on-state current versus lead temperature




Figure 5. Surge peak on-state current versus number of cycles




Figure 6. Non repetitive surge peak on-state current for a sinusoidal pulse with width $t_p < 10 \text{ ms}$




Figure 7. Relative variation of gate trigger current, holding current and latching current versus junction temperature (typical values)




Figure 8. Relative variation of holding current versus gate-cathode resistance (typical values)




Figure 9. Relative variation of static dV/dt immunity versus junction temperature




Figure 10. Relative variation of dV/dt immunity versus gate-cathode resistance (typical values)




Figure 11. Relative variation of dV/dt immunity versus gate-cathode capacitance (typical value)




Figure 12. Relative variation of thermal impedance junction to lead and junction to ambient versus pulse duration





Figure 13. Typical thermal resistance junction to ambient versus copper surface under anode (epoxy FR4, $e_{CU} = 35 \mu\text{m}$, SMBflat-3L)




2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 SMBflat-3L package information

- Epoxy meets UL94, V0
- Lead-free package

Figure 14. SMBflat-3L package outline




Note: This package drawing may slightly differ from the physical package. However, all the specified dimensions in the following table are guaranteed.

Table 5. SMBflat-3L mechanical data

| Ref. | Dimensions | | | | | |
|------|-------------|------|------|--|--------|--------|
| | Millimeters | | | Inches (dimensions are for reference only) | | |
| | Min. | Typ. | Max. | Min. | Typ. | Max. |
| A | 0.90 | | 1.10 | 0.0354 | | 0.0433 |
| b | 0.35 | | 0.65 | 0.0138 | | 0.0256 |
| b4 | 1.95 | | 2.20 | 0.0768 | | 0.0866 |
| c | 0.15 | | 0.40 | 0.0059 | | 0.0157 |
| D | 3.30 | | 3.95 | 0.1299 | | 0.1555 |
| E | 5.10 | | 5.60 | 0.2008 | | 0.2205 |
| E1 | 4.05 | | 4.60 | 0.1594 | | 0.1811 |
| L | 0.75 | | 1.50 | 0.0295 | | 0.0591 |
| L1 | | 0.40 | | | 0.0157 | |
| L2 | | 0.60 | | | 0.0236 | |
| e | | 1.60 | | | 0.0630 | |

Figure 15. Footprint recommendations, dimensions in mm (inches)



Note: This drawing may not be in scale; however, all the specified dimensions are guaranteed.

3 Ordering information

Figure 16. Ordering information scheme




Table 6. Ordering information

| Order code | Marking | Package | Weight | Base qty. | Delivery mode |
|------------|---------|------------|--------|-----------|---------------|
| X0115MUF | X1M | SMBflat-3L | 47 mg | 5000 | Tape and reel |

Revision history

Table 7. Document revision history

| Date | Revision | Changes |
|-------------|----------|---|
| 30-Jul-2019 | 1 | First issue. |
| 10-Oct-2019 | 2 | Updated Table 2. Electrical characteristics ($T_j = 25\text{ }^\circ\text{C}$, unless otherwise specified). |

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics – All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[X0115MUF](#)